




Part Number : [2174802224](#)

Product Description : Pre-Crimped Lead Mini-Fit Sr.
Female-to-Mini-Fit Sr. Female, Gold (Au) Plating,
300.00mm Length, 8 AWG, Red

Series Number : 217480

Status : Active

Product Category : Power and Signal Cable
Assemblies



Documents & Resources

Drawings

[2174802224 sd.pdf](#)

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2021)10043- DC (17 Jan 2022)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	217480
Description	Pre-Crimped Lead Mini-Fit Sr. Female-to-Mini-Fit Sr. Female, Gold (Au) Plating, 300.00mm Length, 8 AWG, Red
Application	Power, Wire-to-Board, Wire-to-Wire
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	Mini-Fit Sr. Crimp Terminals
Product Name	Mini-Fit Sr.
UPC	195842120907

Electrical

Current - Maximum per Contact	50.0A
-------------------------------	-------

Physical

Cable Length	300.00mm
Circuits (Loaded)	1
Circuits (maximum)	1
Color - Resin	Red
Gender	Female-Female
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Tin

Material - Resin	PVC
Net Weight	34.689/g
Number of Rows	1
Packaging Type	Bag
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Single Ended	No
Termination Interface Style	Crimp or Compression
Wire/Cable Type	UL 10669
Wire Size (AWG)	8