



Part Number : [2185363619](#)

Product Description : NTC Probe Thermistor-to-Pigtail Cable Assembly, 300.00mm, 3964 Beta Value with 1% Tolerance, 10kOhm Resistance at 25°C with 1% Tolerance, with Mounting Tab

Series Number : 21853

Status : Active

Product Category : Power and Signal Cable Assemblies



Documents & Resources

Drawings

[2185363619 sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2022)4187-DC (10 June 2022)
EU RoHS	Compliant with Exemption 7(c)-I per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	21853
Description	NTC Probe Thermistor-to-Pigtail Cable Assembly, 300.00mm, 3964 Beta Value with 1% Tolerance, 10kOhm Resistance at 25°C with 1% Tolerance, with Mounting Tab
Assembly Configuration	Single Ended Connector
Connector to Connector	NTC Thermistor-to-Pigtail
Product Name	NTC Temperature Sensor
UPC	195842833562

Electrical

Beta Value (K)	3964
Resistance at 25°C (kohms)	10
Resistance Tolerance (%)	1

Physical

Cable Length	300.00mm
Circuits (Loaded)	1
Circuits (maximum)	1
Gender	N/A
Material - Metal	Stainless Steel
Material - Resin	PTFE
Net Weight	4.500/g
Number of Rows	1
Packaging Type	Bag

Single Ended	Yes
Wire/Cable Type	UL 10344
Wire Size (AWG)	28

This document was generated on Sep 23, 2025