



Part Number : [2204240008](#)
Product Description : Squba Weather Cap for 8 or 4
Circuit Receptacle Housing
Series Number : 220424
Status : Active
Product Category : Connector Accessories



Documents & Resources

Drawings

[2204240008_sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications

[2042200000-AS-000.pdf](#)

[2077760000-AS-000.pdf](#)

[2042200000-PS-000.pdf](#)

[2042200000-TS-000.pdf](#)

[2077760000-PS-000.pdf](#)

[2077760000-TS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)

EU RoHS	Compliant per EU 2015/863
---------	---------------------------

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Accessories
Series	220424
Description	Squba Weather Cap for 8 or 4 Circuit Receptacle Housing
Component Type	Cap
Product Name	Squba
UPC	196823073786

Physical

Circuits (Loaded)	4, 8
Circuits (maximum)	4, 8
Color - Resin	Natural
Lock to Mating Part	Yes
Material - Resin	Polyamide
Net Weight	1.080/g
Packaging Type	Bag
Temperature Range - Operating	-40° to +105°C

Mates With / Use With

Use with Part(s)

Description	Part Number
Squba 1.8 Sealed Single Row Receptacle Assemblies	<u>204220</u>
Squba 3.6 Sealed Single Row Receptacle Assemblies	<u>207782</u>