Part Number : 2244162216
Product Description : SW1-to-Pigtail Off-the-Shelf (OTS) Cable Assembly, 11.00mm Diameter, Female, 1000.00mm Length, 4/0 AWG, Red
Series Number : 224416
Status : Active
Product Category : Power and Signal Cable Assemblies



Documents & Resources

Drawings

2244162216_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

2244100011-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC

- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	224416
Description	SW1-to-Pigtail Off-the-Shelf (OTS) Cable Assembly, 11.00mm Diameter, Female, 1000.00mm Length, 4/0 AWG, Red
Application	Power, Wire-to-Busbar, Wire-to-Board
Assembly Configuration	Single Ended Connector
Connector to Connector	SW1 11.00mm-to-Pigtail
Product Name	SW1
Type	Discrete Wire Assembly
UPC	196823528743

Electrical

Current - Maximum per Contact	300.0A
Voltage - Maximum	1000V

Physical

Cable Length	1000.00mm
Circuits (Loaded)	1
Circuits (maximum)	1

Color - Resin	Red
Gender	Female-Pigtail
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Silver
Material - Resin	PBT
Net Weight	1410.876/g
Number of Rows	1
Overmolded	No
Packaging Type	Bag
Single Ended	Yes
Termination Interface Style	Crimp or Compression
Wire/Cable Type	UL 1015
Wire Size (AWG)	4/0

Mates With / Use With

Mates with Part(s)

Description	Part Number
SW1 11.00mm Knurled Press-fit Locking Pins	218336