



Part Number : [310731042](#)
Product Description : 2.54mm H-DAC 64, 6 Way
Male Housing Assembly, Single Row, Polarization C
Series Number : 31073
Status : Active
Product Category : Connector Housings



Documents and Resources

Drawings

- [310731042 sd.pdf](#)
- [PK-30907-737-001.pdf](#)
- [PK-31301-076-001.pdf](#)

3D Models and Design Files

- [STEP AP242](#)
- [SOLIDWORKS](#)
- [Creo](#)

Specifications

- [AS-31067-100-001.pdf](#)
- [PS-31067-0001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant
China RoHS	Not Relevant
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Contains Boric acid per D(2025)6375-DC (05 Nov 2025)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS

- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	31073
Description	2.54mm H-DAC 64, 6 Way Male Housing Assembly, Single Row, Polarization C
Application	Automotive, Power, Wire-to-Wire
Comments	Polarization Option C, Brown
Product Name	H-DAC 64
UPC	756054393932

Physical

Circuits (maximum)	6
Color - Resin	Brown
Gender	Plug
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Modified Polystyrene, Polyester
Net Weight	2.360/g
Number of Rows	1
Packaging Type	Bag

Panel Mount	No
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	2.54mm
Polarized to Mating Part	Yes
Ports	1
Stackable	No
Temperature Range - Operating	-40° to +100°C

Mates With / Use With

Mates with Part(s)

Description	Part Number
2.54mm H-DAC 64, 6 Way Receptacle Assembly, Single Row, Polarization C	<u>310731012</u>

Use with Part(s)

Description	Part Number
Use With	See Product Specification