



Part Number : [393800107](#)
Product Description : 6.35mm Pitch Beau Eurostyle
Fixed Mount PCB Terminal Block, Modular, 7 Circuits
Series Number : 39380
Status : Active
Product Category : Terminal Blocks and Barrier
Strip
Engineering Part Number : MX-MSP0700S-0N



Documents and Resources

Drawings

[393800107_sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[Symbol and Footprint \(Multi-Format\)](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)4165-DC (25 June 2025) SCIP:da663e5f-f664-4659-a1aa-a954d02d2854
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC

- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Terminal Blocks and Barrier Strip
Series	39380
Description	6.35mm Pitch Beau Eurostyle Fixed Mount PCB Terminal Block, Modular, 7 Circuits
Application	Wire-to-Board
Component Type	One Piece
Product Name	Eurostyle Fixed Mount
Type	PCB Terminal Blocks and Connectors
UPC	800756794280

Electrical

Current - Maximum per Contact	30.0A
Voltage - Maximum	300V

Physical

Circuits (Loaded)	7
Color - Resin	Black
Entry Angle	Horizontal
Lock to Mating Part	None
Material - Resin	Nylon

Net Weight	51.000/g
Number of Rows	1
Orientation	Vertical
Panel Mount	No
PCB Retention	None
PCB Thickness - Recommended	4.00mm
PC Tail Length	38.10mm
Pitch - Mating Interface	6.35mm
Pitch - Termination Interface	6.35mm
Polarized to Mating Part	N/A
Shrouded	Fully
Stackable	Yes
Temperature Range - Operating	110°C
Wire Size (AWG)	10, 12, 14, 16, 18, 20, 22, 24, 26, 28, 30
Wire Size mm ²	0.05-2.50