



Part Number : [395061515](#)
Product Description : 3.50mm Pitch Eurostyle Right-Angle PCB Header, with Threaded Retention Inserts, Gold (Au) Plated, Black, 15 Circuits
Series Number : 39506
Status : Active
Product Category : Terminal Blocks and Barrier Strip



Documents and Resources

Drawings

- [395061515 sd.pdf](#)
- [STEP AP242](#)
- [SOLIDWORKS](#)
- [Creo](#)
- [Symbol and Footprint \(Multi-Format\)](#)

Specifications

- [PS-39500-001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Terminal Blocks and Barrier Strip
Series	39506
Description	3.50mm Pitch Eurostyle Right-Angle PCB Header, with Threaded Retention Inserts, Gold (Au) Plated, Black, 15 Circuits
Application	Wire-to-Board
Component Type	PCB Header
Product Name	Eurostyle Pluggable
Type	PCB Terminal Blocks and Connectors
UPC	822350451895

Agency

UL	E48521
----	--------

Electrical

Current - Maximum per Contact	8.0A
Voltage - Maximum	300V

Physical

Circuits (Loaded)	15
Color - Resin	Black

Entry Angle	N/A
Lock to Mating Part	Yes
Number of Rows	1
Orientation	Right Angle
Panel Mount	No
PCB Thickness - Recommended	2.50mm
PC Tail Length	3.50mm
Pitch - Mating Interface	3.50mm
Pitch - Termination Interface	3.50mm
Polarized to Mating Part	Yes
Shrouded	Fully
Stackable	No
Temperature Range - Operating	-40° to +105°C
Wire Size (AWG)	N/A

Mates With / Use With

Mates with Part(s)

Description	Part Number
3.50mm Pitch Eurostyle Horizontal Plugs	<u>39504</u>
3.50mm Pitch Eurostyle Vertical Plugs	<u>39507</u>
Mates With	Most 3.50mm Pitch Industry Standard Plugs