



**Part Number :** [395377910](#)

**Product Description :** 5.08mm Pitch Eurostyle  
Horizontal Plug, with Retention Screws and Reverse  
Imprinting, Rear Wire Entry, Green Housing, Gold (Au)  
Plated, 10 Circuits

**Series Number :** 39537

**Status :** Active

**Product Category :** Terminal Blocks and Barrier  
Strip



---

## Documents and Resources

### Drawings

[395377910\\_sd.pdf](#)

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

---

## Product Environment Compliance

### Compliance

|                    |                                                   |
|--------------------|---------------------------------------------------|
| GADSL/IMDS         | Not Relevant                                      |
| China RoHS         | Not Reviewed per SJ/T<br>11365-2006               |
| EU ELV             | Not Relevant                                      |
| Low-Halogen Status | Not Reviewed per IEC 61249-2-21                   |
| REACH SVHC         | Not Reviewed per D(2025)7771-<br>DC (04 Feb 2026) |
| EU RoHS            | Not Reviewed per EU 2015/863                      |

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

#### Additional Product Compliance Information

---

## Part Details

### General

|                |                                                                                                                                                     |
|----------------|-----------------------------------------------------------------------------------------------------------------------------------------------------|
| Status         | Active                                                                                                                                              |
| Category       | Terminal Blocks and Barrier Strip                                                                                                                   |
| Series         | 39537                                                                                                                                               |
| Description    | 5.08mm Pitch Eurostyle Horizontal Plug, with Retention Screws and Reverse Imprinting, Rear Wire Entry, Green Housing, Gold (Au) Plated, 10 Circuits |
| Application    | Wire-to-Board                                                                                                                                       |
| Comments       | Rear Wire Entry, with Reverse Imprinting                                                                                                            |
| Component Type | Plug                                                                                                                                                |
| Product Name   | Eurostyle Pluggable                                                                                                                                 |
| Type           | PCB Terminal Blocks and Connectors                                                                                                                  |
| UPC            | 822350675901                                                                                                                                        |

### Electrical

|                               |       |
|-------------------------------|-------|
| Current - Maximum per Contact | 18.0A |
| Voltage - Maximum             | 300V  |

### Physical

|                     |            |
|---------------------|------------|
| Circuits (Loaded)   | 10         |
| Color - Resin       | Green      |
| Entry Angle         | Horizontal |
| Lock to Mating Part | Yes        |

|                               |                                |
|-------------------------------|--------------------------------|
| Number of Rows                | 1                              |
| Orientation                   | N/A                            |
| Panel Mount                   | No                             |
| PCB Retention                 | N/A                            |
| Pitch - Mating Interface      | 5.08mm                         |
| Pitch - Termination Interface | 5.08mm                         |
| Polarized to Mating Part      | Yes                            |
| Stackable                     | No                             |
| Temperature Range - Operating | -40° to +105°C                 |
| Wire Size (AWG)               | 12, 14, 16, 18, 20, 22, 24, 26 |
| Wire Size mm <sup>2</sup>     | 0.13-3.31                      |

### Solder Process Data

|                              |     |
|------------------------------|-----|
| Lead-Free Process Capability | N/A |
|------------------------------|-----|

---

## Mates With / Use With

### Mates with Part(s)

| Description                                   | Part Number                                             |
|-----------------------------------------------|---------------------------------------------------------|
| 5.08mm Pitch Eurostyle Vertical PCB Headers   | <a href="#"><u>39535</u></a>                            |
| 5.08mm Pitch Eurostyle Horizontal PCB Headers | <a href="#"><u>39536</u></a>                            |
| Mates With                                    | Most 5.08mm (.200") Pitch Industry Standard PCB Headers |