



**Part Number :** [395934304](#)  
**Product Description :** 5.00mm Pitch Eurostyle 45° Wire Entry Fixed Mount PCB Terminal Block, Green Housing, 4 Circuits  
**Series Number :** 39593  
**Status :** Active  
**Product Category :** Terminal Blocks and Barrier Strip



## Documents and Resources

### Drawings

[395934304 sd.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[Symbol and Footprint \(Multi-Format\)](#)

## Product Environment Compliance

### Compliance

|                    |                                               |
|--------------------|-----------------------------------------------|
| GADSL/IMDS         | Not Relevant                                  |
| China RoHS         | Not Reviewed per SJ/T 11365-2006              |
| EU ELV             | Not Relevant                                  |
| Low-Halogen Status | Not Reviewed per IEC 61249-2-21               |
| REACH SVHC         | Not Reviewed per D(2025)7771-DC (04 Feb 2026) |
| EU RoHS            | Not Reviewed per EU 2015/863                  |

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

## Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Substances of Interest

- PFAS

## EU RoHS Certificate of Compliance

## Additional Product Compliance Information

---

## Part Details

### General

|                |                                                                                                 |
|----------------|-------------------------------------------------------------------------------------------------|
| Status         | Active                                                                                          |
| Category       | Terminal Blocks and Barrier Strip                                                               |
| Series         | 39593                                                                                           |
| Description    | 5.00mm Pitch Eurostyle 45° Wire Entry Fixed Mount PCB Terminal Block, Green Housing, 4 Circuits |
| Application    | Wire-to-Board                                                                                   |
| Component Type | One Piece                                                                                       |
| Product Name   | Eurostyle Fixed Mount                                                                           |
| Type           | PCB Terminal Blocks and Connectors                                                              |
| UPC            | 822350495813                                                                                    |

### Agency

|    |        |
|----|--------|
| UL | E48521 |
|----|--------|

### Electrical

|                               |       |
|-------------------------------|-------|
| Current - Maximum per Contact | 10.0A |
| Voltage - Maximum             | 300V  |

### Physical

|                    |       |
|--------------------|-------|
| Circuits (Loaded)  | 4     |
| Circuits (maximum) | 4     |
| Color - Resin      | Green |

|                               |                    |
|-------------------------------|--------------------|
| Entry Angle                   | 45° Angle          |
| Lock to Mating Part           | None               |
| Number of Rows                | 1                  |
| Orientation                   | 45° Angle          |
| Panel Mount                   | No                 |
| PCB Thickness - Recommended   | 3.40mm             |
| PC Tail Length                | 4.40mm             |
| Pitch - Mating Interface      | 5.00mm             |
| Pitch - Termination Interface | 5.00mm             |
| Polarized to Mating Part      | N/A                |
| Stackable                     | No                 |
| Temperature Range - Operating | -40° to +105°C     |
| Wire Size (AWG)               | 14, 16, 18, 20, 22 |
| Wire Size mm <sup>2</sup>     | 0.33-2.08          |

### Solder Process Data

|                              |        |
|------------------------------|--------|
| Max-Duration                 | 5      |
| Lead-Free Process Capability | REFLOW |
| Max-Cycle                    | 135    |
| Max-Temp                     | 260    |