



Part Number : [397140009](#)
Product Description : 5.08mm Pitch Eurostyle 45°
Wire Entry Plug, with Mounting Ends, 9 Circuits, Green
Series Number : 39714
Status : Active
Product Category : Terminal Blocks and Barrier
Strip
Engineering Part Number : M750B-14-2-09-3



Documents and Resources

Drawings

[397140009 sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)6375-DC (05 Nov 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

[Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

[Industry Documents](#)

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Terminal Blocks and Barrier Strip
Series	39714
Description	5.08mm Pitch Eurostyle 45° Wire Entry Plug, with Mounting Ends, 9 Circuits, Green
Application	Wire-to-Board
Component Type	Plug
Product Name	Eurostyle Pluggable
Type	PCB Terminal Blocks and Connectors
UPC	78172544199

Electrical

Current - Maximum per Contact	15.0A
Voltage - Maximum	300V

Physical

Circuits (Loaded)	9
Circuits (maximum)	9
Color - Resin	Green
Entry Angle	45° Angle
Lock to Mating Part	Yes
Material - Metal	Copper Alloy

Material - Plating Mating	Tin
Material - Resin	Polyamide
Number of Rows	1
Orientation	N/A
Panel Mount	N/A
PCB Retention	N/A
Pitch - Mating Interface	5.08mm
Pitch - Termination Interface	5.08mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C
Wire Size (AWG)	12, 14, 16, 18, 20, 22, 24, 26, 28
Wire Size mm ²	0.08-3.31