



Part Number : [5055650802](#)

Product Description : 1.25mm Pitch, Micro-Lock Plus Receptacle Crimp Housing, Single Row, Positive Lock, 8 Circuits, Red

Series Number : 505565

Status : Active

Product Category : Connector Housings



Documents & Resources

Drawings

[5055650802_sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[5055650802.dxf](#)

Specifications

[5055650000-AS-000.pdf](#)

[5055659200-200.pdf](#)

[5055650000-000.pdf](#)

[5055650003-PS-000.pdf](#)

[5055651000-PS-000.pdf](#)

[5055650002-000.pdf](#)

[5055651002-PS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC

	61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	505565
Description	1.25mm Pitch, Micro-Lock Plus Receptacle Crimp Housing, Single Row, Positive Lock, 8 Circuits, Red
Application	Signal, Wire-to-Board, Wire-to-Wire
Product Name	Micro-Lock Plus
UPC	889056532105

Agency

UL	E29179
----	--------

Physical

Circuits (maximum)	8
--------------------	---

Color - Resin	Red
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	PBT
Net Weight	165.344/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	1.25mm
Pitch - Termination Interface	1.25mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +105°C

Mates With / Use With

Mates with Part(s)

Description	Part Number
1.25mm Pitch Micro-Lock Plus Vertical, Single Row, Surface Mount Headers	<u>505568</u>
1.25mm Pitch Micro-Lock Plus Right-Angle, Single Row, Surface Mount Headers	<u>505567</u>

Use with Part(s)

Description	Part Number
Pre-Crimped Lead Micro-Lock Plus Female-to-Micro-Lock Plus Female, Tin (Sn) Plating, 150.00mm Length, 26 AWG, Black	<u>797581148</u>
Pre-Crimped Lead Micro-Lock Plus Female-to-Micro-Lock Plus Female, Tin (Sn) Plating, 300.00mm Length, 26 AWG, Black	<u>797581149</u>
Pre-Crimped Lead Micro-Lock Plus	<u>797582143</u>

Female-to-Micro-Lock Plus Female, Gold (Au) Plating, 150.00mm Length, 26 AWG, Black	
Pre-Crimped Lead Micro-Lock Plus Female-to-Micro-Lock Plus Female, Gold (Au) Plating, 300.00mm Length, 26 AWG, Black	<u>797582144</u>
Micro-Lock Plus Female Crimp Terminals	<u>505431</u>