




Part Number : [525591834](#)

Product Description : Easy-On FFC/FPC Connector, 0.50mm Pitch, Slider Series, Vertical, 3.90mm Height, 18 Circuits, Tin-Silver-Bismuth Plating

Series Number : 52559

Status : Obsolete

Product Category : FFC / FPC Connectors



Documents & Resources

[525591834 stp.zip](#)

[Symbol and Footprint \(Multi-Format\)](#)

Specifications

[525590003-A00.pdf](#)

[PS-52559-019-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	FFC / FPC Connectors
Series	Slider
Description	Easy-On FFC/FPC Connector, 0.50mm Pitch, Slider Series, Vertical, 3.90mm Height, 18 Circuits, Tin-Silver-Bismuth Plating
Product Name	Easy-On
UPC	887191347349

Agency

UL	E29179
----	--------

Electrical

Current - Maximum per Contact	0.5A
Voltage - Maximum	50V

Physical

Actuator Type	Slider
Circuits (Loaded)	18
Color - Resin	Natural
Contact Position	N/A
Durability (mating cycles max)	20
Flammability	94V-0
Mated Height	3.90mm
Material - Metal	Phosphor Bronze

Material - Plating Mating	Tin-Silver-Bismuth
Material - Plating Termination	Tin-Silver-Bismuth
Material - Resin	Nylon
Net Weight	253.060/mg
Orientation	Vertical
Packaging Type	Embossed Tape on Reel
PCB Locator	No
PCB Mounting	Surface Mount
PCB Retention	Yes
PC Tail Length	2.00mm
Pitch - Mating Interface	0.50mm
Pitch - Termination Interface	0.50mm
Polarized to PCB	No
Stackable	No
Temperature Range - Operating	-40° to +85°C
Wire/Cable Type	FFC/FPC

Mates With / Use With

Mates with Part(s)

Description	Part Number
0.50mm Pitch Premo-Flex FFC Jumpers	<u>15166</u>
0.50mm Pitch Premo-Flex FFC Jumpers	<u>15266</u>
0.50mm Pitch Premo-Flex FFC Jumpers	<u>15366</u>
0.50mm Pitch Premo-Flex FFC Jumpers	<u>98266</u>