



Part Number : [634620020](#)
Product Description : Insulation Anvil
Series Number : 207126
Status : Active
Product Category : Applicators and Crimp Modules

Documents and Resources

Tooling Specifications
[ATS-STANDARD-PARTS-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Relevant
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Applicators and Crimp Modules
Series	207126
Description	Insulation Anvil
Comments	See Tooling Specification (PDF) Above
Function	Cutter
Geographic Area	Global
Level of Automation	Semi-Automatic
More Detailed Tech Information	toolingsupport@molex.com
Product Name	N/A
Tool Type	Applicator
UPC	822348743582
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Mates With / Use With

Use with Part(s)

Description	Part Number
Mini-Mac Applicator	<u>638850300</u>
Mini-Mac Applicator	<u>638852700</u>

This document was generated on Feb 27, 2026