

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0638233700

Status:

Active

Overview:

Application Tooling

Description:

Hand Crimp Tool for ISO (M3) Receptacle Terminals

Documents:

RoHS Certificate of Compliance (PDF)

General	
Product Family	Application Tooling
Series	207129
Comments	See Tooling Specification (PDF) Above. Type: 4A
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	PremiumGrade
Tool Type	Hand Crimp Tool
UPC	884982769861
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Reference - Drawing Numbers	
Application Tooling Documents	ATS-6382337HM-001



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - ED/61/2018 (27 June 2018)	
Halogen-Free	
Status	
Not Relevant	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

207129 Series

Use With

638233770 Modular Crimp Head, 33001 , 33012 , 34750 , 34780 MX150 ISO (M3) Receptacle Terminals for 0.35mm² and 0.50mm² ISO Wires

Application Tooling Description	FAQ Product #
MX150 Female Terminal for Mat-Sealed Connectors, Gold Plating, Grip Code M3, Preferred Terminal for use in Sealed Application with 0.35-0.50mm², Right Reel Payoff	330012006
MX150 Female Terminal for Mat-Sealed Connectors, Gold Plating, Grip Code M3, Preferred	330013006

Terminal for use in Sealed Application with 0.35-0.50mm², Left Reel Payoff	
MX150 Female	<u>330014005</u>
Terminal for Mat-Sealed Connectors, Silver Plating, Grip Code M3, Preferred	
Terminal for use in Sealed Application with 0.35-0.50mm², Right Reel Payoff	
MX150 Female	<u>330015005</u>
Terminal for Mat-Sealed Connectors, Silver Plating, Grip Code M3, Preferred	
Terminal for use in Sealed Application with 0.35-0.50mm², Left Reel Payoff	
MX150 Female	<u>330122004</u>
Terminal for Mat-Sealed Connectors, Tin Plating, Grip Code M3, Preferred	
Terminal for use in Sealed Application with 0.35-0.50mm², Right Reel Payoff, Contact Material Thickness 0.30mm²	
MX150 Female	<u>330123004</u>
Terminal for Mat-Sealed Connectors, Tin Plating, Grip Code M3, Preferred	
Terminal for use in Sealed Application with 0.35-0.50mm², Left Reel Payoff, Contact Material Thickness 0.30mm²	