




**Part Number :** [702871272](#)  
**Product Description :** 2.54mm Pitch C-Grid Header, Breakaway, Dual Row, Vertical, with Retention Pin, 58 Circuits, 8.13mm Mating Pin Length, 0.76µm Gold (Au) Selective Plating  
**Series Number :** 70287  
**Status :** Obsolete  
**Product Category :** PCB Headers and Receptacles



## Documents and Resources

### Drawings

[702871272 sd.pdf](#)  
[PK-70873-0353-001.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)  
[SOLIDWORKS](#)  
[Creo](#)  
[Symbol and Footprint \(Multi-Format\)](#)

### Specifications

[713080001-AS-000.pdf](#)  
[PS-70280-001.pdf](#)

## Product Environment Compliance

### Compliance

|                    |                                                                                                         |
|--------------------|---------------------------------------------------------------------------------------------------------|
| GADSL/IMDS         | Not Relevant                                                                                            |
| China RoHS         |  per SJ/T 11365-2006 |
| EU ELV             | Not Relevant                                                                                            |
| Low-Halogen Status | Low-Halogen per IEC 61249-2-21                                                                          |
| REACH SVHC         | Not Contained per D(2025)7771-DC (04 Feb 2026)                                                          |
| EU RoHS            | Compliant per EU 2015/863                                                                               |

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

### EU RoHS Certificate of Compliance

### Additional Product Compliance Information

---

## Part Details

### General

|                |                                                                                                                                                          |
|----------------|----------------------------------------------------------------------------------------------------------------------------------------------------------|
| Status         | Obsolete                                                                                                                                                 |
| Category       | PCB Headers and Receptacles                                                                                                                              |
| Series         | 70287                                                                                                                                                    |
| Description    | 2.54mm Pitch C-Grid Header, Breakaway, Dual Row, Vertical, with Retention Pin, 58 Circuits, 8.13mm Mating Pin Length, 0.76µm Gold (Au) Selective Plating |
| Application    | Board-to-Board, Signal, Wire-to-Board                                                                                                                    |
| Component Type | PCB Header                                                                                                                                               |
| Product Name   | C-Grid                                                                                                                                                   |
| UPC            | 822350868143                                                                                                                                             |

### Agency

|     |         |
|-----|---------|
| CSA | LR19980 |
| UL  | E29179  |

### Electrical

|                               |      |
|-------------------------------|------|
| Current - Maximum per Contact | 3.0A |
|-------------------------------|------|

|                   |         |
|-------------------|---------|
| Voltage - Maximum | 250V DC |
|-------------------|---------|

## Physical

|                                |                                |
|--------------------------------|--------------------------------|
| Breakaway                      | Yes                            |
| Circuits (Loaded)              | 58                             |
| Circuits (maximum)             | 58                             |
| Color - Resin                  | Black                          |
| Durability (mating cycles max) | 25                             |
| First Mate / Last Break        | No                             |
| Glow-Wire Capable              | No                             |
| Guide to Mating Part           | No                             |
| Keying to Mating Part          | N/A                            |
| Lock to Mating Part            | None                           |
| Material - Metal               | Brass                          |
| Material - Plating Mating      | Gold                           |
| Material - Plating Termination | Tin                            |
| Material - Resin               | High Temperature Thermoplastic |
| Net Weight                     | 4.877/g                        |
| Number of Rows                 | 2                              |
| Orientation                    | Vertical                       |
| Packaging Type                 | Bag                            |
| PCB Locator                    | No                             |
| PCB Retention                  | None                           |
| PCB Thickness - Recommended    | 1.57mm                         |
| PC Tail Length                 | 3.18mm                         |
| Pitch - Mating Interface       | 2.54mm                         |
| Pitch - Termination Interface  | 2.54mm                         |
| Plating min - Mating           | 0.813µm                        |
| Plating min - Termination      | 2.032µm                        |
| Polarized to Mating Part       | No                             |
| Polarized to PCB               | No                             |
| Shrouded                       | No                             |
| Stackable                      | Yes                            |
| Temperature Range - Operating  | -40° to +120°C                 |
| Termination Interface Style    | Through Hole                   |

## Solder Process Data

|                              |      |
|------------------------------|------|
| Max-Duration                 | 5    |
| Lead-Free Process Capability | WAVE |
| Max-Cycle                    | 1    |
| Max-Temp                     | 260  |

---

## Mates With / Use With

### Mates with Part(s)

| Description                                                           | Part Number  |
|-----------------------------------------------------------------------|--------------|
| C-Grid Right-Angle, Dual Row, Surface Mount PCB Receptacles           | <u>71979</u> |
| C-Grid Vertical, Dual Row, High Profile, Surface Mount PCB Connectors | <u>71395</u> |
| C-Grid Vertical, Dual Row, High Profile, Through Hole PCB Receptacles | <u>71850</u> |
| 2.54mm Pitch C-Grid Shunt Terminal Housings                           | <u>7859</u>  |

---

This document was generated on Feb 26, 2026