



Part Number : [731343862](#)

Product Description : DIN 7/16 Jack, Straight, Clamp, 1-1/4" Annular Corrugated, IP68, One Piece Per Carton, 50 Ohms

Series Number : 73134

Status : Active

Product Category : RF / Coaxial Connectors



Documents and Resources

Drawings

[731343862_sd.pdf](#)

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

[Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

[Industry Documents](#)

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

[Substances of Interest](#)

- PFAS

[EU RoHS Certificate of Compliance](#)

[Additional Product Compliance Information](#)

Part Details

General

Status	Active
Category	RF / Coaxial Connectors
Series	73134
Description	DIN 7/16 Jack, Straight, Clamp, 1-1/4" Annular Corrugated, IP68, One Piece Per Carton, 50 Ohms
Application	Telecommunications/Networking, RF
Product Name	7/16 DIN
Style	Cable
Type	Large
UPC	191128975490

Electrical

Frequency	3 GHz
Impedance	50Ω
Power / Voltage	VOLTAGE: 2700 Vrms@Sea Level

Physical

Cable Attachment	Clamp
Gender	Jack
Keying to Mating Part	N/A
Orientation	Straight
Packaging Type	Individual Carton
Panel Mount	No
Panel Mount Method	N/A
PCB Mounting	N/A
Reverse Polar	No
Wire/Cable Type	1 1/4" Flexible Coaxial

