



Part Number : [731412080](#)

Product Description : N Jack, Straight, Bulkhead
Receptacle, PCB, Through Hole, Brass Body, Nickel (Ni)
Plated, with Jam Nut and Lockwasher, 50 Ohms

Series Number : 73141

Status : Active

Product Category : RF / Coaxial Connectors



Documents and Resources

Drawings

[731412080 sd.pdf](#)

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	RF / Coaxial Connectors
Series	73141
Description	N Jack, Straight, Bulkhead Receptacle, PCB, Through Hole, Brass Body, Nickel (Ni) Plated, with Jam Nut and Lockwasher, 50 Ohms
Application	RF
Product Name	N
Style	PCB
Type	Medium
UPC	884982420656

Electrical

Frequency	11 GHz
Impedance	50Ω
Power / Voltage	VOLTAGE: 1000 Vrms@Sea Level

Physical

Cable Attachment	N/A
Gender	Jack
Keying to Mating Part	N/A
Orientation	Straight
Packaging Type	Tray
Panel Mount	Yes
Panel Mount Method	Bulkhead
PCB Mounting	Through Hole
PCB Thickness - Recommended	4.30mm
Reverse Polar	No

Wire/Cable Type	N/A
-----------------	-----

This document was generated on Feb 27, 2026