

MATERIALS AND FINISHES:

SMA PLUG STR

BODY: BRASS
PLATED GOLD

COUPLING NUT: BRASS
PLATED GOLD

CRIMP TUBE: BRASS
PLATED NICKEL

CENTER CONTACT: BRASS
PLATED GOLD

INSULATOR: TEFLON

C'RING: BERYLLIUM COPPER

SHRINK TUBE VERSAFIT OR EQUIVALENT
CABLE RG316
LABEL SHRINK TUBE BLACK
TEXT AS SHOWN

PACKAGING BY PLASTIC BAG.






TABLE 1:

PS-89675-3460	PRODUCT SPECIFICATION
MIL-STD-348A, FIG, 301.1	INTERFACE
SPECIFICATION	DEACRIPTION

TABLE 2:

73230-5316	39.370±.472	1000.00±12.00
73230-5315	36.000±.472	914.40±12.00
73230-5314	24.000±.315	609.60±8.00
73230-5313	18.000±.236	457.20±6.00
73230-5312	12.000±.157	304.80±4.00
73230-5311	7.874±.118	200.00±3.00
73230-5310	6.000±.079	152.40±2.00
PART NO.	IN	MM
	DIM A	

FUNCTIONAL SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																			
#####		DIMENSION UNITS		SCALE		CURRENT REV DESC: EC NO: 675763 DRWN: WANGR22021/06/24 CHK'D: MYLU072021/08/30 APPR: LCHEN032021/08/30 INITIAL REVISION: DRWN: WANGR22021/06/24 APPR: LCHEN032021/08/30					molex CA SMA PLUG STR TO SMA PLUG STR WITH RG316 CABLE EWR#14558-A										
MM/INCH		3:1																			
GENERAL TOLERANCES (UNLESS SPECIFIED)																					
ANGULAR TOL		±°		PRODUCT CUSTOMER DRAWING																	
4 PLACES		±									DOCUMENT NUMBER		DOC TYPE		DOC PART		REVISION				
3 PLACES		±																			
2 PLACES		±		732305310					PSD		000		A								
1 PLACE		±																			
0 PLACES		±		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS					THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER		
				C-SIZE					73230					SEE TABLE 2		GENERAL MARKET		1 OF 1			