



Part Number : [732306220](#)

Product Description : MCX Right-Angle Plug to I-PEX
MHF I LK Plug on 1.32mm Cable, 304.20mm Length, 50
Ohms

Series Number : 73230

Status : Active

Product Category : RF Cable Assemblies



Documents & Resources

Drawings

[732306220_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)4165-DC (25 June 2025)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

Part Details

General

Status	Active
Category	RF Cable Assemblies
Series	73230
Description	MCX Right-Angle Plug to I-PEX MHF I LK Plug on 1.32mm Cable, 304.20mm Length, 50 Ohms
Application	RF
Assembly Configuration	Dual Ended Connectors
Connector to Connector	MCX-to-I-PEX MHF
Product Name	I-PEX MHF,MCX
Type	RF Cable Assembly
UPC	196823189005

Electrical

Frequency	6 GHz
Impedance	50Ω

Physical

Cable Length	304.20mm
Gender	Plug/Plug
Material - Metal	Brass, Phosphor Bronze
Material - Plating Mating	Gold
Material - Resin	PTFE, Liquid Crystal Polymer
Net Weight	2.500/g
Packaging Type	Bag
Single Ended	No
Wire/Cable Type	1.32mm Coaxial

Mates With / Use With

Mates with Part(s)

Description	Part Number
MCX Plugs and Jacks	<u>73366</u>
MCRF Cable Assemblies	<u>73412</u>