Part Number : 732510420
Product Description : SMA Jack, Straight, 2-Hole Flange Mount, Candlestick Contact, 17.93mm Length, Stainless Steel Body, Passivated, 40 Pieces Per Tray, 50 Ohms
Series Number : 73251
Status : Active
Product Category : RF / Coaxial Connectors



Documents & Resources

Drawings

732510420_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2022)4187-DC (10 June 2022)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	RF / Coaxial Connectors
Series	73251
Description	SMA Jack, Straight, 2-Hole Flange Mount, Candlestick Contact, 17.93mm Length, Stainless Steel Body, Passivated, 40 Pieces Per Tray, 50 Ohms
Application	RF
Product Name	SMA
Style	Panel
Type	Subminiature
UPC	756054714935

Electrical

Frequency	18 GHz
Impedance	50Ω
Power / Voltage	VOLTAGE: 500 Vrms@Sea Level

Physical

Cable Attachment	N/A
Gender	Jack
Keying to Mating Part	N/A
Net Weight	2.260/g
Orientation	Straight

Packaging Type	Tray
Panel Mount	Yes
Panel Mount Method	Flange
PCB Mounting	Round Post
PCB Thickness - Recommended	Various
Reverse Polar	No
Wire/Cable Type	N/A

Solder Process Data

Max-Duration	10
Lead-Free Process Capability	SMC&WAVE
Max-Cycle	2
Max-Temp	260