



Part Number : [732762190](#)

Product Description : N Jack, Right-Angle, Bulkhead Front Mount, Crimp, LMR-100A-FR Cable, Brass Body, Nickel (Ni) Plated, IP68, Tray, 50 Ohms

Series Number : 73276

Status : Active

Product Category : RF / Coaxial Connectors



Documents and Resources

Drawings

[732762190_sd.pdf](#)

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	RF / Coaxial Connectors
Series	73276
Description	N Jack, Right-Angle, Bulkhead Front Mount, Crimp, LMR-100A-FR Cable, Brass Body, Nickel (Ni) Plated, IP68, Tray, 50 Ohms
Application	RF
Product Name	N
Style	Cable
Type	Medium
UPC	884982148970

Electrical

Frequency	11 GHz
Impedance	50Ω
Power / Voltage	VOLTAGE: 1000 Vrms@Sea Level

Physical

Cable Attachment	Crimp
Gender	Jack
Keying to Mating Part	N/A
Orientation	Right Angle
Packaging Type	Tray
Panel Mount	Yes
Panel Mount Method	Bulkhead
PCB Mounting	N/A
Reverse Polar	No
Wire/Cable Type	LMR-100, RG-174, RG-188, RG-316