



Part Number : [732870631](#)

Product Description : 2.92mm Termination, Plug, Straight, 40 GHz, 1 Watt, with Chain

Series Number : 73287

Status : Active

Product Category : RF / Coaxial Connectors



Documents & Resources

Drawings

[732870631_sd.pdf](#)

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Product Environment Compliance

Compliance

| | |
|--------------------|--|
| GADSL/IMDS | Not Relevant |
| China RoHS | Not Reviewed per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Not Reviewed per IEC 61249-2-21 |
| REACH SVHC | Not Reviewed per D(2025)4165-DC (25 June 2025) |
| EU RoHS | Not Reviewed per EU 2015/863 |

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

| | |
|--------------|--|
| Status | Active |
| Category | RF / Coaxial Connectors |
| Series | 73287 |
| Description | 2.92mm Termination, Plug, Straight, 40 GHz, 1 Watt, with Chain |
| Application | RF |
| Keyword | Termination, Terminations |
| Product Name | 2.92mm, Termination |
| Style | Coaxial Termination |
| Type | Subminiature |
| UPC | 198282628705 |

Electrical

| | |
|---------------------------|--------|
| Average Power Max (Watts) | 1 |
| Frequency | 40 GHz |
| Impedance | 50Ω |
| VSWR (max) | 1.20:1 |

Physical

| | |
|-----------------------|------------|
| Body Style | With Chain |
| Cable Attachment | N/A |
| Gender | Plug |
| Keying to Mating Part | N/A |
| Orientation | Straight |
| Packaging Type | Bag |
| Panel Mount | No |
| Panel Mount Method | N/A |
| PCB Mounting | N/A |

| | |
|-----------------|-----|
| Reverse Polar | No |
| Wire/Cable Type | N/A |

This document was generated on Oct 02, 2025