

Datasheet for 76650-0062

General Information

Part Number:	76650-0062
Manufacturer:	Molex / Waldom
Title:	.062" Power Connector Kit
Description:	Free Hanging Plug and Receptacle, 1 Circuit
Product Family:	Standard .062"
Certificates:	(Molex parts within this kit) - EU and China RoHS, UL, CSA and TUV
Country of Origin:	Kit assembled in U.S.A.

Specifications

Design

Configuration:	Wire to Wire
Pitch:	3.68mm (.145 ")
Connector Type:	Plug and Receptacle
Mounting	
Orientation:	Free-hanging
Circuit Sizes:	1
Current Rating:	5 Amps
Voltage:	250 Volts
Wire size:	24-18 AWG

Product Highlights

The Standard .062" is a durable and economical power or signal connector, capable of carrying up to 5.0 amps per circuit. Tough Nylon housings and robust terminal design create a durable, long lasting product. The Standard .062" products are reliable and offer high value in features and price. These products are an excellent choice for power or signal interconnect applications.

Features and Benefits

- Male and female terminals may be used in either plug or receptacle housings
- Free hanging or panel mount housing version available
- Round terminals may be oriented in any direction for fast assembly
- Passive (friction lock)

Applications

- Power Supplies
- Appliances
- Gaming Machines
- Vending Machines
- Refrigerators
- Washing Machines
- Copy Machines

Datasheet for 76650-0062

Bill of Materials for Part No. 76650-0062

Molex Part No.	Country of Origin	Description	Quantity in Kit
02-06-1103	USA	.062" Dia. Female Crimp Terminals, 24-18 AWG	7
02-06-2103	USA	.062" Dia. Crimp Type Male Pin Terminals, 24-18 AWG	7
03-06-1011	USA	1-Circuit Free-hanging Nylon Connector Receptacle	5
03-06-2011	USA	1-Circuit Free-hanging Nylon Connector Plug	5

Recommended Molex Tool(s) for Part No. 76650-0062*

Molex Part No.	Country of Origin	Description
63811-1000 *	Sweden	Hand Crimp Tool
11-03-0002 *	Sweden	Extraction Tool
11-02-0001 *	Sweden	Insertion Tool

*Tools not included in kit. Tools ordered separately.