

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0082268805
Status: Active
Description: 2.54mm Pitch Round Conductor Flat Cable - 26 AWG (7 x 26) Stranded, Topcoat, 5 Circuits, Reel 30.48m Length



Series image - Reference only

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Cable
Series	8996
Crimp Quality Equipment	Yes
Product Name	Ribbon
UPC	884982586604
Physical	
Cable Length	30.48m
Circuits (Loaded)	5
Insulation	PVC
Net Weight	473.835/g
Packaging Type	Reel
Pitch - Termination Interface	2.54mm
Temperature Range - Operating	-20°C to +105°C
Wire Size AWG	26
Wire/Cable Type	(7x26) Stranded, Tinned
Electrical	
Current - Maximum per Contact	N/A
Voltage - Maximum	300V
Solder Process Data	
Lead-freeProcess Capability	N/A
Max. Cycles at Max. Process Temperature	001
Material Info	
Engineering Number	8996-05-100B
Reference - Drawing Numbers	
Sales Drawing	SD-8996-001

EU ELV Not Relevant	
EU RoHS Compliant REACH SVHC Not Contained Per - ED/61/2018 (27 June 2018) Halogen-Free Status Not Low-Halogen Need more information on product environmental compliance? Email productcompliance@molex.com Please visit the Contact Us section for any non-product compliance questions.	China RoHS China ROHS ELV RoHS Phthalates
	Green Image Not Relevant Not Contained

Search Parts in this Series
[8996 Series](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION