

- NOTES:**
- MATERIAL:**
HSG: LCP, GLASS-FILLED, UL94V-0,
COLOR: BLACK
PIN: 0.64MM SQ PIN, COPPER ALLOY
 - PLATING TYPE:**
 - 0.0254 µm GOLD FLASH OVER
1.25 µm MIN. NICKEL OVERALL.
 - 0.025 µm MIN. GOLD PLATE ON CONTACT AND
1.88 µm MIN. TIN ON SOLDERTAIL OVER
1.25 µm MIN. NICKEL OVERALL.
 - 0.25 µm MIN. GOLD PLATE ON CONTACT AND
1.88 µm MIN. TIN ON SOLDERTAIL OVER
1.25 µm MIN. NICKEL OVERALL.
 - 0.38 µm MIN. GOLD PLATE ON CONTACT AND
1.88 µm MIN. TIN ON SOLDERTAIL OVER
1.25 µm MIN. NICKEL OVERALL.
 - 0.75 µm MIN. GOLD PLATE ON CONTACT AND
1.88 µm MIN. TIN ON SOLDERTAIL OVER
1.25 µm MIN. NICKEL OVERALL
 - 2.50 µm MIN. TIN IN SELECTED AREA OVER
1.25 m MIN. NICKEL OVERALL.
 - 0.38 µm MIN. GOLD PLATE ON CONTACT AND
2.50 µm MIN. TIN ON SOLDERTAIL OVER
1.25 µm MIN. NICKEL OVERALL.
 - 0.38 µm MIN. GOLD PLATE ON CONTACT AND
0.05 µm MIN. GOLD FLASH ON SOLDERTAIL OVER
1.25 µm MIN. NICKEL OVERALL.
 - 0.05 - 0.25 µm MIN. GOLD FLASH OVER
1.25 µm MIN. NICKEL OVERALL.
 - PIN PUSHOUT FORCE: 1KG MIN IN EITHER DIRECTION
 - THE ABOVE 14 CKT IS FOR ILLUSTRATION PURPOSE ONLY.
 - FOR PACKAGING OPTION PLEASE REFER TO THE TABLE.
 - RECOMMENDED PCB THICKNESS 1.60MM.
 - PRODUCT SPECIFICATION: PS-87920-019
 - WAFER TO BE FLAT WITHIN 0.003mm/mm
 - IRREGULAR CIRCUIT CUTOFF WITHIN BREAKAWAY SECTION IS PERMISSIBLE. CUTTING OR CHIPPING OF THE MAIN BODY IS NOT ACCEPTABLE.
 - PARTS ARE NOT STACKABLE ON 2.54 CENTER
 - CAP TO BE PLACED AS CENTRAL OF PART AS POSSIBLE WITH THE TOP SURFACE FLAT FOR PICK AND PLACE.
 - PACKAGING SPECIFICATION:**
TRAY: PK-89990-489
BULK: PK-89990-491
TUBE: PK-87914-300



REVISION OF DRAWING MAY BE CHANGED DURING FINAL RELEASED FOR PRODUCTION.

DOCUMENT STATUS	P1	RELEASE DATE	2021/10/11	11:53:31
-----------------	----	--------------	------------	----------

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		CURRENT REV DESC: BRIGHT TIN PHASE OUT		molex	
DIMENSION UNITS	SCALE				
mm	NTS			2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H	
GENERAL TOLERANCES (UNLESS SPECIFIED)				PRODUCT CUSTOMER DRAWING	
		MM	INCH		
4 PLACES	±		±	DOCUMENT NUMBER	
3 PLACES	±		±	DOC TYPE	
2 PLACES	±	0.2	±	DOC PART	
1 PLACE	±		±	REVISION	
0 PLACES	±		±	SD-87914-013	
ANGULAR TOL ± 3.0°				PSD	000
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION	DRAWING	SERIES	SHEET NUMBER
			A3-SIZE	87914	1 OF 45
		EC NO: 679909		2021/06/29	
		DRWN: AKUMAR19		2021/10/11	
		CHK'D: MRAMAKRISHNA		2021/10/11	
		APPR: MRAMAKRISHNA		2021/10/11	
		INITIAL REVISION:			
		DRWN: YLQIAO		2005/01/17	
		APPR: SLOW		2005/01/25	
		MATERIAL NUMBER		CUSTOMER	
		SEE TABLE		GENERAL MARKET	

PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION				
								A	B	F	M	P
87914-0211	-----	-----	-----	-----	2	-----	1	2.54	----	10.92	5.84	2.79
87914-0221	-----	-----	-----	-----	2	-----	1	2.54	----	12.25	7.00	2.96
87914-0231	-----	-----	-----	-----	2	-----	1	2.54	----	13.38	6.09	5.00
87914-0212	-----	-----	-----	-----	2	-----	2	2.54	----	10.92	5.84	2.79
87914-0222	-----	-----	-----	-----	2	-----	2	2.54	----	12.25	7.00	2.96
87914-0232	-----	-----	-----	-----	2	-----	2	2.54	----	13.38	6.09	5.00
87914-0213	-----	-----	-----	-----	2	-----	3	2.54	----	10.92	5.84	2.79
87914-0223	-----	-----	-----	-----	2	-----	3	2.54	----	12.25	7.00	2.96
87914-0233	-----	-----	-----	-----	2	-----	3	2.54	----	13.38	6.09	5.00
87914-0214	-----	-----	-----	-----	2	-----	4	2.54	----	10.92	5.84	2.79
87914-0224	-----	-----	-----	-----	2	-----	4	2.54	----	12.25	7.00	2.96
87914-0234	-----	-----	-----	-----	2	-----	4	2.54	----	13.38	6.09	5.00
87914-0215	-----	-----	-----	-----	2	-----	5	2.54	----	10.92	5.84	2.79
87914-0225	-----	-----	-----	-----	2	-----	5	2.54	----	12.25	7.00	2.96
87914-0235	-----	-----	-----	-----	2	-----	5	2.54	----	13.38	6.09	5.00
87914-0216	-----	-----	-----	-----	2	-----	6	2.54	----	10.92	5.84	2.79
87914-0217	-----	-----	-----	-----	2	-----	6	2.54	----	10.92	5.84	2.79
87914-0226	-----	-----	-----	-----	2	-----	6	2.54	----	12.25	7.00	2.96
87914-0227	-----	-----	-----	-----	2	-----	6	2.54	----	12.25	7.00	2.96
87914-0236	-----	-----	-----	-----	2	-----	6	2.54	----	13.38	6.09	5.00
87914-0204	-----	-----	-----	-----	2	-----	4	2.54	----	11.11	6.10	2.72
87914-0205	-----	-----	-----	-----	2	-----	5	2.54	---	11.11	6.10	2.72
87914-0206	-----	-----	-----	-----	2	-----	6	2.54	---	11.11	6.10	2.72
87914-0207	-----	-----	-----	-----	2	-----	6	2.54	---	11.11	6.10	2.72

(D22)
(D22)
(D22)

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											
DIMENSION UNITS		SCALE		CURRENT REV DESC: BRIGHT TIN PHASE OUT							
mm		NTS									
GENERAL TOLERANCES (UNLESS SPECIFIED)											
		MM		INCH							
4 PLACES		±		±							
3 PLACES		±		±							
2 PLACES		± 0.2		±							
1 PLACE		±		±							
0 PLACES		±		±							
ANGULAR TOL		± 3.0°									
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES		SHEET NUMBER	
						A3-SIZE		87914		2 OF 45	

DOCUMENT STATUS	P1	RELEASE DATE	2021/10/11	11:53:31
-----------------	----	--------------	------------	----------

PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION				
								A	B	F	M	P
87914-0411	-----	-----	-----	-----	4	-----	1	5.08	2.54	10.92	5.84	2.79
87914-0421	-----	-----	-----	-----	4	-----	1	5.08	2.54	12.25	7.00	2.96
87914-0431	-----	-----	-----	-----	4	-----	1	5.08	2.54	13.38	6.09	5.00
87914-0412	-----	-----	-----	-----	4	-----	2	5.08	2.54	10.92	5.84	2.79
87914-0422	-----	-----	-----	-----	4	-----	2	5.08	2.54	12.25	7.00	2.96
87914-0432	-----	-----	-----	-----	4	-----	2	5.08	2.54	13.38	6.09	5.00
87914-0413	-----	-----	-----	-----	4	-----	3	5.08	2.54	10.92	5.84	2.79
87914-0423	-----	-----	-----	-----	4	-----	3	5.08	2.54	12.25	7.00	2.96
87914-0433	-----	-----	-----	-----	4	-----	3	5.08	2.54	13.38	6.09	5.00
87914-0414	-----	-----	-----	-----	4	-----	4	5.08	2.54	10.92	5.84	2.79
87914-0424	-----	-----	-----	-----	4	-----	4	5.08	2.54	12.25	7.00	2.96
87914-0434	-----	-----	-----	-----	4	-----	4	5.08	2.54	13.38	6.09	5.00
87914-0415	-----	-----	-----	-----	4	-----	5	5.08	2.54	10.92	5.84	2.79
87914-0425	-----	-----	-----	-----	4	-----	5	5.08	2.54	12.25	7.00	2.96
87914-0435	-----	-----	-----	-----	4	-----	5	5.08	2.54	13.38	6.09	5.00
87914-0416	-----	-----	-----	-----	4	-----	6	5.08	2.54	10.92	5.84	2.79
87914-0417	-----	-----	-----	-----	4	-----	6	5.08	2.54	10.92	5.84	2.79
87914-0426	-----	-----	-----	-----	4	-----	6	5.08	2.54	12.25	7.00	2.96
87914-0427	-----	-----	-----	-----	4	-----	6	5.08	2.54	12.25	7.00	2.96
87914-0436	-----	-----	-----	-----	4	-----	6	5.08	2.54	13.38	6.09	5.00
87914-0401	-----	-----	-----	-----	4	-----	4	5.08	2.54	13.21	8.13	2.79
87914-0402	-----	-----	-----	-----	4	-----	5	5.08	2.54	13.21	8.13	2.79
87914-0403	-----	-----	-----	-----	4	-----	6	5.08	2.54	13.21	8.13	2.79
87914-0404	-----	-----	-----	-----	4	-----	4	5.08	2.54	11.11	6.10	2.72
87914-0405	-----	-----	-----	-----	4	-----	5	5.08	2.54	11.11	6.10	2.72
87914-0406	-----	-----	-----	-----	4	-----	6	5.08	2.54	11.11	6.10	2.72
87914-0408	-----	-----	-----	-----	4	-----	6	5.08	2.54	11.11	6.10	2.72
-----	-----	-----	87914-0407	-----	4	-----	6	5.08	2.54	17.49	12.60	2.60

(D22)
(D22)
(D22)

<p>THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION</p> <p>CURRENT REV DESC: BRIGHT TIN PHASE OUT</p> <p>molex</p> <p>2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H</p> <p>PRODUCT CUSTOMER DRAWING</p> <p>EC NO: 679909 DRWN: AKUMAR19 2021/06/29 CHK'D: MRAMAKRISHNA 2021/10/11 APPR: MRAMAKRISHNA 2021/10/11</p> <p>INITIAL REVISION: DRWN: YLQIAO 2005/01/17 APPR: SLOW 2005/01/25</p> <p>DOCUMENT NUMBER: SD-87914-013 DOC TYPE: PSD DOC PART: 000 REVISION: D22</p> <p>DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS</p> <p>THIRD ANGLE PROJECTION</p> <p>DRAWING: A3-SIZE SERIES: 87914 MATERIAL NUMBER: SEE TABLE CUSTOMER: GENERAL MARKET SHEET NUMBER: 3 OF 45</p>																																			
<p>4 PLACES ±</p>	<p>3 PLACES ±</p>	<p>2 PLACES ± 0.2</p>	<p>1 PLACE ±</p>	<p>0 PLACES ±</p>	<p>ANGULAR TOL ± 3.0°</p>	<p>GENERAL TOLERANCES (UNLESS SPECIFIED)</p> <table border="1"> <tr> <th></th> <th>MM</th> <th>INCH</th> </tr> <tr> <td>4 PLACES</td> <td>±</td> <td>±</td> </tr> <tr> <td>3 PLACES</td> <td>±</td> <td>±</td> </tr> <tr> <td>2 PLACES</td> <td>± 0.2</td> <td>±</td> </tr> <tr> <td>1 PLACE</td> <td>±</td> <td>±</td> </tr> <tr> <td>0 PLACES</td> <td>±</td> <td>±</td> </tr> </table>		MM	INCH	4 PLACES	±	±	3 PLACES	±	±	2 PLACES	± 0.2	±	1 PLACE	±	±	0 PLACES	±	±	<p>DIMENSION UNITS: mm</p> <p>SCALE: NTS</p>	<p>DOCUMENT STATUS: P1</p> <p>RELEASE DATE: 2021/10/11 11:53:31</p>	<p>9</p>	<p>8</p>	<p>7</p>	<p>6</p>	<p>5</p>	<p>4</p>	<p>3</p>	<p>2</p>	<p>1</p>
	MM	INCH																																	
4 PLACES	±	±																																	
3 PLACES	±	±																																	
2 PLACES	± 0.2	±																																	
1 PLACE	±	±																																	
0 PLACES	±	±																																	

PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION					
								A	B	F	M	P	G
87914-0611	-----	-----	-----	-----	6	-----	1	7.62	5.08	10.92	5.84	2.79	----
87914-0621	-----	-----	-----	-----	6	-----	1	7.62	5.08	12.25	7.00	2.96	----
87914-0631	-----	-----	-----	-----	6	-----	1	7.62	5.08	13.38	6.09	5.00	----
87914-0612	-----	-----	-----	-----	6	-----	2	7.62	5.08	10.92	5.84	2.79	----
87914-0622	-----	-----	-----	-----	6	-----	2	7.62	5.08	12.25	7.00	2.96	----
87914-0632	-----	-----	-----	-----	6	-----	2	7.62	5.08	13.38	6.09	5.00	----
87914-0613	-----	-----	-----	-----	6	-----	3	7.62	5.08	10.92	5.84	2.79	----
87914-0623	-----	-----	-----	-----	6	-----	3	7.62	5.08	12.25	7.00	2.96	----
87914-0633	-----	-----	-----	-----	6	-----	3	7.62	5.08	13.38	6.09	5.00	----
87914-0614	-----	-----	-----	-----	6	-----	4	7.62	5.08	10.92	5.84	2.79	----
87914-0624	-----	-----	-----	-----	6	-----	4	7.62	5.08	12.25	7.00	2.96	----
87914-0634	-----	-----	-----	-----	6	-----	4	7.62	5.08	13.38	6.09	5.00	----
87914-0615	-----	-----	-----	D20 87914-0652	6	-----	5	7.62	5.08	10.92	5.84	2.79	----
87914-0625	-----	-----	-----	-----	6	-----	5	7.62	5.08	12.25	7.00	2.96	----
87914-0635	-----	-----	-----	-----	6	-----	5	7.62	5.08	13.38	6.09	5.00	----
87914-0616	-----	-----	-----	-----	6	-----	6	7.62	5.08	10.92	5.84	2.79	----
87914-0617	-----	-----	-----	-----	6	-----	6	7.62	5.08	10.92	5.84	2.79	----
87914-0626	-----	-----	-----	-----	6	-----	6	7.62	5.08	12.25	7.00	2.96	----
87914-0628	-----	-----	-----	-----	6	-----	6	7.62	5.08	12.25	7.00	2.96	----
87914-0636	-----	-----	-----	-----	6	-----	6	7.62	5.08	13.38	6.09	5.00	----
87914-0601	-----	-----	-----	-----	6	-----	4	7.62	5.08	13.21	8.13	2.79	----
87914-0602	-----	-----	-----	-----	6	-----	5	7.62	5.08	13.21	8.13	2.79	----
87914-0603	-----	-----	-----	-----	6	-----	6	7.62	5.08	13.21	8.13	2.79	----
87914-0604	-----	-----	-----	-----	6	-----	4	7.62	5.08	11.11	6.10	2.72	----
87914-0605	-----	-----	-----	-----	6	-----	5	7.62	5.08	11.11	6.10	2.72	----
87914-0606	-----	-----	-----	-----	6	-----	6	7.62	5.08	11.11	6.10	2.72	----
87914-0608	-----	-----	-----	-----	6	-----	6	7.62	5.08	11.11	6.10	2.72	----



(D22)
(D22)
(D22)

<p>THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION</p> <p>DIMENSION UNITS: mm SCALE: NTS</p> <p>GENERAL TOLERANCES (UNLESS SPECIFIED)</p> <table border="1"> <tr><th></th><th>MM</th><th>INCH</th></tr> <tr><td>4 PLACES</td><td>±</td><td>±</td></tr> <tr><td>3 PLACES</td><td>±</td><td>±</td></tr> <tr><td>2 PLACES</td><td>± 0.2</td><td>±</td></tr> <tr><td>1 PLACE</td><td>±</td><td>±</td></tr> <tr><td>0 PLACES</td><td>±</td><td>±</td></tr> </table> <p>ANGULAR TOL ± 3.0°</p> <p>DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS</p>											MM	INCH	4 PLACES	±	±	3 PLACES	±	±	2 PLACES	± 0.2	±	1 PLACE	±	±	0 PLACES	±	±	<p>CURRENT REV DESC: BRIGHT TIN PHASE OUT</p> <p>molex</p> <p>2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H</p> <p>PRODUCT CUSTOMER DRAWING</p> <p>EC NO: 679909 DRWN: AKUMAR19 2021/06/29 CHK'D: MRAMAKRISHNA 2021/10/11 APPR: MRAMAKRISHNA 2021/10/11</p> <p>INITIAL REVISION: DRWN: YLQIAO 2005/01/17 APPR: SCLOW 2005/01/25</p> <p>DOCUMENT NUMBER: SD-87914-013 DOC TYPE: PSD DOC PART: 000 REVISION: D22</p> <p>MATERIAL NUMBER: SEE TABLE CUSTOMER: GENERAL MARKET SHEET NUMBER: 4 OF 45</p>									
	MM	INCH																																			
4 PLACES	±	±																																			
3 PLACES	±	±																																			
2 PLACES	± 0.2	±																																			
1 PLACE	±	±																																			
0 PLACES	±	±																																			

DOCUMENT STATUS	P1	RELEASE DATE	2021/10/11	11:53:31
-----------------	----	--------------	------------	----------



PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION					
								A	B	F	M	P	G
87914-0807	-----	-----	-----	-----	8	-----	6	10.16	7.62	21.75	16.51	2.95	----
87914-0818	-----	-----	-----	-----	8	-----	6	10.16	7.62	21.75	16.51	2.95	----
87914-0108	-----	-----	-----	-----	8	-----	6	10.16	7.62	16.50	11.11	3.10	----
87914-0811	-----	-----	-----	-----	8	-----	1	10.16	7.62	10.92	5.84	2.79	----
87914-0821	-----	-----	-----	-----	8	-----	1	10.16	7.62	12.25	7.00	2.96	----
87914-0831	-----	-----	-----	-----	8	-----	1	10.16	7.62	13.38	6.09	5.00	----
87914-0812	-----	-----	-----	-----	8	-----	2	10.16	7.62	10.92	5.84	2.79	----
87914-0822	-----	-----	-----	-----	8	-----	2	10.16	7.62	12.25	7.00	2.96	----
87914-0832	-----	-----	-----	-----	8	-----	2	10.16	7.62	13.38	6.09	5.00	----
87914-0813	-----	-----	-----	-----	8	-----	3	10.16	7.62	10.92	5.84	2.79	----
87914-0823	-----	-----	-----	-----	8	-----	3	10.16	7.62	12.25	7.00	2.96	----
87914-0833	-----	-----	-----	-----	8	-----	4	10.16	7.62	13.38	6.09	5.00	----
87914-0814	-----	-----	-----	-----	8	-----	4	10.16	7.62	10.92	5.84	2.79	----
87914-0824	-----	-----	-----	-----	8	-----	4	10.16	7.62	12.25	7.00	2.96	----
87914-0834	-----	-----	-----	-----	8	-----	4	10.16	7.62	13.38	6.09	5.00	----
87914-0815	-----	-----	-----	-----	8	-----	5	10.16	7.62	10.92	5.84	2.79	----
87914-0825	-----	-----	-----	-----	8	-----	5	10.16	7.62	12.25	7.00	2.96	----
87914-0835	-----	-----	-----	-----	8	-----	5	10.16	7.62	13.38	6.09	5.00	----
87914-0816	-----	-----	-----	-----	8	-----	6	10.16	7.62	10.92	5.84	2.79	----
87914-0819	-----	-----	-----	-----	8	-----	6	10.16	7.62	10.92	5.84	2.79	----
87914-0826	-----	-----	-----	-----	8	-----	6	10.16	7.62	12.25	7.00	2.96	----
87914-0828	-----	-----	-----	-----	8	-----	6	10.16	7.62	12.25	7.00	2.96	----
87914-0836	-----	-----	-----	-----	8	-----	6	10.16	7.62	13.38	6.09	5.00	----
87914-0801	-----	-----	-----	-----	8	-----	4	10.16	7.62	13.21	8.13	2.79	----
87914-0802	-----	-----	-----	-----	8	-----	5	10.16	7.62	13.21	8.13	2.79	----
87914-0803	-----	-----	-----	-----	8	-----	6	10.16	7.62	13.21	8.13	2.79	----
87914-0809	-----	-----	-----	-----	8	-----	6	10.16	7.62	13.21	8.13	2.79	----
87914-0804	-----	-----	-----	-----	8	-----	4	10.16	7.62	11.11	6.10	2.72	----
87914-0805	-----	-----	-----	-----	8	-----	5	10.16	7.62	11.11	6.10	2.72	----
87914-0806	-----	-----	-----	-----	8	-----	6	10.16	7.62	11.11	6.10	2.72	----
87914-0810	-----	-----	-----	-----	8	-----	6	10.16	7.62	11.11	6.10	2.72	----

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

DIMENSION UNITS	SCALE	CURRENT REV DESC: BRIGHT TIN PHASE OUT	
mm	NTS		
GENERAL TOLERANCES (UNLESS SPECIFIED)			
	MM	INCH	EC NO: 679909 DRWN: AKUMAR19 2021/06/29 CHK'D: MRAMAKRISHNA 2021/10/11 APPR: MRAMAKRISHNA 2021/10/11 INITIAL REVISION: DRWN: YLQIAO 2005/01/17 APPR: SCLOW 2005/01/25
4 PLACES	±	±	
3 PLACES	±	±	
2 PLACES	± 0.2	±	
1 PLACE	±	±	
0 PLACES	±	±	DOCUMENT NUMBER SD-87914-013
ANGULAR TOL	± 3.0°		DOC TYPE PSD
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION 	DRAWING A3-SIZE
		SERIES 87914	DOC PART 000
		MATERIAL NUMBER SEE TABLE	CUSTOMER GENERAL MARKET
		SHEET NUMBER 6 OF 45	REVISION D22

F	10	9	8	7	6	5	4	3	2	1					
	PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	PART NO. FOR BULK PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION					
									A	B	F	M	P	G	
87914-0001	-----	-----	-----	-----	-----	-----	10	-----	4	12.70	10.16	12.07	5.97	3.81	----
87914-1011	-----	-----	-----	-----	-----	-----	10	-----	1	12.70	10.16	10.92	5.84	2.79	----
87914-1021	-----	-----	-----	-----	-----	-----	10	-----	1	12.70	10.16	12.25	7.00	2.96	----
87914-1031	-----	-----	-----	-----	-----	-----	10	-----	1	12.70	10.16	13.38	6.09	5.00	----
87914-1012	-----	-----	-----	-----	-----	-----	10	-----	2	12.70	10.16	10.92	5.84	2.79	----
87914-1022	-----	-----	-----	-----	-----	-----	10	-----	2	12.70	10.16	12.25	7.00	2.96	----
87914-1032	-----	-----	-----	-----	-----	-----	10	-----	2	12.70	10.16	13.38	6.09	5.00	----
87914-1013	-----	-----	-----	-----	-----	-----	10	-----	3	12.70	10.16	10.92	5.84	2.79	----
87914-1023	-----	-----	-----	-----	-----	-----	10	-----	3	12.70	10.16	12.25	7.00	2.96	----
87914-1033	-----	-----	-----	-----	-----	-----	10	-----	3	12.70	10.16	13.38	6.09	5.00	----
87914-1014	-----	-----	-----	-----	-----	-----	10	-----	4	12.70	10.16	10.92	5.84	2.79	----
87914-1024	-----	-----	-----	-----	-----	-----	10	-----	4	12.70	10.16	12.25	7.00	2.96	----
87914-1034	-----	-----	-----	-----	-----	-----	10	-----	4	12.70	10.16	13.38	6.09	5.00	----
87914-1015	-----	-----	-----	-----	-----	-----	10	-----	5	12.70	10.16	10.92	5.84	2.79	----
87914-1025	-----	-----	-----	-----	-----	-----	10	-----	5	12.70	10.16	12.25	7.00	2.96	----
87914-1035	-----	-----	-----	-----	-----	-----	10	-----	5	12.70	10.16	13.38	6.09	5.00	----
87914-1016	-----	-----	-----	-----	-----	-----	10	-----	6	12.70	10.16	10.92	5.84	2.79	----
87914-1018	-----	-----	-----	-----	-----	-----	10	-----	6	12.70	10.16	10.92	5.84	2.79	----
87914-1026	-----	-----	-----	-----	-----	-----	10	-----	6	12.70	10.16	12.25	7.00	2.96	----
87914-1027	-----	-----	-----	-----	-----	-----	10	-----	6	12.70	10.16	12.25	7.00	2.96	----
87914-1036	-----	-----	-----	-----	-----	-----	10	-----	6	12.70	10.16	13.38	6.09	5.00	----
-----	-----	-----	-----	-----	87914-1037	-----	10	9	4	12.70	10.16	10.92	5.84	2.79	----
87914-1001	-----	-----	-----	-----	-----	-----	10	-----	-----	12.70	10.16	13.21	8.13	2.79	---
87914-1002	-----	-----	-----	-----	-----	-----	10	-----	-----	12.70	10.16	13.21	8.13	2.79	---
87914-1003	-----	-----	-----	-----	-----	-----	10	-----	-----	12.70	10.16	13.21	8.13	2.79	---
87914-1007	-----	-----	-----	-----	-----	-----	10	-----	-----	12.70	10.16	13.21	8.13	2.79	---
87914-1004	-----	-----	-----	-----	-----	-----	10	-----	-----	12.70	10.16	13.21	6.10	2.72	---
87914-1005	-----	-----	-----	-----	-----	-----	10	-----	-----	12.70	10.16	13.21	6.10	2.72	---
87914-1006	-----	-----	-----	-----	-----	-----	10	-----	-----	12.70	10.16	13.21	6.10	2.72	---
87914-1008	-----	-----	-----	-----	-----	-----	10	-----	-----	12.70	10.16	13.21	6.10	2.72	---

(D22)
(D22)
(D22)
(D22)
(D22)

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											
DIMENSION UNITS		SCALE		CURRENT REV DESC: BRIGHT TIN PHASE OUT							
mm		NTS									
GENERAL TOLERANCES (UNLESS SPECIFIED)											
		MM		INCH							
4 PLACES		±		±							
3 PLACES		±		±							
2 PLACES		± 0.2		±							
1 PLACE		±		±							
0 PLACES		±		±							
ANGULAR TOL		± 3.0°									
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES		SHEET NUMBER	
						A3-SIZE		87914		8 OF 45	

DOCUMENT STATUS | P1 | RELEASE DATE | 2021/10/11 11:53:31



PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION				
								A	B	F	M	P
87914-1211	-----	-----	-----	-----	12	-----	1	15.24	12.70	10.92	5.84	2.79
-----	87914-1291	-----	-----	-----	12	-----	9	15.24	12.70	10.92	5.84	2.79
87914-1221	-----	-----	-----	-----	12	-----	1	15.24	12.70	12.25	7.00	2.96
87914-1231	-----	-----	-----	-----	12	-----	1	15.24	12.70	13.38	6.09	5.00
87914-1212	-----	-----	-----	-----	12	-----	2	15.24	12.70	10.92	5.84	2.79
87914-1222	-----	-----	-----	-----	12	-----	2	15.24	12.70	12.25	7.00	2.96
87914-1232	-----	-----	-----	-----	12	-----	2	15.24	12.70	13.38	6.09	5.00
87914-1213	-----	-----	-----	-----	12	-----	3	15.24	12.70	10.92	5.84	2.79
87914-1223	-----	-----	-----	-----	12	-----	3	15.24	12.70	12.25	7.00	2.96
87914-1233	-----	-----	-----	-----	12	-----	3	15.24	12.70	13.38	6.09	5.00
87914-1214	-----	-----	-----	-----	12	-----	4	15.24	12.70	10.92	5.84	2.79
87914-1224	-----	-----	-----	-----	12	-----	4	15.24	12.70	12.25	7.00	2.96
87914-1234	-----	-----	-----	-----	12	-----	4	15.24	12.70	13.38	6.09	5.00
87914-1215	-----	-----	-----	-----	12	-----	5	15.24	12.70	10.92	5.84	2.79
87914-1225	-----	-----	-----	-----	12	-----	5	15.24	12.70	12.25	7.00	2.96
87914-1235	-----	-----	-----	-----	12	-----	5	15.24	12.70	13.38	6.09	5.00
87914-1216	-----	-----	-----	-----	12	-----	6	15.24	12.70	10.92	5.84	2.79
87914-1218	-----	-----	-----	-----	12	-----	6	15.24	12.70	10.92	5.84	2.79
87914-1226	-----	-----	-----	-----	12	-----	6	15.24	12.70	12.25	7.00	2.96
87914-1228	-----	-----	-----	-----	12	-----	6	15.24	12.70	12.25	7.00	2.96
87914-1236	-----	-----	-----	-----	12	-----	6	15.24	12.70	13.38	6.09	5.00
87914-1246	-----	-----	-----	-----	12	-----	5	15.24	12.70	29.26	23.32	3.65
87914-1247	-----	-----	-----	-----	12	-----	5	15.24	12.70	29.26	23.32	3.65

(D22)
(D22)
(D22)

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											
DIMENSION UNITS		SCALE		CURRENT REV DESC: BRIGHT TIN PHASE OUT						molex	
mm		NTS									
GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 679909		DRWN: AKUMAR19		2021/06/29		2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H	
				CHK'D: MRAMAKRISHNA		2021/10/11				PRODUCT CUSTOMER DRAWING	
				APPR: MRAMAKRISHNA		2021/10/11				DOCUMENT NUMBER	
4 PLACES ±				INITIAL REVISION:		DRWN: YLQIAO		2005/01/17		SD-87914-013	
3 PLACES ±				DRWN: YLQIAO		2005/01/25		APPR: SLOW		DOC TYPE DOC PART REVISION	
2 PLACES ± 0.2				ANGULAR TOL ± 3.0°						PSD 000 D22	
1 PLACE ±				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION		DRAWING		SERIES	
0 PLACES ±								A3-SIZE		87914	
DOCUMENT STATUS				P1		RELEASE DATE		2021/10/11 11:53:31		MATERIAL NUMBER	
								SEE TABLE		CUSTOMER	
								GENERAL MARKET		SHEET NUMBER	
										9 OF 45	

PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION				
								A	B	F	M	P
87914-1251	-----	-----	-----	-----	12	-----	1	15.24	12.70	18.40	13.08	3.03
87914-1252	-----	-----	-----	-----	12	-----	2	15.24	12.70	18.40	13.08	3.03
87914-1253	-----	-----	-----	-----	12	-----	3	15.24	12.70	18.40	13.08	3.03
87914-1254	-----	-----	-----	-----	12	-----	4	15.24	12.70	18.40	13.08	3.03
87914-1255	-----	-----	-----	-----	12	-----	5	15.24	12.70	18.40	13.08	3.03
87914-1256	-----	-----	-----	-----	12	-----	6	15.24	12.70	18.40	13.08	3.03
87914-1241	-----	-----	-----	-----	12	-----	1	15.24	12.70	12.50	6.95	3.26
87914-1242	-----	-----	-----	-----	12	-----	2	15.24	12.70	12.50	6.95	3.26
87914-1243	-----	-----	-----	-----	12	-----	3	15.24	12.70	12.50	6.95	3.26
87914-1244	-----	-----	-----	-----	12	-----	4	15.24	12.70	12.50	6.95	3.26
87914-1245	-----	-----	-----	-----	12	-----	5	15.24	12.70	12.50	6.95	3.26
87914-1201	-----	-----	-----	-----	12	-----	4	15.24	12.70	13.21	8.13	2.79
87914-1202	-----	-----	-----	-----	12	-----	5	15.24	12.70	13.21	8.13	2.79
87914-1203	-----	-----	-----	-----	12	-----	6	15.24	12.70	13.21	8.13	2.79
87914-1204	-----	-----	-----	-----	12	-----	4	15.24	12.70	11.11	6.10	2.72
87914-1205	-----	-----	-----	-----	12	-----	5	15.24	12.70	11.11	6.10	2.72
87914-1206	-----	-----	-----	-----	12	-----	6	15.24	12.70	11.11	6.10	2.72
87914-1207	-----	-----	-----	-----	12	-----	6	15.24	12.70	11.11	6.10	2.72

D22

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											
DIMENSION UNITS		SCALE		CURRENT REV DESC: BRIGHT TIN PHASE OUT							
mm		NTS									
GENERAL TOLERANCES (UNLESS SPECIFIED)											
		MM		INCH							
4 PLACES	±		±			EC NO: 679909					
3 PLACES	±		±			DRWN: AKUMAR19		2021/06/29			
2 PLACES	±	0.2	±			CHK'D: MRAMAKRISHNA		2021/10/11			
1 PLACE	±		±			APPR: MRAMAKRISHNA		2021/10/11			
0 PLACES	±		±			INITIAL REVISION:					
		ANGULAR TOL		± 3.0°		DRWN: YLQIAO		2005/01/17		DOCUMENT NUMBER	
						APPR: SLOW		2005/01/25		SD-87914-013	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER	
				A3-SIZE		87914		SEE TABLE		GENERAL MARKET	
										SHEET NUMBER	
										10 OF 45	



DOCUMENT STATUS	P1	RELEASE DATE	2021/10/11	11:53:31
-----------------	----	--------------	------------	----------

PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION				
								A	B	F	M	P
87914-1411	-----	-----	-----	-----	14	-----	1	17.78	15.24	10.92	5.84	2.79
87914-1421	-----	-----	-----	-----	14	-----	1	17.78	15.24	12.25	7.00	2.96
87914-1431	-----	-----	-----	-----	14	-----	1	17.78	15.24	13.38	6.09	5.00
87914-1412	-----	-----	-----	-----	14	-----	2	17.78	15.24	10.92	5.84	2.79
87914-1422	-----	-----	-----	-----	14	-----	2	17.78	15.24	12.25	7.00	2.96
87914-1432	-----	-----	-----	-----	14	-----	2	17.78	15.24	13.38	6.09	5.00
87914-1413	-----	-----	-----	-----	14	-----	3	17.78	15.24	10.92	5.84	2.79
87914-1423	-----	-----	-----	-----	14	-----	3	17.78	15.24	12.25	7.00	2.96
87914-1433	-----	-----	-----	-----	14	-----	3	17.78	15.24	13.38	6.09	5.00
87914-1414	-----	-----	-----	-----	14	-----	4	17.78	15.24	10.92	5.84	2.79
87914-1424	-----	-----	-----	-----	14	-----	4	17.78	15.24	12.25	7.00	2.96
87914-1434	-----	-----	-----	-----	14	-----	4	17.78	15.24	13.38	6.09	5.00
87914-1415	-----	-----	-----	-----	14	-----	5	17.78	15.24	10.92	5.84	2.79
87914-1425	-----	-----	-----	-----	14	-----	5	17.78	15.24	12.25	7.00	2.96
87914-1435	-----	-----	-----	-----	14	-----	5	17.78	15.24	13.38	6.09	5.00
87914-1416	-----	-----	-----	-----	14	-----	6	17.78	15.24	10.92	5.84	2.79
87914-1417	-----	-----	-----	-----	14	-----	6	17.78	15.24	10.92	5.84	2.79
87914-1426	-----	-----	-----	-----	14	-----	6	17.78	15.24	12.25	7.00	2.96
87914-1427	-----	-----	-----	-----	14	-----	6	17.78	15.24	12.25	7.00	2.96
87914-1436	-----	-----	-----	-----	14	-----	6	17.78	15.24	13.38	6.09	5.00
87914-1401	-----	-----	-----	-----	14	-----	4	17.78	15.24	13.21	8.13	2.79
87914-1402	-----	-----	-----	-----	14	-----	5	17.78	15.24	13.21	8.13	2.79
87914-1403	-----	-----	-----	-----	14	-----	6	17.78	15.24	13.21	8.13	2.79
87914-1404	-----	-----	-----	-----	14	-----	4	17.78	15.24	11.11	6.10	2.72
87914-1405	-----	-----	-----	-----	14	-----	5	17.78	15.24	11.11	6.10	2.72
87914-1406	-----	-----	-----	-----	14	-----	6	17.78	15.24	11.11	6.10	2.72
87914-1407	-----	-----	-----	-----	14	-----	6	17.78	15.24	11.11	6.10	2.72
87914-0007	-----	-----	-----	-----	14	-----	5	17.78	15.24	13.42	8.08	3.05

D22



D22

D22

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											
DIMENSION UNITS		SCALE		CURRENT REV DESC: BRIGHT TIN PHASE OUT							
mm		NTS									
GENERAL TOLERANCES (UNLESS SPECIFIED)											
		MM	INCH	EC NO: 679909 DRWN: AKUMAR19 2021/06/29 CHK'D: MRAMAKRISHNA 2021/10/11 APPR: MRAMAKRISHNA 2021/10/11 INITIAL REVISION: DRWN: YLQIAO 2005/01/17 APPR: SCLOW 2005/01/25							
4 PLACES	±		±								
3 PLACES	±		±								
2 PLACES	±	0.2	±								
1 PLACE	±		±								
0 PLACES	±		±	ANGULAR TOL ± 3.0°		DOCUMENT NUMBER SD-87914-013		DOC TYPE PSD	DOC PART 000	REVISION D22	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION	DRAWING	SERIES	MATERIAL NUMBER	CUSTOMER	SHEET NUMBER		
					A3-SIZE	87914	SEE TABLE	GENERAL MARKET	11 OF 45		

F	10	9	8	7	6	5	4	3	2	1			
	PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION				
									A	B	F	M	P
	87914-1611	-----	-----	-----	-----	16	-----	1	20.32	17.78	10.92	5.84	2.79
	87914-1621	-----	-----	-----	-----	16	-----	1	20.32	17.78	12.25	7.00	2.96
	87914-1631	-----	-----	-----	-----	16	-----	1	20.32	17.78	13.38	6.09	5.00
	87914-1612	-----	-----	-----	-----	16	-----	2	20.32	17.78	10.92	5.84	2.79
	87914-1622	-----	-----	-----	-----	16	-----	2	20.32	17.78	12.25	7.00	2.96
	87914-1632	-----	-----	-----	-----	16	-----	2	20.32	17.78	13.38	6.09	5.00
	87914-1613	-----	-----	-----	-----	16	-----	3	20.32	17.78	10.92	5.84	2.79
	87914-1623	-----	-----	-----	-----	16	-----	3	20.32	17.78	12.25	7.00	2.96
	87914-1633	-----	-----	-----	-----	16	-----	3	20.32	17.78	13.38	6.09	5.00
E	87914-1614	-----	-----	-----	-----	16	-----	4	20.32	17.78	10.92	5.84	2.79
	87914-1624	-----	-----	-----	-----	16	-----	4	20.32	17.78	12.25	7.00	2.96
	87914-1634	-----	-----	-----	-----	16	-----	4	20.32	17.78	13.38	6.09	5.00
	87914-1615	-----	-----	-----	-----	16	-----	5	20.32	17.78	10.92	5.84	2.79
	87914-1625	-----	-----	-----	-----	16	-----	5	20.32	17.78	12.25	7.00	2.96
	87914-1635	-----	-----	-----	-----	16	-----	5	20.32	17.78	13.38	6.09	5.00
	87914-1616	-----	-----	-----	-----	16	-----	6	20.32	17.78	10.92	5.84	2.79
	87914-1617	-----	-----	-----	-----	16	-----	6	20.32	17.78	10.92	5.84	2.79
	87914-1626	-----	-----	-----	-----	16	-----	6	20.32	17.78	12.25	7.00	2.96
	87914-1627	-----	-----	-----	-----	16	-----	6	20.32	17.78	12.25	7.00	2.96
D	87914-1636	-----	-----	-----	-----	16	-----	6	20.32	17.78	13.38	6.09	5.00
	87914-1601	-----	-----	-----	-----	16	-----	4	20.32	17.78	13.21	8.13	2.79
	87914-1602	-----	-----	-----	-----	16	-----	5	20.32	17.78	13.21	8.13	2.79
	87914-1603	-----	-----	-----	-----	16	-----	6	20.32	17.78	13.21	8.13	2.79
	87914-1604	-----	-----	-----	-----	16	-----	4	20.32	17.78	11.11	6.10	2.72
	87914-1605	-----	-----	-----	-----	16	-----	5	20.32	17.78	11.11	6.10	2.72
	87914-1606	-----	-----	-----	-----	16	-----	6	20.32	17.78	11.11	6.10	2.72
	87914-1608	-----	-----	-----	-----	16	-----	6	20.32	17.78	11.11	6.10	2.72
	87914-1650	-----	-----	-----	-----	16	-----	5	20.32	17.78	12.49	7.40	2.80
	87914-1600	-----	-----	-----	-----	16	-----	5	20.32	17.78	9.49	4.50	2.70
C	87914-1607	-----	-----	-----	-----	16	-----	5	20.32	17.78	9.49	4.50	2.70
	87914-1637	-----	-----	-----	-----	16	-----	5	20.32	17.78	15.79	10.45	3.05
	87914-1652	-----	-----	-----	-----	16	-----	5	20.32	17.78	25.90	19.81	3.80

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

DIMENSION UNITS	SCALE	CURRENT REV DESC: BRIGHT TIN PHASE OUT		
mm	NTS			
GENERAL TOLERANCES (UNLESS SPECIFIED)				
		MM	INCH	EC NO: 679909 DRWN: AKUMAR19 2021/06/29 CHK'D: MRAMAKRISHNA 2021/10/11 APPR: MRAMAKRISHNA 2021/10/11 INITIAL REVISION: DRWN: YLQIAO 2005/01/17 APPR: SLOW 2005/01/25
4 PLACES	±	±	±	
3 PLACES	±	±	±	
2 PLACES	±	0.2	±	
1 PLACE	±	±	±	
0 PLACES	±	±	±	
ANGULAR TOL	± 3.0°			DOCUMENT NUMBER: SD-87914-013 DOC TYPE: PSD DOC PART: 000 REVISION: D22
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION	DRAWING	SERIES
			A3-SIZE	87914
		MATERIAL NUMBER	CUSTOMER	SHEET NUMBER
		SEE TABLE	GENERAL MARKET	13 OF 45

PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION					
								A	B	F	M	P	G
87914-1811	-----	-----	-----	-----	18	-----	1	22.86	20.32	10.92	5.84	2.79	----
87914-1821	-----	-----	-----	-----	18	-----	1	22.86	20.32	12.25	7.00	2.96	----
87914-1831	-----	-----	-----	-----	18	-----	1	22.86	20.32	13.38	6.09	5.00	----
87914-1812	-----	-----	-----	-----	18	-----	2	22.86	20.32	10.92	5.84	2.79	----
87914-1822	-----	-----	-----	-----	18	-----	2	22.86	20.32	12.25	7.00	2.96	----
87914-1832	-----	-----	-----	-----	18	-----	2	22.86	20.32	13.38	6.09	5.00	----
87914-1813	-----	-----	-----	-----	18	-----	3	22.86	20.32	10.92	5.84	2.79	----
87914-1823	-----	-----	-----	-----	18	-----	3	22.86	20.32	12.25	7.00	2.96	----
87914-1833	-----	-----	-----	-----	18	-----	3	22.86	20.32	13.38	6.09	5.00	----
87914-1814	-----	-----	-----	-----	18	-----	4	22.86	20.32	10.92	5.84	2.79	----
87914-1824	-----	-----	-----	-----	18	-----	4	22.86	20.32	12.25	7.00	2.96	----
87914-1834	-----	-----	-----	-----	18	-----	4	22.86	20.32	13.38	6.09	5.00	----
87914-1815	-----	-----	-----	-----	18	-----	5	22.86	20.32	10.92	5.84	2.79	----
87914-1825	-----	-----	-----	-----	18	-----	5	22.86	20.32	12.25	7.00	2.96	----
87914-1835	-----	-----	-----	-----	18	-----	5	22.86	20.32	13.38	6.09	5.00	----
87914-1816	-----	-----	-----	-----	18	-----	6	22.86	20.32	10.92	5.84	2.79	----
87914-1817	-----	-----	-----	-----	18	-----	6	22.86	20.32	10.92	5.84	2.79	----
87914-1826	-----	-----	-----	-----	18	-----	6	22.86	20.32	12.25	7.00	2.96	----
87914-1827	-----	-----	-----	-----	18	-----	6	22.86	20.32	12.25	7.00	2.96	----
87914-1836	-----	-----	-----	-----	18	-----	6	22.86	20.32	13.38	6.09	5.00	----
87914-1801	-----	-----	-----	-----	18	-----	4	22.86	20.32	13.21	8.13	2.79	---
87914-1802	-----	-----	-----	-----	18	-----	5	22.86	20.32	13.21	8.13	2.79	---
87914-1803	-----	-----	-----	-----	18	-----	6	22.86	20.32	13.21	8.13	2.79	---
87914-1804	-----	-----	-----	-----	18	-----	4	22.86	20.32	11.11	6.10	2.72	---
87914-1805	-----	-----	-----	-----	18	-----	5	22.86	20.32	11.11	6.10	2.72	---
87914-1806	-----	-----	-----	-----	18	-----	6	22.86	20.32	11.11	6.10	2.72	---
87914-1809	-----	-----	-----	-----	18	-----	6	22.86	20.32	11.11	6.10	2.72	---
-----	-----	87914-1807	-----	-----	18	-----	5	22.86	20.32	17.02	11.05	3.68	18.02

D22

D22

D22

<p>THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION</p> <p>CURRENT REV DESC: BRIGHT TIN PHASE OUT</p> <p>molex</p> <p>2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H</p> <p>PRODUCT CUSTOMER DRAWING</p> <p>EC NO: 679909 DRWN: AKUMAR19 2021/06/29 CHK'D: MRAMAKRISHNA 2021/10/11 APPR: MRAMAKRISHNA 2021/10/11</p> <p>INITIAL REVISION: DRWN: YLQIAO 2005/01/17 APPR: SLOW 2005/01/25</p> <p>DOCUMENT NUMBER: SD-87914-013 DOC TYPE: PSD DOC PART: 000 REVISION: D22</p> <p>DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS</p> <p>THIRD ANGLE PROJECTION</p> <p>DRAWING: A3-SIZE SERIES: 87914 MATERIAL NUMBER: SEE TABLE CUSTOMER: GENERAL MARKET SHEET NUMBER: 14 OF 45</p>														
<p>4 PLACES ±</p> <p>3 PLACES ±</p> <p>2 PLACES ± 0.2</p> <p>1 PLACE ±</p> <p>0 PLACES ±</p>	<p>GENERAL TOLERANCES (UNLESS SPECIFIED)</p> <table border="1"> <tr><th>MM</th><th>INCH</th></tr> <tr><td>±</td><td>±</td></tr> <tr><td>±</td><td>±</td></tr> <tr><td>± 0.2</td><td>±</td></tr> <tr><td>±</td><td>±</td></tr> <tr><td>±</td><td>±</td></tr> </table> <p>ANGULAR TOL ± 3.0°</p>	MM	INCH	±	±	±	±	± 0.2	±	±	±	±	±	<p>SCALE: NTS</p> <p>DIMENSION UNITS: mm</p>
MM	INCH													
±	±													
±	±													
± 0.2	±													
±	±													
±	±													
<p>DOCUMENT STATUS</p> <p>P1</p> <p>RELEASE DATE</p> <p>2021/10/11 11:53:31</p>	9	8	7	6	5	4	3	2	1					

PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION				
								A	B	F	M	P
87914-2011	-----	-----	-----	-----	20	-----	1	25.40	22.86	10.92	5.84	2.79
87914-2021	-----	-----	-----	-----	20	-----	1	25.40	22.86	12.25	7.00	2.96
87914-2031	-----	-----	-----	-----	20	-----	1	25.40	22.86	13.38	6.09	5.00
87914-2012	-----	-----	-----	-----	20	-----	2	25.40	22.86	10.92	5.84	2.79
87914-2022	-----	-----	-----	-----	20	-----	2	25.40	22.86	12.25	7.00	2.96
87914-2032	-----	-----	-----	-----	20	-----	2	25.40	22.86	13.38	6.09	5.00
87914-2013	-----	-----	-----	-----	20	-----	3	25.40	22.86	10.92	5.84	2.79
87914-2023	-----	-----	-----	-----	20	-----	3	25.40	22.86	12.25	7.00	2.96
87914-2033	-----	-----	-----	-----	20	-----	3	25.40	22.86	13.38	6.09	5.00
87914-2014	-----	-----	-----	-----	20	-----	4	25.40	22.86	10.92	5.84	2.79
87914-2024	-----	-----	-----	-----	20	-----	4	25.40	22.86	12.25	7.00	2.96
87914-2034	-----	-----	-----	-----	20	-----	4	25.40	22.86	13.38	6.09	5.00
87914-2015	-----	-----	-----	-----	20	-----	5	25.40	22.86	10.92	5.84	2.79
87914-2025	-----	-----	-----	-----	20	-----	5	25.40	22.86	12.25	7.00	2.96
87914-2035	-----	-----	-----	-----	20	-----	5	25.40	22.86	13.38	6.09	5.00
87914-2016	-----	-----	-----	-----	20	-----	6	25.40	22.86	10.92	5.84	2.79
87914-2017	-----	-----	-----	-----	20	-----	6	25.40	22.86	10.92	5.84	2.79
87914-2026	-----	-----	-----	-----	20	-----	6	25.40	22.86	12.25	7.00	2.96
87914-2027	-----	-----	-----	-----	20	-----	6	25.40	22.86	12.25	7.00	2.96
87914-2036	-----	-----	-----	-----	20	-----	6	25.40	22.86	13.38	6.09	5.00
87914-2037	-----	-----	-----	-----	20	-----	6	25.40	22.86	13.38	6.09	5.00
87914-2001	-----	-----	-----	-----	20	-----	4	25.40	22.86	13.21	8.13	2.79
87914-2002	-----	-----	-----	-----	20	-----	5	25.40	22.86	13.21	8.13	2.79
87914-2003	-----	-----	-----	-----	20	-----	6	25.40	22.86	13.21	8.13	2.79
87914-2004	-----	-----	-----	-----	20	-----	4	25.40	22.86	11.11	6.10	2.72
87914-2005	-----	-----	-----	-----	20	-----	5	25.40	22.86	11.11	6.10	2.72
87914-2006	-----	-----	-----	-----	20	-----	6	25.40	22.86	11.11	6.10	2.72
87914-2008	-----	-----	-----	-----	20	-----	6	25.40	22.86	11.11	6.10	2.72
87914-2051	-----	-----	-----	-----	20	-----	6	25.40	22.86	18.29	13.00	3.00
87914-0201	-----	-----	-----	-----	20	-----	5	25.40	22.86	18.84	13.46	3.09
87914-0202	-----	-----	-----	-----	20	-----	5	25.40	22.86	18.84	13.46	3.09

D22

D22

D22

D22



D22

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											
DIMENSION UNITS		SCALE		CURRENT REV DESC: BRIGHT TIN PHASE OUT						molex	
mm		NTS									
GENERAL TOLERANCES (UNLESS SPECIFIED)											
		MM		INCH							
4 PLACES		±		±							
3 PLACES		±		±							
2 PLACES		± 0.2		±							
1 PLACE		±		±							
0 PLACES		±		±							
ANGULAR TOL ± 3.0°											
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES		SHEET NUMBER	
						A3-SIZE		87914		15 OF 45	

DOCUMENT STATUS	P1	RELEASE DATE	2021/10/11	11:53:31
-----------------	----	--------------	------------	----------

PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION				
								A	B	F	M	P
87914-2211	-----	-----	-----	-----	22	-----	1	27.94	25.40	10.92	5.84	2.79
87914-2221	-----	-----	-----	-----	22	-----	1	27.94	25.40	12.25	7.00	2.96
87914-2231	-----	-----	-----	-----	22	-----	1	27.94	25.40	13.38	6.09	5.00
87914-2212	-----	-----	-----	-----	22	-----	2	27.94	25.40	10.92	5.84	2.79
87914-2222	-----	-----	-----	-----	22	-----	2	27.94	25.40	12.25	7.00	2.96
87914-2232	-----	-----	-----	-----	22	-----	2	27.94	25.40	13.38	6.09	5.00
87914-2213	-----	-----	-----	-----	22	-----	3	27.94	25.40	10.92	5.84	2.79
87914-2223	-----	-----	-----	-----	22	-----	3	27.94	25.40	12.25	7.00	2.96
87914-2233	-----	-----	-----	-----	22	-----	3	27.94	25.40	13.38	6.09	5.00
87914-2214	-----	-----	-----	-----	22	-----	4	27.94	25.40	10.92	5.84	2.79
87914-2224	-----	-----	-----	-----	22	-----	4	27.94	25.40	12.25	7.00	2.96
87914-2234	-----	-----	-----	-----	22	-----	4	27.94	25.40	13.38	6.09	5.00
87914-2215	-----	-----	-----	-----	22	-----	5	27.94	25.40	10.92	5.84	2.79
87914-2225	-----	-----	-----	-----	22	-----	5	27.94	25.40	12.25	7.00	2.96
87914-2235	-----	-----	-----	-----	22	-----	5	27.94	25.40	13.38	6.09	5.00
87914-2216	-----	-----	-----	-----	22	-----	6	27.94	25.40	10.92	5.84	2.79
87914-2217	-----	-----	-----	-----	22	-----	6	27.94	25.40	10.92	5.84	2.79
87914-2226	-----	-----	-----	-----	22	-----	6	27.94	25.40	12.25	7.00	2.96
87914-2227	-----	-----	-----	-----	22	-----	6	27.94	25.40	12.25	7.00	2.96
87914-2236	-----	-----	-----	-----	22	-----	6	27.94	25.40	13.38	6.09	5.00
87914-2201	-----	-----	-----	-----	22	-----	4	27.94	25.40	13.21	8.13	2.79
87914-2202	-----	-----	-----	-----	22	-----	5	27.94	25.40	13.21	8.13	2.79
87914-2203	-----	-----	-----	-----	22	-----	6	27.94	25.40	13.21	8.13	2.79
87914-2204	-----	-----	-----	-----	22	-----	4	27.94	25.40	11.11	6.10	2.72
87914-2205	-----	-----	-----	-----	22	-----	5	27.94	25.40	11.11	6.10	2.72
87914-2206	-----	-----	-----	-----	22	-----	6	27.94	25.40	11.11	6.10	2.72
87914-2207	-----	-----	-----	-----	22	-----	6	27.94	25.40	11.11	6.10	2.72

(D22)
(D22)
(D22)

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											
DIMENSION UNITS		SCALE		CURRENT REV DESC: BRIGHT TIN PHASE OUT							
mm		NTS									
GENERAL TOLERANCES (UNLESS SPECIFIED)											
		MM		INCH		EC NO: 679909 DRWN: AKUMAR19 2021/06/29 CHK'D: MRAMAKRISHNA 2021/10/11 APPR: MRAMAKRISHNA 2021/10/11 INITIAL REVISION: DRWN: YLQIAO 2005/01/17 APPR: SCLOW 2005/01/25					
4 PLACES		±		±							
3 PLACES		±		±							
2 PLACES		± 0.2		±							
1 PLACE		±		±							
0 PLACES		±		±		DOCUMENT NUMBER		DOC TYPE		DOC PART	
ANGULAR TOL		± 3.0°				SD-87914-013		PSD		000 D22	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES		SHEET NUMBER	
						A3-SIZE		87914		16 OF 45	

DOCUMENT STATUS	P1	RELEASE DATE	2021/10/11	11:53:31
-----------------	----	--------------	------------	----------

PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION				
								A	B	F	M	P
87914-2411	-----	-----	-----	-----	24	-----	1	30.48	27.94	10.92	5.84	2.79
87914-2421	-----	-----	-----	-----	24	-----	1	30.48	27.94	12.25	7.00	2.96
87914-2431	-----	-----	-----	-----	24	-----	1	30.48	27.94	13.38	6.09	5.00
87914-2412	-----	-----	-----	-----	24	-----	2	30.48	27.94	10.92	5.84	2.79
87914-2422	-----	-----	-----	-----	24	-----	2	30.48	27.94	12.25	7.00	2.96
87914-2432	-----	-----	-----	-----	24	-----	2	30.48	27.94	13.38	6.09	5.00
87914-2413	-----	-----	-----	-----	24	-----	3	30.48	27.94	10.92	5.84	2.79
87914-2423	-----	-----	-----	-----	24	-----	3	30.48	27.94	12.25	7.00	2.96
87914-2433	-----	-----	-----	-----	24	-----	3	30.48	27.94	13.38	6.09	5.00
87914-2414	-----	-----	-----	-----	24	-----	4	30.48	27.94	10.92	5.84	2.79
87914-2424	-----	-----	-----	-----	24	-----	4	30.48	27.94	12.25	7.00	2.96
87914-2434	-----	-----	-----	-----	24	-----	4	30.48	27.94	13.38	6.09	5.00
87914-2415	-----	-----	-----	-----	24	-----	5	30.48	27.94	10.92	5.84	2.79
87914-2425	-----	-----	-----	-----	24	-----	5	30.48	27.94	12.25	7.00	2.96
87914-2435	-----	-----	-----	-----	24	-----	5	30.48	27.94	13.38	6.09	5.00
87914-2416	-----	-----	-----	-----	24	-----	6	30.48	27.94	10.92	5.84	2.79
87914-2417	-----	-----	-----	-----	24	-----	6	30.48	27.94	10.92	5.84	2.79
87914-2426	-----	-----	-----	-----	24	-----	6	30.48	27.94	12.25	7.00	2.96
87914-2427	-----	-----	-----	-----	24	-----	6	30.48	27.94	12.25	7.00	2.96
87914-2436	-----	-----	-----	-----	24	-----	6	30.48	27.94	13.38	6.09	5.00
87914-2401	-----	-----	-----	-----	24	-----	4	30.48	27.94	13.21	8.13	2.79
87914-2402	-----	-----	-----	-----	24	-----	5	30.48	27.94	13.21	8.13	2.79
87914-2403	-----	-----	-----	-----	24	-----	6	30.48	27.94	13.21	8.13	2.79
87914-2404	-----	-----	-----	-----	24	-----	4	30.48	27.94	11.11	6.10	2.72
87914-2405	-----	-----	-----	-----	24	-----	5	30.48	27.94	11.11	6.10	2.72
87914-2406	-----	-----	-----	-----	24	-----	6	30.48	27.94	11.11	6.10	2.72
87914-2407	-----	-----	-----	-----	24	-----	6	30.48	27.94	11.11	6.10	2.72


(D22)
(D22)
(D22)

<p>THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION</p> <p>DIMENSION UNITS: mm SCALE: NTS</p> <p>GENERAL TOLERANCES (UNLESS SPECIFIED)</p> <table border="1"> <thead> <tr> <th></th> <th>MM</th> <th>INCH</th> </tr> </thead> <tbody> <tr><td>4 PLACES</td><td>±</td><td>±</td></tr> <tr><td>3 PLACES</td><td>±</td><td>±</td></tr> <tr><td>2 PLACES</td><td>± 0.2</td><td>±</td></tr> <tr><td>1 PLACE</td><td>±</td><td>±</td></tr> <tr><td>0 PLACES</td><td>±</td><td>±</td></tr> </tbody> </table> <p>ANGULAR TOL ± 3.0°</p> <p>DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS</p>											MM	INCH	4 PLACES	±	±	3 PLACES	±	±	2 PLACES	± 0.2	±	1 PLACE	±	±	0 PLACES	±	±	<p>CURRENT REV DESC: BRIGHT TIN PHASE OUT</p> <p>molex</p> <p>2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H</p> <p>PRODUCT CUSTOMER DRAWING</p> <p>EC NO: 679909 DRWN: AKUMAR19 2021/06/29 CHK'D: MRAMAKRISHNA 2021/10/11 APPR: MRAMAKRISHNA 2021/10/11</p> <p>INITIAL REVISION: DRWN: YLQIAO 2005/01/17 APPR: SCLOW 2005/01/25</p> <p>DOCUMENT NUMBER: SD-87914-013 DOC TYPE: PSD DOC PART: 000 REVISION: D22</p> <p>DRAFTING: A3-SIZE SERIES: 87914 MATERIAL NUMBER: SEE TABLE CUSTOMER: GENERAL MARKET SHEET NUMBER: 17 OF 45</p>									
	MM	INCH																																			
4 PLACES	±	±																																			
3 PLACES	±	±																																			
2 PLACES	± 0.2	±																																			
1 PLACE	±	±																																			
0 PLACES	±	±																																			

DOCUMENT STATUS	P1	RELEASE DATE	2021/10/11	11:53:31
-----------------	----	--------------	------------	----------

PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION				
								A	B	F	M	P
87914-2611	-----	-----	-----	-----	26	-----	1	33.02	30.48	10.92	5.84	2.79
87914-2621	-----	-----	-----	-----	26	-----	1	33.02	30.48	12.25	7.00	2.96
87914-2631	-----	-----	-----	-----	26	-----	1	33.02	30.48	13.38	6.09	5.00
87914-2612	-----	-----	-----	-----	26	-----	2	33.02	30.48	10.92	5.84	2.79
87914-2622	-----	-----	-----	-----	26	-----	2	33.02	30.48	12.25	7.00	2.96
87914-2632	-----	-----	-----	-----	26	-----	2	33.02	30.48	13.38	6.09	5.00
87914-2613	-----	-----	-----	-----	26	-----	3	33.02	30.48	10.92	5.84	2.79
87914-2623	-----	-----	-----	-----	26	-----	3	33.02	30.48	12.25	7.00	2.96
87914-2633	-----	-----	-----	-----	26	-----	3	33.02	30.48	13.38	6.09	5.00
87914-2614	-----	-----	-----	-----	26	-----	4	33.02	30.48	10.92	5.84	2.79
87914-2624	-----	-----	-----	-----	26	-----	4	33.02	30.48	12.25	7.00	2.96
87914-2634	-----	-----	-----	-----	26	-----	4	33.02	30.48	13.38	6.09	5.00
87914-2615	-----	-----	-----	-----	26	-----	5	33.02	30.48	10.92	5.84	2.79
87914-2625	-----	-----	-----	-----	26	-----	5	33.02	30.48	12.25	7.00	2.96
87914-2635	-----	-----	-----	-----	26	-----	5	33.02	30.48	13.38	6.09	5.00
87914-2616	-----	-----	-----	-----	26	-----	6	33.02	30.48	10.92	5.84	2.79
87914-2617	-----	-----	-----	-----	26	-----	6	33.02	30.48	10.92	5.84	2.79
87914-2626	-----	-----	-----	-----	26	-----	6	33.02	30.48	12.25	7.00	2.96
87914-2627	-----	-----	-----	-----	26	-----	6	33.02	30.48	12.25	7.00	2.96
87914-2636	-----	-----	-----	-----	26	-----	6	33.02	30.48	13.38	6.09	5.00
87914-2601	-----	-----	-----	-----	26	-----	4	33.02	30.48	13.21	8.13	2.79
87914-2602	-----	-----	-----	-----	26	-----	5	33.02	30.48	13.21	8.13	2.79
87914-2603	-----	-----	-----	-----	26	-----	6	33.02	30.48	13.21	8.13	2.79
87914-2604	-----	-----	-----	-----	26	-----	4	33.02	30.48	11.11	6.10	2.72
87914-2605	-----	-----	-----	-----	26	-----	5	33.02	30.48	11.11	6.10	2.72
87914-2606	-----	-----	-----	-----	26	-----	6	33.02	30.48	11.11	6.10	2.72
87914-2607	-----	-----	-----	-----	26	-----	6	33.02	30.48	11.11	6.10	2.72

(D22)
(D22)
(D22)

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									
DIMENSION UNITS		SCALE		CURRENT REV DESC: BRIGHT TIN PHASE OUT					
mm		NTS		 2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H					
GENERAL TOLERANCES (UNLESS SPECIFIED)									
		MM	INCH	EC NO: 679909 DRWN: AKUMAR19 2021/06/29 CHK'D: MRAMAKRISHNA 2021/10/11 APPR: MRAMAKRISHNA 2021/10/11 INITIAL REVISION: DRWN: YLQIAO 2005/01/17 APPR: SLOW 2005/01/25					
4 PLACES	±		±						
3 PLACES	±		±						
2 PLACES	±	0.2	±						
1 PLACE	±		±						
0 PLACES	±		±	ANGULAR TOL ± 3.0°		DOCUMENT NUMBER: SD-87914-013 DOC TYPE: PSD DOC PART: 000 REVISION: D22			
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION		DRAWING	SERIES	MATERIAL NUMBER	CUSTOMER	SHEET NUMBER	
				A3-SIZE	87914	SEE TABLE	GENERAL MARKET	18 OF 45	


DOCUMENT STATUS	P1	RELEASE DATE	2021/10/11 11:53:31
-----------------	----	--------------	---------------------

PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION				
								A	B	F	M	P
87914-2811	-----	-----	-----	-----	28	-----	1	35.56	33.02	10.92	5.84	2.79
87914-2821	-----	-----	-----	-----	28	-----	1	35.56	33.02	12.25	7.00	2.96
87914-2831	-----	-----	-----	-----	28	-----	1	35.56	33.02	13.38	6.09	5.00
87914-2812	-----	-----	-----	-----	28	-----	2	35.56	33.02	10.92	5.84	2.79
87914-2822	-----	-----	-----	-----	28	-----	2	35.56	33.02	12.25	7.00	2.96
87914-2832	-----	-----	-----	-----	28	-----	2	35.56	33.02	13.38	6.09	5.00
87914-2813	-----	-----	-----	-----	28	-----	3	35.56	33.02	10.92	5.84	2.79
87914-2823	-----	-----	-----	-----	28	-----	3	35.56	33.02	12.25	7.00	2.96
87914-2833	-----	-----	-----	-----	28	-----	3	35.56	33.02	13.38	6.09	5.00
87914-2814	-----	-----	-----	-----	28	-----	4	35.56	33.02	10.92	5.84	2.79
87914-2824	-----	-----	-----	-----	28	-----	4	35.56	33.02	12.25	7.00	2.96
87914-2834	-----	-----	-----	-----	28	-----	4	35.56	33.02	13.38	6.09	5.00
87914-2815	-----	-----	-----	-----	28	-----	5	35.56	33.02	10.92	5.84	2.79
87914-2825	-----	-----	-----	-----	28	-----	5	35.56	33.02	12.25	7.00	2.96
87914-2835	-----	-----	-----	-----	28	-----	5	35.56	33.02	13.38	6.09	5.00
87914-2816	-----	-----	-----	-----	28	-----	6	35.56	33.02	10.92	5.84	2.79
87914-2817	-----	-----	-----	-----	28	-----	6	35.56	33.02	10.92	5.84	2.79
87914-2826	-----	-----	-----	-----	28	-----	6	35.56	33.02	12.25	7.00	2.96
87914-2827	-----	-----	-----	-----	28	-----	6	35.56	33.02	12.25	7.00	2.96
87914-2836	-----	-----	-----	-----	28	-----	6	35.56	33.02	13.38	6.09	5.00
87914-2801	-----	-----	-----	-----	28	-----	4	35.56	33.02	13.21	8.13	2.79
87914-2802	-----	-----	-----	-----	28	-----	5	35.56	33.02	13.21	8.13	2.79
87914-2803	-----	-----	-----	-----	28	-----	6	35.56	33.02	13.21	8.13	2.79
87914-2804	-----	-----	-----	-----	28	-----	4	35.56	33.02	11.11	6.10	2.72
87914-2805	-----	-----	-----	-----	28	-----	5	35.56	33.02	11.11	6.10	2.72
87914-2806	-----	-----	-----	-----	28	-----	6	35.56	33.02	11.11	6.10	2.72
87914-2807	-----	-----	-----	-----	28	-----	6	35.56	33.02	11.11	6.10	2.72

⊙D22

⊙D22

⊙D22



THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											
DIMENSION UNITS		SCALE		CURRENT REV DESC: BRIGHT TIN PHASE OUT							
mm		NTS									
GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 679909		DRWN: AKUMAR19		2021/06/29		2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H	
				CHK'D: MRAMAKRISHNA		2021/10/11					
				APPR: MRAMAKRISHNA		2021/10/11				PRODUCT CUSTOMER DRAWING	
				INITIAL REVISION:							
				DRWN: YLQIAO		2005/01/17		DOCUMENT NUMBER		DOC TYPE	
				APPR: SCLW		2005/01/25		SD-87914-013		PSD	
				ANGULAR TOL ± 3.0°				DOC PART		000	
				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION		DRAWING		SERIES	
						A3-SIZE		87914		MATERIAL NUMBER	
								CUSTOMER		SEE TABLE	
								GENERAL MARKET		SHEET NUMBER	
										19 OF 45	

PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION					
								A	B	F	M	P	G
87914-3011	-----	-----	-----	-----	30	-----	1	38.10	35.56	10.92	5.84	2.79	---
87914-3021	-----	-----	-----	-----	30	-----	1	38.10	35.56	12.25	7.00	2.96	---
87914-3031	-----	-----	-----	-----	30	-----	1	38.10	35.56	13.38	6.09	5.00	---
87914-3012	-----	-----	-----	-----	30	-----	2	38.10	35.56	10.92	5.84	2.79	---
87914-3022	-----	-----	-----	-----	30	-----	2	38.10	35.56	12.25	7.00	2.96	---
87914-3032	-----	-----	-----	-----	30	-----	2	38.10	35.56	13.38	6.09	5.00	---
87914-3013	-----	-----	-----	-----	30	-----	3	38.10	35.56	10.92	5.84	2.79	---
87914-3023	-----	-----	-----	-----	30	-----	3	38.10	35.56	12.25	7.00	2.96	---
87914-3033	-----	-----	-----	-----	30	-----	3	38.10	35.56	13.38	6.09	5.00	---
87914-3014	-----	-----	-----	-----	30	-----	4	38.10	35.56	10.92	5.84	2.79	---
87914-3024	-----	-----	-----	-----	30	-----	4	38.10	35.56	12.25	7.00	2.96	---
87914-3034	-----	-----	-----	-----	30	-----	4	38.10	35.56	13.38	6.09	5.00	---
87914-3015	-----	-----	-----	-----	30	-----	5	38.10	35.56	10.92	5.84	2.79	---
87914-3025	-----	-----	-----	-----	30	-----	5	38.10	35.56	12.25	7.00	2.96	---
87914-3035	-----	-----	-----	-----	30	-----	5	38.10	35.56	13.38	6.09	5.00	---
87914-3016	-----	-----	-----	-----	30	-----	6	38.10	35.56	10.92	5.84	2.79	---
87914-3017	-----	-----	-----	-----	30	-----	6	38.10	35.56	10.92	5.84	2.79	---
87914-3026	-----	-----	-----	-----	30	-----	6	38.10	35.56	12.25	7.00	2.96	---
87914-3027	-----	-----	-----	-----	30	-----	6	38.10	35.56	12.25	7.00	2.96	---
87914-3036	-----	-----	-----	-----	30	-----	6	38.10	35.56	13.38	6.09	5.00	---
87914-3001	-----	-----	-----	-----	30	-----	4	38.10	35.56	13.21	8.13	2.79	---
87914-3002	-----	-----	-----	-----	30	-----	5	38.10	35.56	13.21	8.13	2.79	---
87914-3003	-----	-----	-----	-----	30	-----	6	38.10	35.56	13.21	8.13	2.79	---
87914-3004	-----	-----	-----	-----	30	-----	4	38.10	35.56	11.11	6.10	2.72	---
87914-3005	-----	-----	-----	-----	30	-----	5	38.10	35.56	11.11	6.10	2.72	---
87914-3006	-----	-----	-----	-----	30	-----	6	38.10	35.56	11.11	6.10	2.72	---
87914-3007	-----	-----	-----	-----	30	-----	6	38.10	35.56	11.11	6.10	2.72	---
-----	-----	-----	-----	87914-3037	30	-----	6	38.10	35.56	15.29	10.00	3.00	16.29

D22

D22

D22



THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											
DIMENSION UNITS		SCALE		CURRENT REV DESC: BRIGHT TIN PHASE OUT							
mm		NTS									
GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 679909		DRWN: AKUMAR19		2021/06/29		2.54MM PITCH	
				CHK'D: MRAMAKRISHNA		2021/10/11				DUAL ROW HEADER SINGLE WAFER, T/H	
				APPR: MRAMAKRISHNA		2021/10/11				PRODUCT CUSTOMER DRAWING	
				INITIAL REVISION:		DRWN: YLQIAO		2005/01/17		DOCUMENT NUMBER	
				ANGULAR TOL ± 3.0°		APPR: SCLW		2005/01/25		SD-87914-013	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER	
						A3-SIZE		87914		CUSTOMER	
								SEE TABLE		GENERAL MARKET	
										SHEET NUMBER	
										20 OF 45	

DOCUMENT STATUS	P1	RELEASE DATE	2021/10/11	11:53:31
-----------------	----	--------------	------------	----------

PART NO FOR TRAY PACKAGING	PART NO FOR BULK PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION				
									A	B	F	M	P
-----	87914-0032	-----	-----	-----	-----	32	-----	5	40.64	38.10	7.62	3.05	2.28
87914-3211	-----	-----	-----	-----	-----	32	-----	1	40.64	38.10	10.92	5.84	2.79
87914-3221	-----	-----	-----	-----	-----	32	-----	1	40.64	38.10	12.25	7.00	2.96
87914-3231	-----	-----	-----	-----	-----	32	-----	1	40.64	38.10	13.38	6.09	5.00
87914-3212	-----	-----	-----	-----	-----	32	-----	2	40.64	38.10	10.92	5.84	2.79
87914-3222	-----	-----	-----	-----	-----	32	-----	2	40.64	38.10	12.25	7.00	2.96
87914-3232	-----	-----	-----	-----	-----	32	-----	2	40.64	38.10	13.38	6.09	5.00
87914-3213	-----	-----	-----	-----	-----	32	-----	3	40.64	38.10	10.92	5.84	2.79
87914-3223	-----	-----	-----	-----	-----	32	-----	3	40.64	38.10	12.25	7.00	2.96
87914-3233	-----	-----	-----	-----	-----	32	-----	3	40.64	38.10	13.38	6.09	5.00
87914-3214	-----	-----	-----	-----	-----	32	-----	4	40.64	38.10	10.92	5.84	2.79
87914-3224	-----	-----	-----	-----	-----	32	-----	4	40.64	38.10	12.25	7.00	2.96
87914-3234	-----	-----	-----	-----	-----	32	-----	4	40.64	38.10	13.38	6.09	5.00
87914-3215	-----	-----	-----	-----	-----	32	-----	5	40.64	38.10	10.92	5.84	2.79
87914-3225	-----	-----	-----	-----	-----	32	-----	5	40.64	38.10	12.25	7.00	2.96
87914-3235	-----	-----	-----	-----	-----	32	-----	5	40.64	38.10	13.38	6.09	5.00
87914-3216	-----	-----	-----	-----	-----	32	-----	6	40.64	38.10	10.92	5.84	2.79
87914-3217	-----	-----	-----	-----	-----	32	-----	6	40.64	38.10	10.92	5.84	2.79
87914-3226	-----	-----	-----	-----	-----	32	-----	6	40.64	38.10	12.25	7.00	2.96
87914-3227	-----	-----	-----	-----	-----	32	-----	6	40.64	38.10	12.25	7.00	2.96
87914-3236	-----	-----	-----	-----	-----	32	-----	6	40.64	38.10	13.38	6.09	5.00
87914-3201	-----	-----	-----	-----	-----	32	-----	4	40.64	38.10	13.21	8.13	2.79
87914-3202	-----	-----	-----	-----	-----	32	-----	5	40.64	38.10	13.21	8.13	2.79
87914-3203	-----	-----	-----	-----	-----	32	-----	6	40.64	38.10	13.21	8.13	2.79
87914-3207	-----	-----	-----	-----	-----	32	-----	6	40.64	38.10	13.21	8.13	2.79
87914-3204	-----	-----	-----	-----	-----	32	-----	4	40.64	38.10	11.11	6.10	2.72
87914-3205	-----	-----	-----	-----	-----	32	-----	5	40.64	38.10	11.11	6.10	2.72
87914-3206	-----	-----	-----	-----	-----	32	-----	6	40.64	38.10	11.11	6.10	2.72
87914-3208	-----	-----	-----	-----	-----	32	-----	6	40.64	38.10	11.11	6.10	2.72

D22
D22
D22
D22
D22

C										A				
B										A				
A										A				



THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION															
DIMENSION UNITS		SCALE		CURRENT REV DESC: BRIGHT TIN PHASE OUT											
mm		NTS		 <p>2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H</p>											
GENERAL TOLERANCES (UNLESS SPECIFIED)															
		MM		INCH		EC NO: 679909									
4 PLACES		±		±		DRWN: AKUMAR19 2021/06/29									
3 PLACES		±		±		CHK'D: MRAMAKRISHNA 2021/10/11									
2 PLACES		± 0.2		±		APPR: MRAMAKRISHNA 2021/10/11									
1 PLACE		±		±		INITIAL REVISION:									
0 PLACES		±		±		DRWN: YLQIAO 2005/01/17									
ANGULAR TOL		± 3.0°		±		APPR: SLOW 2005/01/25									
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
						A3-SIZE		87914		SEE TABLE		GENERAL MARKET		21 OF 45	

PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION				
								A	B	F	M	P
87914-3411	-----	-----	-----	-----	34	-----	1	43.18	40.64	10.92	5.84	2.79
87914-3421	-----	-----	-----	-----	34	-----	1	43.18	40.64	12.25	7.00	2.96
87914-3431	-----	-----	-----	-----	34	-----	1	43.18	40.64	13.38	6.09	5.00
87914-3412	-----	-----	-----	-----	34	-----	2	43.18	40.64	10.92	5.84	2.79
87914-3422	-----	-----	-----	-----	34	-----	2	43.18	40.64	12.25	7.00	2.96
87914-3432	-----	-----	-----	-----	34	-----	2	43.18	40.64	13.38	6.09	5.00
87914-3413	-----	-----	-----	-----	34	-----	3	43.18	40.64	10.92	5.84	2.79
87914-3423	-----	-----	-----	-----	34	-----	3	43.18	40.64	12.25	7.00	2.96
87914-3433	-----	-----	-----	-----	34	-----	3	43.18	40.64	13.38	6.09	5.00
87914-3414	-----	-----	-----	-----	34	-----	4	43.18	40.64	10.92	5.84	2.79
87914-3424	-----	-----	-----	-----	34	-----	4	43.18	40.64	12.25	7.00	2.96
87914-3434	-----	-----	-----	-----	34	-----	4	43.18	40.64	13.38	6.09	5.00
87914-3415	-----	-----	-----	-----	34	-----	5	43.18	40.64	10.92	5.84	2.79
87914-3425	-----	-----	-----	-----	34	-----	5	43.18	40.64	12.25	7.00	2.96
87914-3435	-----	-----	-----	-----	34	-----	5	43.18	40.64	13.38	6.09	5.00
87914-3416	-----	-----	-----	-----	34	-----	6	43.18	40.64	10.92	5.84	2.79
87914-3417	-----	-----	-----	-----	34	-----	6	43.18	40.64	10.92	5.84	2.79
87914-3426	-----	-----	-----	-----	34	-----	6	43.18	40.64	12.25	7.00	2.96
87914-3427	-----	-----	-----	-----	34	-----	6	43.18	40.64	12.25	7.00	2.96
87914-3436	-----	-----	-----	-----	34	-----	6	43.18	40.64	13.38	6.09	5.00
87914-3401	-----	-----	-----	-----	34	-----	4	43.18	40.64	13.21	8.13	2.79
87914-3402	-----	-----	-----	-----	34	-----	5	43.18	40.64	13.21	8.13	2.79
87914-3403	-----	-----	-----	-----	34	-----	6	43.18	40.64	13.21	8.13	2.79
87914-3404	-----	-----	-----	-----	34	-----	4	43.18	40.64	11.11	6.10	2.72
87914-3405	-----	-----	-----	-----	34	-----	5	43.18	40.64	11.11	6.10	2.72
87914-3406	-----	-----	-----	-----	34	-----	6	43.18	40.64	11.11	6.10	2.72
87914-3407	-----	-----	-----	-----	34	-----	6	43.18	40.64	11.11	6.10	2.72

D22

D22

D22

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION													
DIMENSION UNITS		SCALE		CURRENT REV DESC: BRIGHT TIN PHASE OUT									
mm		NTS											
GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 679909		DRWN: AKUMAR19		2021/06/29		2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H			
				CHK'D: MRAMAKRISHNA		2021/10/11							
				APPR: MRAMAKRISHNA		2021/10/11		PRODUCT CUSTOMER DRAWING					
				INITIAL REVISION:				DOCUMENT NUMBER		DOC TYPE		DOC PART	
				DRWN: YLQIAO		2005/01/17		SD-87914-013		PSD		000	
				APPR: SLOW		2005/01/25				D22			
ANGULAR TOL ± 3.0°				THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS						A3-SIZE		87914		SEE TABLE		GENERAL MARKET	
										SHEET NUMBER		22 OF 45	

DOCUMENT STATUS	P1	RELEASE DATE	2021/10/11	11:53:31
-----------------	----	--------------	------------	----------

PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION				
								A	B	F	M	P
87914-3611	-----	-----	-----	-----	36	-----	1	45.72	43.18	10.92	5.84	2.79
87914-3621	-----	-----	-----	-----	36	-----	1	45.72	43.18	12.25	7.00	2.96
87914-3631	-----	-----	-----	-----	36	-----	1	45.72	43.18	13.38	6.09	5.00
87914-3612	-----	-----	-----	-----	36	-----	2	45.72	43.18	10.92	5.84	2.79
87914-3622	-----	-----	-----	-----	36	-----	2	45.72	43.18	12.25	7.00	2.96
87914-3632	-----	-----	-----	-----	36	-----	2	45.72	43.18	13.38	6.09	5.00
87914-3613	-----	-----	-----	-----	36	-----	3	45.72	43.18	10.92	5.84	2.79
87914-3623	-----	-----	-----	-----	36	-----	3	45.72	43.18	12.25	7.00	2.96
87914-3633	-----	-----	-----	-----	36	-----	3	45.72	43.18	13.38	6.09	5.00
87914-3614	-----	-----	-----	-----	36	-----	4	45.72	43.18	10.92	5.84	2.79
87914-3624	-----	-----	-----	-----	36	-----	4	45.72	43.18	12.25	7.00	2.96
87914-3634	-----	-----	-----	-----	36	-----	4	45.72	43.18	13.38	6.09	5.00
87914-3615	-----	-----	-----	-----	36	-----	5	45.72	43.18	10.92	5.84	2.79
87914-3625	-----	-----	-----	-----	36	-----	5	45.72	43.18	12.25	7.00	2.96
87914-3635	-----	-----	-----	-----	36	-----	5	45.72	43.18	13.38	6.09	5.00
87914-3616	-----	-----	-----	-----	36	-----	6	45.72	43.18	10.92	5.84	2.79
87914-3617	-----	-----	-----	-----	36	-----	6	45.72	43.18	10.92	5.84	2.79
87914-3626	-----	-----	-----	-----	36	-----	6	45.72	43.18	12.25	7.00	2.96
87914-3627	-----	-----	-----	-----	36	-----	6	45.72	43.18	12.25	7.00	2.96
87914-3636	-----	-----	-----	-----	36	-----	6	45.72	43.18	13.38	6.09	5.00
87914-3601	-----	-----	-----	-----	36	-----	4	45.72	43.18	13.21	8.13	2.79
87914-3602	-----	-----	-----	-----	36	-----	5	45.72	43.18	13.21	8.13	2.79
87914-3603	-----	-----	-----	-----	36	-----	6	45.72	43.18	13.21	8.13	2.79
87914-3604	-----	-----	-----	-----	36	-----	4	45.72	43.18	11.11	6.10	2.72
87914-3605	-----	-----	-----	-----	36	-----	5	45.72	43.18	11.11	6.10	2.72
87914-3606	-----	-----	-----	-----	36	-----	6	45.72	43.18	11.11	6.10	2.72
87914-3607	-----	-----	-----	-----	36	-----	6	45.72	43.18	11.11	6.10	2.72

(D22)
(D22)
(D22)

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									
DIMENSION UNITS		SCALE		CURRENT REV DESC: BRIGHT TIN PHASE OUT					
mm		NTS		 2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H					
GENERAL TOLERANCES (UNLESS SPECIFIED)									
		MM	INCH	EC NO: 679909 DRWN: AKUMAR19 2021/06/29 CHK'D: MRAMAKRISHNA 2021/10/11 APPR: MRAMAKRISHNA 2021/10/11 INITIAL REVISION: DRWN: YLQIAO 2005/01/17 APPR: SCLOW 2005/01/25					
4 PLACES	±		±						
3 PLACES	±		±						
2 PLACES	±	0.2	±						
1 PLACE	±		±						
0 PLACES	±		±	DOCUMENT NUMBER		DOC TYPE	DOC PART	REVISION	
ANGULAR TOL ± 3.0°				SD-87914-013		PSD	000	D22	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION	DRAWING	SERIES	MATERIAL NUMBER	CUSTOMER	SHEET NUMBER
					A3-SIZE	87914	SEE TABLE	GENERAL MARKET	23 OF 45



DOCUMENT STATUS	P1	RELEASE DATE	2021/10/11	11:53:31
-----------------	----	--------------	------------	----------

PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION				
								A	B	F	M	P
87914-3811	-----	-----	-----	-----	38	-----	1	48.26	45.72	10.92	5.84	2.79
87914-3821	-----	-----	-----	-----	38	-----	1	48.26	45.72	12.25	7.00	2.96
87914-3831	-----	-----	-----	-----	38	-----	1	48.26	45.72	13.38	6.09	5.00
87914-3812	-----	-----	-----	-----	38	-----	2	48.26	45.72	10.92	5.84	2.79
87914-3822	-----	-----	-----	-----	38	-----	2	48.26	45.72	12.25	7.00	2.96
87914-3832	-----	-----	-----	-----	38	-----	2	48.26	45.72	13.38	6.09	5.00
87914-3813	-----	-----	-----	-----	38	-----	3	48.26	45.72	10.92	5.84	2.79
87914-3823	-----	-----	-----	-----	38	-----	3	48.26	45.72	12.25	7.00	2.96
87914-3833	-----	-----	-----	-----	38	-----	3	48.26	45.72	13.38	6.09	5.00
87914-3814	-----	-----	-----	-----	38	-----	4	48.26	45.72	10.92	5.84	2.79
87914-3824	-----	-----	-----	-----	38	-----	4	48.26	45.72	12.25	7.00	2.96
87914-3834	-----	-----	-----	-----	38	-----	4	48.26	45.72	13.38	6.09	5.00
87914-3815	-----	-----	-----	-----	38	-----	5	48.26	45.72	10.92	5.84	2.79
87914-3825	-----	-----	-----	-----	38	-----	5	48.26	45.72	12.25	7.00	2.96
87914-3835	-----	-----	-----	-----	38	-----	5	48.26	45.72	13.38	6.09	5.00
87914-3816	-----	-----	-----	-----	38	-----	6	48.26	45.72	10.92	5.84	2.79
87914-3817	-----	-----	-----	-----	38	-----	6	48.26	45.72	10.92	5.84	2.79
87914-3826	-----	-----	-----	-----	38	-----	6	48.26	45.72	12.25	7.00	2.96
87914-3827	-----	-----	-----	-----	38	-----	6	48.26	45.72	12.25	7.00	2.96
87914-3836	-----	-----	-----	-----	38	-----	6	48.26	45.72	13.38	6.09	5.00
87914-3801	-----	-----	-----	-----	38	-----	4	48.26	45.72	13.21	8.13	2.79
87914-3802	-----	-----	-----	-----	38	-----	5	48.26	45.72	13.21	8.13	2.79
87914-3803	-----	-----	-----	-----	38	-----	6	48.26	45.72	13.21	8.13	2.79
87914-3804	-----	-----	-----	-----	38	-----	4	48.26	45.72	11.11	6.10	2.72
87914-3805	-----	-----	-----	-----	38	-----	5	48.26	45.72	11.11	6.10	2.72
87914-3806	-----	-----	-----	-----	38	-----	6	48.26	45.72	11.11	6.10	2.72
87914-3807	-----	-----	-----	-----	38	-----	6	48.26	45.72	11.11	6.10	2.72

D22

D22



D22

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											
DIMENSION UNITS		SCALE		CURRENT REV DESC: BRIGHT TIN PHASE OUT							
mm		NTS									
GENERAL TOLERANCES (UNLESS SPECIFIED)											
		MM	INCH	EC NO: 679909 DRWN: AKUMAR19 2021/06/29 CHK'D: MRAMAKRISHNA 2021/10/11 APPR: MRAMAKRISHNA 2021/10/11 INITIAL REVISION: DRWN: YLQIAO 2005/01/17 APPR: SCLOW 2005/01/25							
4 PLACES	±		±								
3 PLACES	±		±								
2 PLACES	±	0.2	±								
1 PLACE	±		±								
0 PLACES	±		±	DOCUMENT NUMBER		DOC TYPE	DOC PART	REVISION			
ANGULAR TOL ± 3.0°				SD-87914-013		PSD	000	D22			
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER	
				A3-SIZE		87914		SEE TABLE		GENERAL MARKET	
								SHEET NUMBER		24 OF 45	

DOCUMENT STATUS	P1	RELEASE DATE	2021/10/11	11:53:31
-----------------	----	--------------	------------	----------

PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION				
								A	B	F	M	P
87914-4011	-----	-----	-----	-----	40	-----	1	50.80	48.26	10.92	5.84	2.79
87914-4021	-----	-----	-----	-----	40	-----	1	50.80	48.26	12.25	7.00	2.96
87914-4031	-----	-----	-----	-----	40	-----	1	50.80	48.26	13.38	6.09	5.00
87914-4012	-----	-----	-----	-----	40	-----	2	50.80	48.26	10.92	5.84	2.79
87914-4022	-----	-----	-----	-----	40	-----	2	50.80	48.26	12.25	7.00	2.96
87914-4032	-----	-----	-----	-----	40	-----	2	50.80	48.26	13.38	6.09	5.00
87914-4013	-----	-----	-----	-----	40	-----	3	50.80	48.26	10.92	5.84	2.79
87914-4023	-----	-----	-----	-----	40	-----	3	50.80	48.26	12.25	7.00	2.96
87914-4033	-----	-----	-----	-----	40	-----	3	50.80	48.26	13.38	6.09	5.00
87914-4014	-----	-----	-----	-----	40	-----	4	50.80	48.26	10.92	5.84	2.79
87914-4024	-----	-----	-----	-----	40	-----	4	50.80	48.26	12.25	7.00	2.96
87914-4034	-----	-----	-----	-----	40	-----	4	50.80	48.26	13.38	6.09	5.00
87914-4015	-----	-----	-----	-----	40	-----	5	50.80	48.26	10.92	5.84	2.79
87914-4025	-----	-----	-----	-----	40	-----	5	50.80	48.26	12.25	7.00	2.96
87914-4035	-----	-----	-----	-----	40	-----	5	50.80	48.26	13.38	6.09	5.00
87914-4016	-----	-----	-----	-----	40	-----	6	50.80	48.26	10.92	5.84	2.79
87914-4017	-----	-----	-----	-----	40	-----	6	50.80	48.26	10.92	5.84	2.79
87914-4026	-----	-----	-----	-----	40	-----	6	50.80	48.26	12.25	7.00	2.96
87914-4027	-----	-----	-----	-----	40	-----	6	50.80	48.26	12.25	7.00	2.96
87914-4036	-----	-----	-----	-----	40	-----	6	50.80	48.26	13.38	6.09	5.00
87914-4001	-----	-----	-----	-----	40	-----	4	50.80	48.26	13.21	8.13	2.79
87914-4002	-----	-----	-----	-----	40	-----	5	50.80	48.26	13.21	8.13	2.79
87914-4003	-----	-----	-----	-----	40	-----	6	50.80	48.26	13.21	8.13	2.79
87914-4004	-----	-----	-----	-----	40	-----	4	50.80	48.26	11.11	6.10	2.72
87914-4005	-----	-----	-----	-----	40	-----	5	50.80	48.26	11.11	6.10	2.72
87914-4006	-----	-----	-----	-----	40	-----	6	50.80	48.26	11.11	6.10	2.72
87914-4007	-----	-----	-----	-----	40	-----	6	50.80	48.26	11.11	6.10	2.72

(D22)
(D22)
(D22)

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									
DIMENSION UNITS		SCALE		CURRENT REV DESC: BRIGHT TIN PHASE OUT					
mm		NTS		 2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H PRODUCT CUSTOMER DRAWING					
GENERAL TOLERANCES (UNLESS SPECIFIED)									
		MM	INCH						
4 PLACES	±		±						
3 PLACES	±		±						
2 PLACES	±	0.2	±						
1 PLACE	±		±						
0 PLACES	±		±						
ANGULAR TOL		± 3.0°		EC NO: 679909		DRWN: AKUMAR19		2021/06/29	
				CHK'D: MRAMAKRISHNA		APPR: MRAMAKRISHNA		2021/10/11	
				INITIAL REVISION:		DRWN: YLQIAO		2005/01/17	
				APPR: SCLOW		APPR: SCLOW		2005/01/25	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER	
				A3-SIZE		87914		SEE TABLE	
				CUSTOMER		GENERAL MARKET		SHEET NUMBER	
								25 OF 45	

DOCUMENT STATUS	P1	RELEASE DATE	2021/10/11	11:53:31
-----------------	----	--------------	------------	----------

PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION				
								A	B	F	M	P
87914-4211	-----	-----	-----	-----	42	-----	1	53.34	50.80	10.92	5.84	2.79
87914-4221	-----	-----	-----	-----	42	-----	1	53.34	50.80	12.25	7.00	2.96
87914-4212	-----	-----	-----	-----	42	-----	2	53.34	50.80	10.92	5.84	2.79
87914-4222	-----	-----	-----	-----	42	-----	2	53.34	50.80	12.25	7.00	2.96
87914-4213	-----	-----	-----	-----	42	-----	3	53.34	50.80	10.92	5.84	2.79
87914-4223	-----	-----	-----	-----	42	-----	3	53.34	50.80	12.25	7.00	2.96
87914-4214	-----	-----	-----	-----	42	-----	4	53.34	50.80	10.92	5.84	2.79
87914-4224	-----	-----	-----	-----	42	-----	4	53.34	50.80	12.25	7.00	2.96
87914-4215	-----	-----	-----	-----	42	-----	5	53.34	50.80	10.92	5.84	2.79
87914-4225	-----	-----	-----	-----	42	-----	5	53.34	50.80	12.25	7.00	2.96
87914-4216	-----	-----	-----	-----	42	-----	6	53.34	50.80	10.92	5.84	2.79
87914-4217	-----	-----	-----	-----	42	-----	6	53.34	50.80	10.92	5.84	2.79
87914-4226	-----	-----	-----	-----	42	-----	6	53.34	50.80	12.25	7.00	2.96
87914-4227	-----	-----	-----	-----	42	-----	6	53.34	50.80	12.25	7.00	2.96
87914-4201	-----	-----	-----	-----	42	-----	4	53.34	50.80	13.21	8.13	2.79
87914-4202	-----	-----	-----	-----	42	-----	5	53.34	50.80	13.21	8.13	2.79
87914-4203	-----	-----	-----	-----	42	-----	6	53.34	50.80	13.21	8.13	2.79
87914-4204	-----	-----	-----	-----	42	-----	4	53.34	50.80	11.11	6.10	2.72
87914-4205	-----	-----	-----	-----	42	-----	5	53.34	50.80	11.11	6.10	2.72
87914-4206	-----	-----	-----	-----	42	-----	6	53.34	50.80	11.11	6.10	2.72
87914-4207	-----	-----	-----	-----	42	-----	6	53.34	50.80	11.11	6.10	2.72

⊘D22
⊘D22
⊘D22

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											
DIMENSION UNITS		SCALE		CURRENT REV DESC: BRIGHT TIN PHASE OUT						molex	
mm		NTS									
GENERAL TOLERANCES (UNLESS SPECIFIED)											
		MM		INCH							
4 PLACES		±		±							
3 PLACES		±		±							
2 PLACES		± 0.2		±							
1 PLACE		±		±							
0 PLACES		±		±							
ANGULAR TOL ± 3.0°											
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES		SHEET NUMBER	
						A3-SIZE		87914		26 OF 45	


DOCUMENT STATUS	P1	RELEASE DATE	2021/10/11	11:53:31
-----------------	----	--------------	------------	----------

PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION				
								A	B	F	M	P
87914-4411	-----	-----	-----	-----	44	-----	1	55.88	53.34	10.92	5.84	2.79
87914-4421	-----	-----	-----	-----	44	-----	1	55.88	53.34	12.25	7.00	2.96
87914-4412	-----	-----	-----	-----	44	-----	2	55.88	53.34	10.92	5.84	2.79
87914-4422	-----	-----	-----	-----	44	-----	2	55.88	53.34	12.25	7.00	2.96
87914-4413	-----	-----	-----	-----	44	-----	3	55.88	53.34	10.92	5.84	2.79
87914-4423	-----	-----	-----	-----	44	-----	3	55.88	53.34	12.25	7.00	2.96
87914-4414	-----	-----	-----	-----	44	-----	4	55.88	53.34	10.92	5.84	2.79
87914-4424	-----	-----	-----	-----	44	-----	4	55.88	53.34	12.25	7.00	2.96
87914-4415	-----	-----	-----	-----	44	-----	5	55.88	53.34	10.92	5.84	2.79
87914-4425	-----	-----	-----	-----	44	-----	5	55.88	53.34	12.25	7.00	2.96
87914-4416	-----	-----	-----	-----	44	-----	6	55.88	53.34	10.92	5.84	2.79
87914-4417	-----	-----	-----	-----	44	-----	6	55.88	53.34	10.92	5.84	2.79
87914-4426	-----	-----	-----	-----	44	-----	6	55.88	53.34	12.25	7.00	2.96
87914-4427	-----	-----	-----	-----	44	-----	6	55.88	53.34	12.25	7.00	2.96
87914-4401	-----	-----	-----	-----	44	-----	4	55.88	53.34	13.21	8.13	2.79
87914-4402	-----	-----	-----	-----	44	-----	5	55.88	53.34	13.21	8.13	2.79
87914-4403	-----	-----	-----	-----	44	-----	6	55.88	53.34	13.21	8.13	2.79
87914-4404	-----	-----	-----	-----	44	-----	4	55.88	53.34	11.11	6.10	2.72
87914-4405	-----	-----	-----	-----	44	-----	5	55.88	53.34	11.11	6.10	2.72
87914-4406	-----	-----	-----	-----	44	-----	6	55.88	53.34	11.11	6.10	2.72
87914-4407	-----	-----	-----	-----	44	-----	6	55.88	53.34	11.11	6.10	2.72

Ⓟ

Ⓟ

Ⓟ


THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											
DIMENSION UNITS		SCALE		CURRENT REV DESC: BRIGHT TIN PHASE OUT							
mm		NTS									
GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 679909		DRWN: AKUMAR19		2021/06/29		2.54MM PITCH	
				CHK'D: MRAMAKRISHNA		2021/10/11				DUAL ROW HEADER SINGLE WAFER, T/H	
				APPR: MRAMAKRISHNA		2021/10/11				PRODUCT CUSTOMER DRAWING	
4 PLACES ±				INITIAL REVISION:		DRWN: YLQIAO		2005/01/17		DOCUMENT NUMBER	
3 PLACES ±				DRWN: YLQIAO		2005/01/25		SD-87914-013		DOC TYPE DOC PART REVISION	
2 PLACES ± 0.2				APPR: SLOW		2005/01/25		PSD		000 D22	
1 PLACE ±				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION		DRAWING		SERIES	
0 PLACES ±								A3-SIZE		87914	
ANGULAR TOL ± 3.0°								MATERIAL NUMBER		CUSTOMER	
								SEE TABLE		GENERAL MARKET	
DOCUMENT STATUS				P1		RELEASE DATE		2021/10/11 11:53:31		SHEET NUMBER	
								27 OF 45			

PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION				
								A	B	F	M	P
87914-4611	-----	-----	-----	-----	46	-----	1	58.42	55.88	10.92	5.84	2.79
87914-4621	-----	-----	-----	-----	46	-----	1	58.42	55.88	12.25	7.00	2.96
87914-4612	-----	-----	-----	-----	46	-----	2	58.42	55.88	10.92	5.84	2.79
87914-4622	-----	-----	-----	-----	46	-----	2	58.42	55.88	12.25	7.00	2.96
87914-4613	-----	-----	-----	-----	46	-----	3	58.42	55.88	10.92	5.84	2.79
87914-4623	-----	-----	-----	-----	46	-----	3	58.42	55.88	12.25	7.00	2.96
87914-4614	-----	-----	-----	-----	46	-----	4	58.42	55.88	10.92	5.84	2.79
87914-4624	-----	-----	-----	-----	46	-----	4	58.42	55.88	12.25	7.00	2.96
87914-4615	-----	-----	-----	-----	46	-----	5	58.42	55.88	10.92	5.84	2.79
87914-4625	-----	-----	-----	-----	46	-----	5	58.42	55.88	12.25	7.00	2.96
87914-4616	-----	-----	-----	-----	46	-----	6	58.42	55.88	10.92	5.84	2.79
87914-4617	-----	-----	-----	-----	46	-----	6	58.42	55.88	10.92	5.84	2.79
87914-4626	-----	-----	-----	-----	46	-----	6	58.42	55.88	12.25	7.00	2.96
87914-4627	-----	-----	-----	-----	46	-----	6	58.42	55.88	12.25	7.00	2.96
87914-4601	-----	-----	-----	-----	46	-----	4	58.42	55.88	13.21	8.13	2.79
87914-4602	-----	-----	-----	-----	46	-----	5	58.42	55.88	13.21	8.13	2.79
87914-4603	-----	-----	-----	-----	46	-----	6	58.42	55.88	13.21	8.13	2.79
87914-4604	-----	-----	-----	-----	46	-----	4	58.42	55.88	11.11	6.10	2.72
87914-4605	-----	-----	-----	-----	46	-----	5	58.42	55.88	11.11	6.10	2.72
87914-4606	-----	-----	-----	-----	46	-----	6	58.42	55.88	11.11	6.10	2.72
87914-4607	-----	-----	-----	-----	46	-----	6	58.42	55.88	11.11	6.10	2.72

Ⓟ

Ⓟ

Ⓟ

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											
DIMENSION UNITS		SCALE		CURRENT REV DESC: BRIGHT TIN PHASE OUT							
mm		NTS									
GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 679909		DRWN: AKUMAR19		2021/06/29		2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H	
				CHK'D: MRAMAKRISHNA		2021/10/11					
				APPR: MRAMAKRISHNA		2021/10/11		PRODUCT CUSTOMER DRAWING			
4 PLACES ±				INITIAL REVISION:		DRWN: YLQIAO		2005/01/17		DOCUMENT NUMBER	
3 PLACES ±				DRWN: YLQIAO		2005/01/25		SD-87914-013		DOC TYPE	
2 PLACES ± 0.2				APPR: SLOW		2005/01/25		PSD		DOC PART	
1 PLACE ±				THIRD ANGLE PROJECTION		DRAWING		SERIES		REVISION	
0 PLACES ±				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		A3-SIZE		87914		D22	
ANGULAR TOL ± 3.0°				MATERIAL NUMBER		CUSTOMER		SEE TABLE		GENERAL MARKET	
SHEET NUMBER				28 OF 45							


DOCUMENT STATUS	P1	RELEASE DATE	2021/10/11	11:53:31
-----------------	----	--------------	------------	----------

PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION				
								A	B	F	M	P
87914-4811	-----	-----	-----	-----	48	-----	1	60.96	58.42	10.92	5.84	2.79
87914-4821	-----	-----	-----	-----	48	-----	1	60.96	58.42	12.25	7.00	2.96
87914-4812	-----	-----	-----	-----	48	-----	2	60.96	58.42	10.92	5.84	2.79
87914-4822	-----	-----	-----	-----	48	-----	2	60.96	58.42	12.25	7.00	2.96
87914-4813	-----	-----	-----	-----	48	-----	3	60.96	58.42	10.92	5.84	2.79
87914-4823	-----	-----	-----	-----	48	-----	3	60.96	58.42	12.25	7.00	2.96
87914-4814	-----	-----	-----	-----	48	-----	4	60.96	58.42	10.92	5.84	2.79
87914-4824	-----	-----	-----	-----	48	-----	4	60.96	58.42	12.25	7.00	2.96
87914-4815	-----	-----	-----	-----	48	-----	5	60.96	58.42	10.92	5.84	2.79
87914-4825	-----	-----	-----	-----	48	-----	5	60.96	58.42	12.25	7.00	2.96
87914-4816	-----	-----	-----	-----	48	-----	6	60.96	58.42	10.92	5.84	2.79
87914-4817	-----	-----	-----	-----	48	-----	6	60.96	58.42	10.92	5.84	2.79
87914-4826	-----	-----	-----	-----	48	-----	6	60.96	58.42	12.25	7.00	2.96
87914-4827	-----	-----	-----	-----	48	-----	6	60.96	58.42	12.25	7.00	2.96
87914-4801	-----	-----	-----	-----	48	-----	4	60.96	58.42	13.21	8.13	2.79
87914-4802	-----	-----	-----	-----	48	-----	5	60.96	58.42	13.21	8.13	2.79
87914-4803	-----	-----	-----	-----	48	-----	6	60.96	58.42	13.21	8.13	2.79
87914-4804	-----	-----	-----	-----	48	-----	4	60.96	58.42	11.11	6.10	2.72
87914-4805	-----	-----	-----	-----	48	-----	5	60.96	58.42	11.11	6.10	2.72
87914-4806	-----	-----	-----	-----	48	-----	6	60.96	58.42	11.11	6.10	2.72
87914-4807	-----	-----	-----	-----	48	-----	6	60.96	58.42	11.11	6.10	2.72

⊘D22

⊘D22

⊘D22

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											
DIMENSION UNITS		SCALE		CURRENT REV DESC: BRIGHT TIN PHASE OUT							
mm		NTS									
GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 679909		DRWN: AKUMAR19		2021/06/29		2.54MM PITCH	
				CHK'D: MRAMAKRISHNA		2021/10/11				DUAL ROW HEADER SINGLE WAFER, T/H	
				APPR: MRAMAKRISHNA		2021/10/11				PRODUCT CUSTOMER DRAWING	
4 PLACES ±				INITIAL REVISION:		DRWN: YLQIAO		2005/01/17		DOCUMENT NUMBER	
3 PLACES ±				DRWN: YLQIAO		2005/01/25		SD-87914-013		DOC TYPE DOC PART REVISION	
2 PLACES ± 0.2				APPR: SLOW		2005/01/25		PSD		000 D22	
1 PLACE ±				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION		DRAWING		SERIES	
0 PLACES ±						A3-SIZE		87914		MATERIAL NUMBER CUSTOMER SHEET NUMBER	
ANGULAR TOL ± 3.0°								SEE TABLE		GENERAL MARKET 29 OF 45	



DOCUMENT STATUS	P1	RELEASE DATE	2021/10/11	11:53:31
-----------------	----	--------------	------------	----------

PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION				
								A	B	F	M	P
87914-0002	-----	-----	-----	-----	50	-----	8	63.50	60.96	18.54	11.58	4.47
87914-5011	-----	-----	-----	-----	50	-----	1	63.50	60.96	10.92	5.84	2.79
87914-5021	-----	-----	-----	-----	50	-----	1	63.50	60.96	12.25	7.00	2.96
87914-5012	-----	-----	-----	-----	50	-----	2	63.50	60.96	10.92	5.84	2.79
87914-5022	-----	-----	-----	-----	50	-----	2	63.50	60.96	12.25	7.00	2.96
87914-5013	-----	-----	-----	-----	50	-----	3	63.50	60.96	10.92	5.84	2.79
87914-5023	-----	-----	-----	-----	50	-----	3	63.50	60.96	12.25	7.00	2.96
87914-5014	-----	-----	-----	-----	50	-----	4	63.50	60.96	10.92	5.84	2.79
87914-5024	-----	-----	-----	-----	50	-----	4	63.50	60.96	12.25	7.00	2.96
87914-5015	-----	-----	-----	-----	50	-----	5	63.50	60.96	10.92	5.84	2.79
87914-5025	-----	-----	-----	-----	50	-----	5	63.50	60.96	12.25	7.00	2.96
87914-5016	-----	-----	-----	-----	50	-----	6	63.50	60.96	10.92	5.84	2.79
87914-5017	-----	-----	-----	-----	50	-----	6	63.50	60.96	10.92	5.84	2.79
87914-5026	-----	-----	-----	-----	50	-----	6	63.50	60.96	12.25	7.00	2.96
87914-5027	-----	-----	-----	-----	50	-----	6	63.50	60.96	12.25	7.00	2.96
87914-5001	-----	-----	-----	-----	50	-----	4	63.50	60.96	13.21	8.13	2.79
87914-5002	-----	-----	-----	-----	50	-----	5	63.50	60.96	13.21	8.13	2.79
87914-5003	-----	-----	-----	-----	50	-----	6	63.50	60.96	13.21	8.13	2.79
87914-5004	-----	-----	-----	-----	50	-----	4	63.50	60.96	11.11	6.10	2.72
87914-5005	-----	-----	-----	-----	50	-----	5	63.50	60.96	11.11	6.10	2.72
87914-5006	-----	-----	-----	-----	50	-----	6	63.50	60.96	11.11	6.10	2.72
87914-5007	-----	-----	-----	-----	50	-----	6	63.50	60.96	11.11	6.10	2.72

D22

D22

D22



THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											
DIMENSION UNITS		SCALE		CURRENT REV DESC: BRIGHT TIN PHASE OUT							
mm		NTS									
GENERAL TOLERANCES (UNLESS SPECIFIED)											
		MM		INCH							
4 PLACES		±		±							
3 PLACES		±		±							
2 PLACES		± 0.2		±							
1 PLACE		±		±							
0 PLACES		±		±							
ANGULAR TOL ± 3.0°											
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES		SHEET NUMBER	
						A3-SIZE		87914		30 OF 45	

DOCUMENT STATUS	P1	RELEASE DATE	2021/10/11	11:53:31
-----------------	----	--------------	------------	----------

PART NO FOR BULK PACKAGING	PART NO FOR BULK PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION				
									A	B	F	M	P
87914-5211	-----	-----	-----	-----	-----	52	-----	1	66.04	63.50	10.92	5.84	2.79
87914-5221	-----	-----	-----	-----	-----	52	-----	1	66.04	63.50	12.25	7.00	2.96
87914-5212	-----	-----	-----	-----	-----	52	-----	2	66.04	63.50	10.92	5.84	2.79
87914-5222	-----	-----	-----	-----	-----	52	-----	2	66.04	63.50	12.25	7.00	2.96
87914-5213	-----	-----	-----	-----	-----	52	-----	3	66.04	63.50	10.92	5.84	2.79
87914-5223	-----	-----	-----	-----	-----	52	-----	3	66.04	63.50	12.25	7.00	2.96
87914-5214	-----	-----	-----	-----	-----	52	-----	4	66.04	63.50	10.92	5.84	2.79
87914-5224	-----	-----	-----	-----	-----	52	-----	4	66.04	63.50	12.25	7.00	2.96
87914-5215	-----	-----	-----	-----	-----	52	-----	5	66.04	63.50	10.92	5.84	2.79
87914-5225	-----	-----	-----	-----	-----	52	-----	5	66.04	63.50	12.25	7.00	2.96
87914-5216	-----	-----	-----	-----	-----	52	-----	6	66.04	63.50	10.92	5.84	2.79
87914-5226	-----	-----	-----	-----	-----	52	-----	6	66.04	63.50	12.25	7.00	2.96
87914-5227	-----	-----	-----	-----	-----	52	-----	6	66.04	63.50	12.25	7.00	2.96
-----	87914-5201	-----	-----	-----	-----	52	-----	4	66.04	63.50	13.21	8.13	2.79
-----	87914-5202	-----	-----	-----	-----	52	-----	5	66.04	63.50	13.21	8.13	2.79
-----	87914-5203	-----	-----	-----	-----	52	-----	6	66.04	63.50	13.21	8.13	2.79
-----	87914-5204	-----	-----	-----	-----	52	-----	4	66.04	63.50	11.11	6.10	2.72
-----	87914-5205	-----	-----	-----	-----	52	-----	5	66.04	63.50	11.11	6.10	2.72
-----	87914-5206	-----	-----	-----	-----	52	-----	6	66.04	63.50	11.11	6.10	2.72
-----	87914-5207	-----	-----	-----	-----	52	-----	6	66.04	63.50	11.11	6.10	2.72

D22

D22



THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									
DIMENSION UNITS		SCALE		CURRENT REV DESC: BRIGHT TIN PHASE OUT					
mm		NTS							
GENERAL TOLERANCES (UNLESS SPECIFIED)									
		MM		INCH		EC NO: 679909 DRWN: AKUMAR19 2021/06/29 CHK'D: MRAMAKRISHNA 2021/10/11 APPR: MRAMAKRISHNA 2021/10/11 INITIAL REVISION: DRWN: YLQIAO 2005/01/17 APPR: SCLOW 2005/01/25			
4 PLACES	±	±	±	±					
3 PLACES	±	±	±	±					
2 PLACES	±	0.2	±	±					
1 PLACE	±	±	±	±					
0 PLACES	±	±	±	±					
ANGULAR TOL		± 3.0°							
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES	
						A3-SIZE		87914	
DOCUMENT NUMBER				DOC TYPE		DOC PART		REVISION	
SD-87914-013				PSD		000		D22	
MATERIAL NUMBER				CUSTOMER		SHEET NUMBER			
SEE TABLE				GENERAL MARKET		31 OF 45			

DOCUMENT STATUS	P1	RELEASE DATE	2021/10/11	11:53:31
-----------------	----	--------------	------------	----------

PART NO FOR BULK PACKAGING	PART NO FOR BULK PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION				
									A	B	F	M	P
87914-5411	-----	-----	-----	-----	-----	54	-----	1	68.58	66.04	10.92	5.84	2.79
87914-5421	-----	-----	-----	-----	-----	54	-----	1	68.58	66.04	12.25	7.00	2.96
87914-5412	-----	-----	-----	-----	-----	54	-----	2	68.58	66.04	10.92	5.84	2.79
87914-5422	-----	-----	-----	-----	-----	54	-----	2	68.58	66.04	12.25	7.00	2.96
87914-5413	-----	-----	-----	-----	-----	54	-----	3	68.58	66.04	10.92	5.84	2.79
87914-5423	-----	-----	-----	-----	-----	54	-----	3	68.58	66.04	12.25	7.00	2.96
87914-5414	-----	-----	-----	-----	-----	54	-----	4	68.58	66.04	10.92	5.84	2.79
87914-5424	-----	-----	-----	-----	-----	54	-----	4	68.58	66.04	12.25	7.00	2.96
87914-5415	-----	-----	-----	-----	-----	54	-----	5	68.58	66.04	10.92	5.84	2.79
87914-5425	-----	-----	-----	-----	-----	54	-----	5	68.58	66.04	12.25	7.00	2.96
87914-5416	-----	-----	-----	-----	-----	54	-----	6	68.58	66.04	10.92	5.84	2.79
87914-5426	-----	-----	-----	-----	-----	54	-----	6	68.58	66.04	12.25	7.00	2.96
87914-5427	-----	-----	-----	-----	-----	54	-----	6	68.58	66.04	12.25	7.00	2.96
-----	87914-5401	-----	-----	-----	-----	54	-----	4	68.58	66.04	13.21	8.13	2.79
-----	87914-5402	-----	-----	-----	-----	54	-----	5	68.58	66.04	13.21	8.13	2.79
-----	87914-5403	-----	-----	-----	-----	54	-----	6	68.58	66.04	13.21	8.13	2.79
-----	87914-5404	-----	-----	-----	-----	54	-----	4	68.58	66.04	11.11	6.10	2.72
-----	87914-5405	-----	-----	-----	-----	54	-----	5	68.58	66.04	11.11	6.10	2.72
-----	87914-5406	-----	-----	-----	-----	54	-----	6	68.58	66.04	11.11	6.10	2.72
-----	87914-5407	-----	-----	-----	-----	54	-----	6	68.58	66.04	11.11	6.10	2.72

D22

D22


THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									
DIMENSION UNITS		SCALE		CURRENT REV DESC: BRIGHT TIN PHASE OUT					
mm		NTS							
GENERAL TOLERANCES (UNLESS SPECIFIED)									
		MM		INCH		EC NO: 679909 DRWN: AKUMAR19 2021/06/29 CHK'D: MRAMAKRISHNA 2021/10/11 APPR: MRAMAKRISHNA 2021/10/11 INITIAL REVISION: DRWN: YLQIAO 2005/01/17 APPR: SCLOW 2005/01/25			
4 PLACES	±	±	±	±					
3 PLACES	±	±	±	±					
2 PLACES	±	0.2	±	±					
1 PLACE	±	±	±	±					
0 PLACES	±	±	±	±					
ANGULAR TOL		± 3.0°							
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES	
						A3-SIZE		87914	
DOCUMENT NUMBER				DOC TYPE		DOC PART		REVISION	
SD-87914-013				PSD		000		D22	
MATERIAL NUMBER				CUSTOMER		SHEET NUMBER			
SEE TABLE				GENERAL MARKET		32 OF 45			

DOCUMENT STATUS	P1	RELEASE DATE	2021/10/11	11:53:31
-----------------	----	--------------	------------	----------

PART NO FOR BULK PACKAGING	PART NO FOR BULK PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION				
									A	B	F	M	P
87914-5611	-----	-----	-----	-----	-----	56	-----	1	71.12	68.58	10.92	5.84	2.79
87914-5621	-----	-----	-----	-----	-----	56	-----	1	71.12	68.58	12.25	7.00	2.96
87914-5612	-----	-----	-----	-----	-----	56	-----	2	71.12	68.58	10.92	5.84	2.79
87914-5622	-----	-----	-----	-----	-----	56	-----	2	71.12	68.58	12.25	7.00	2.96
87914-5613	-----	-----	-----	-----	-----	56	-----	3	71.12	68.58	10.92	5.84	2.79
87914-5623	-----	-----	-----	-----	-----	56	-----	3	71.12	68.58	12.25	7.00	2.96
87914-5614	-----	-----	-----	-----	-----	56	-----	4	71.12	68.58	10.92	5.84	2.79
87914-5624	-----	-----	-----	-----	-----	56	-----	4	71.12	68.58	12.25	7.00	2.96
87914-5615	-----	-----	-----	-----	-----	56	-----	5	71.12	68.58	10.92	5.84	2.79
87914-5625	-----	-----	-----	-----	-----	56	-----	5	71.12	68.58	12.25	7.00	2.96
87914-5616	-----	-----	-----	-----	-----	56	-----	6	71.12	68.58	10.92	5.84	2.79
87914-5626	-----	-----	-----	-----	-----	56	-----	6	71.12	68.58	12.25	7.00	2.96
87914-5627	-----	-----	-----	-----	-----	56	-----	6	71.12	68.58	12.25	7.00	2.96
-----	87914-5601	-----	-----	-----	-----	56	-----	4	71.12	68.58	13.21	8.13	2.79
-----	87914-5602	-----	-----	-----	-----	56	-----	5	71.12	68.58	13.21	8.13	2.79
-----	87914-5603	-----	-----	-----	-----	56	-----	6	71.12	68.58	13.21	8.13	2.79
-----	87914-5604	-----	-----	-----	-----	56	-----	4	71.12	68.58	11.11	6.10	2.72
-----	87914-5605	-----	-----	-----	-----	56	-----	5	71.12	68.58	11.11	6.10	2.72
-----	87914-5606	-----	-----	-----	-----	56	-----	6	71.12	68.58	11.11	6.10	2.72
-----	87914-5607	-----	-----	-----	-----	56	-----	6	71.12	68.58	11.11	6.10	2.72

D22

D22



THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											
DIMENSION UNITS		SCALE		CURRENT REV DESC: BRIGHT TIN PHASE OUT							
mm		NTS									
GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 679909		DRWN: AKUMAR19		2021/06/29		2.54MM PITCH	
				CHK'D: MRAMAKRISHNA		2021/10/11		2021/10/11		DUAL ROW HEADER SINGLE WAFER, T/H	
				APPR: MRAMAKRISHNA		2021/10/11		2021/10/11		PRODUCT CUSTOMER DRAWING	
4 PLACES ±				INITIAL REVISION:		DRWN: YLQIAO		2005/01/17		DOCUMENT NUMBER	
3 PLACES ±				DRWN: YLQIAO		2005/01/25		2005/01/25		SD-87914-013	
2 PLACES ± 0.2				APPR: SCLOW						DOC TYPE DOC PART REVISION	
1 PLACE ±				THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER	
0 PLACES ±				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		A3-SIZE		87914		CUSTOMER	
ANGULAR TOL ± 3.0°										SEE TABLE	
										GENERAL MARKET	
										SHEET NUMBER	
										33 OF 45	

DOCUMENT STATUS	P1	RELEASE DATE	2021/10/11	11:53:31
-----------------	----	--------------	------------	----------

PART NO FOR BULK PACKAGING	PART NO FOR BULK PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION				
									A	B	F	M	P
87914-5811	-----	-----	-----	-----	-----	58	-----	1	73.66	71.12	10.92	5.84	2.79
87914-5821	-----	-----	-----	-----	-----	58	-----	1	73.66	71.12	12.25	7.00	2.96
87914-5812	-----	-----	-----	-----	-----	58	-----	2	73.66	71.12	10.92	5.84	2.79
87914-5822	-----	-----	-----	-----	-----	58	-----	2	73.66	71.12	12.25	7.00	2.96
87914-5813	-----	-----	-----	-----	-----	58	-----	3	73.66	71.12	10.92	5.84	2.79
87914-5823	-----	-----	-----	-----	-----	58	-----	3	73.66	71.12	12.25	7.00	2.96
87914-5814	-----	-----	-----	-----	-----	58	-----	4	73.66	71.12	10.92	5.84	2.79
87914-5824	-----	-----	-----	-----	-----	58	-----	4	73.66	71.12	12.25	7.00	2.96
87914-5815	-----	-----	-----	-----	-----	58	-----	5	73.66	71.12	10.92	5.84	2.79
87914-5825	-----	-----	-----	-----	-----	58	-----	5	73.66	71.12	12.25	7.00	2.96
87914-5816	-----	-----	-----	-----	-----	58	-----	6	73.66	71.12	10.92	5.84	2.79
87914-5826	-----	-----	-----	-----	-----	58	-----	6	73.66	71.12	12.25	7.00	2.96
87914-5827	-----	-----	-----	-----	-----	58	-----	6	73.66	71.12	12.25	7.00	2.96
-----	87914-5801	-----	-----	-----	-----	58	-----	4	73.66	71.12	13.21	8.13	2.79
-----	87914-5802	-----	-----	-----	-----	58	-----	5	73.66	71.12	13.21	8.13	2.79
-----	87914-5803	-----	-----	-----	-----	58	-----	6	73.66	71.12	13.21	8.13	2.79
-----	87914-5804	-----	-----	-----	-----	58	-----	4	73.66	71.12	11.11	6.10	2.72
-----	87914-5805	-----	-----	-----	-----	58	-----	5	73.66	71.12	11.11	6.10	2.72
-----	87914-5806	-----	-----	-----	-----	58	-----	6	73.66	71.12	11.11	6.10	2.72
-----	87914-5807	-----	-----	-----	-----	58	-----	6	73.66	71.12	11.11	6.10	2.72

D22

D22



THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											
DIMENSION UNITS		SCALE		CURRENT REV DESC: BRIGHT TIN PHASE OUT							
mm		NTS									
GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 679909		DRWN: AKUMAR19		2021/06/29		2.54MM PITCH	
				CHK'D: MRAMAKRISHNA		2021/10/11				DUAL ROW HEADER SINGLE WAFER, T/H	
				APPR: MRAMAKRISHNA		2021/10/11				PRODUCT CUSTOMER DRAWING	
4 PLACES ±				INITIAL REVISION:		DRWN: YLQIAO		2005/01/17		DOCUMENT NUMBER	
3 PLACES ±				DRWN: YLQIAO		2005/01/25		2005/01/25		SD-87914-013	
2 PLACES ± 0.2				APPR: SLOW						DOC TYPE	
1 PLACE ±										PSD	
0 PLACES ±										DOC PART	
ANGULAR TOL ± 3.0°				THIRD ANGLE PROJECTION		DRAWING		SERIES		REVISION	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS						A3-SIZE		87914		D22	
				MATERIAL NUMBER		CUSTOMER		SHEET NUMBER			
				SEE TABLE		GENERAL MARKET		34 OF 45			

DOCUMENT STATUS	P1	RELEASE DATE	2021/10/11	11:53:31
-----------------	----	--------------	------------	----------

PART NO FOR BULK PACKAGING	PART NO FOR BULK PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION				
									A	B	F	M	P
87914-6011	-----	-----	-----	-----	-----	60	-----	1	76.20	73.66	10.92	5.84	2.79
87914-6021	-----	-----	-----	-----	-----	60	-----	1	76.20	73.66	12.25	7.00	2.96
87914-6012	-----	-----	-----	-----	-----	60	-----	2	76.20	73.66	10.92	5.84	2.79
87914-6022	-----	-----	-----	-----	-----	60	-----	2	76.20	73.66	12.25	7.00	2.96
87914-6013	-----	-----	-----	-----	-----	60	-----	3	76.20	73.66	10.92	5.84	2.79
87914-6023	-----	-----	-----	-----	-----	60	-----	3	76.20	73.66	12.25	7.00	2.96
87914-6014	-----	-----	-----	-----	-----	60	-----	4	76.20	73.66	10.92	5.84	2.79
87914-6024	-----	-----	-----	-----	-----	60	-----	4	76.20	73.66	12.25	7.00	2.96
87914-6015	-----	-----	-----	-----	-----	60	-----	5	76.20	73.66	10.92	5.84	2.79
87914-6025	-----	-----	-----	-----	-----	60	-----	5	76.20	73.66	12.25	7.00	2.96
87914-6016	-----	-----	-----	-----	-----	60	-----	6	76.20	73.66	10.92	5.84	2.79
87914-6026	-----	-----	-----	-----	-----	60	-----	6	76.20	73.66	12.25	7.00	2.96
87914-6027	-----	-----	-----	-----	-----	60	-----	6	76.20	73.66	12.25	7.00	2.96
-----	87914-6001	-----	-----	-----	-----	60	-----	4	76.20	73.66	13.21	8.13	2.79
-----	87914-6002	-----	-----	-----	-----	60	-----	5	76.20	73.66	13.21	8.13	2.79
-----	87914-6003	-----	-----	-----	-----	60	-----	6	76.20	73.66	13.21	8.13	2.79
-----	87914-6004	-----	-----	-----	-----	60	-----	4	76.20	73.66	11.11	6.10	2.72
-----	87914-6005	-----	-----	-----	-----	60	-----	5	76.20	73.66	11.11	6.10	2.72
-----	87914-6006	-----	-----	-----	-----	60	-----	6	76.20	73.66	11.11	6.10	2.72
-----	87914-6007	-----	-----	-----	-----	60	-----	6	76.20	73.66	11.11	6.10	2.72

D22

D22



THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									
DIMENSION UNITS		SCALE		CURRENT REV DESC: BRIGHT TIN PHASE OUT					
mm		NTS							
GENERAL TOLERANCES (UNLESS SPECIFIED)									
		MM		INCH		EC NO: 679909 DRWN: AKUMAR19 2021/06/29 CHK'D: MRAMAKRISHNA 2021/10/11 APPR: MRAMAKRISHNA 2021/10/11 INITIAL REVISION: DRWN: YLQIAO 2005/01/17 APPR: SCLOW 2005/01/25			
4 PLACES	±	±	±	±					
3 PLACES	±	±	±	±					
2 PLACES	±	0.2	±	±					
1 PLACE	±	±	±	±					
0 PLACES	±	±	±	±					
ANGULAR TOL		± 3.0°							
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES	
						A3-SIZE		87914	
DOCUMENT NUMBER				DOC TYPE		DOC PART		REVISION	
SD-87914-013				PSD		000		D22	
MATERIAL NUMBER				CUSTOMER		SHEET NUMBER			
SEE TABLE				GENERAL MARKET		35 OF 45			

DOCUMENT STATUS	P1	RELEASE DATE	2021/10/11	11:53:31
-----------------	----	--------------	------------	----------

PART NO FOR BULK PACKAGING	PART NO FOR BULK PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION				
									A	B	F	M	P
87914-6211	-----	-----	-----	-----	-----	62	-----	1	78.74	76.20	10.92	5.84	2.79
87914-6221	-----	-----	-----	-----	-----	62	-----	1	78.74	76.20	12.25	7.00	2.96
87914-6212	-----	-----	-----	-----	-----	62	-----	2	78.74	76.20	10.92	5.84	2.79
87914-6222	-----	-----	-----	-----	-----	62	-----	2	78.74	76.20	12.25	7.00	2.96
87914-6213	-----	-----	-----	-----	-----	62	-----	3	78.74	76.20	10.92	5.84	2.79
87914-6223	-----	-----	-----	-----	-----	62	-----	3	78.74	76.20	12.25	7.00	2.96
87914-6214	-----	-----	-----	-----	-----	62	-----	4	78.74	76.20	10.92	5.84	2.79
87914-6224	-----	-----	-----	-----	-----	62	-----	4	78.74	76.20	12.25	7.00	2.96
87914-6215	-----	-----	-----	-----	-----	62	-----	5	78.74	76.20	10.92	5.84	2.79
87914-6225	-----	-----	-----	-----	-----	62	-----	5	78.74	76.20	12.25	7.00	2.96
87914-6216	-----	-----	-----	-----	-----	62	-----	6	78.74	76.20	10.92	5.84	2.79
87914-6226	-----	-----	-----	-----	-----	62	-----	6	78.74	76.20	12.25	7.00	2.96
87914-6227	-----	-----	-----	-----	-----	62	-----	6	78.74	76.20	12.25	7.00	2.96
-----	87914-6201	-----	-----	-----	-----	62	-----	4	78.74	76.20	13.21	8.13	2.79
-----	87914-6202	-----	-----	-----	-----	62	-----	5	78.74	76.20	13.21	8.13	2.79
-----	87914-6203	-----	-----	-----	-----	62	-----	6	78.74	76.20	13.21	8.13	2.79
-----	87914-6204	-----	-----	-----	-----	62	-----	4	78.74	76.20	11.11	6.10	2.72
-----	87914-6205	-----	-----	-----	-----	62	-----	5	78.74	76.20	11.11	6.10	2.72
-----	87914-6206	-----	-----	-----	-----	62	-----	6	78.74	76.20	11.11	6.10	2.72
-----	87914-6207	-----	-----	-----	-----	62	-----	6	78.74	76.20	11.11	6.10	2.72

D22

D22



THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									
DIMENSION UNITS		SCALE		CURRENT REV DESC: BRIGHT TIN PHASE OUT					
mm		NTS							
GENERAL TOLERANCES (UNLESS SPECIFIED)									
		MM		INCH		EC NO: 679909 DRWN: AKUMAR19 2021/06/29 CHK'D: MRAMAKRISHNA 2021/10/11 APPR: MRAMAKRISHNA 2021/10/11 INITIAL REVISION: DRWN: YLQIAO 2005/01/17 APPR: SCLOW 2005/01/25			
4 PLACES	±	±	±	±					
3 PLACES	±	±	±	±					
2 PLACES	±	0.2	±	±					
1 PLACE	±	±	±	±					
0 PLACES	±	±	±	±					
ANGULAR TOL		± 3.0°							
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES	
						A3-SIZE		87914	
DOCUMENT NUMBER				DOC TYPE		DOC PART		REVISION	
SD-87914-013				PSD		000		D22	
MATERIAL NUMBER				CUSTOMER		SHEET NUMBER			
SEE TABLE				GENERAL MARKET		36 OF 45			

DOCUMENT STATUS	P1	RELEASE DATE	2021/10/11	11:53:31
-----------------	----	--------------	------------	----------

PART NO FOR BULK PACKAGING	PART NO FOR BULK PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION				
									A	B	F	M	P
87914-6411	-----	-----	-----	-----	-----	64	-----	1	81.28	78.74	10.92	5.84	2.79
87914-6421	-----	-----	-----	-----	-----	64	-----	1	81.28	78.74	12.25	7.00	2.96
87914-6412	-----	-----	-----	-----	-----	64	-----	2	81.28	78.74	10.92	5.84	2.79
87914-6422	-----	-----	-----	-----	-----	64	-----	2	81.28	78.74	12.25	7.00	2.96
87914-6413	-----	-----	-----	-----	-----	64	-----	3	81.28	78.74	10.92	5.84	2.79
87914-6423	-----	-----	-----	-----	-----	64	-----	3	81.28	78.74	12.25	7.00	2.96
87914-6414	-----	-----	-----	-----	-----	64	-----	4	81.28	78.74	10.92	5.84	2.79
87914-6424	-----	-----	-----	-----	-----	64	-----	4	81.28	78.74	12.25	7.00	2.96
87914-6415	-----	-----	-----	-----	-----	64	-----	5	81.28	78.74	10.92	5.84	2.79
87914-6425	-----	-----	-----	-----	-----	64	-----	5	81.28	78.74	12.25	7.00	2.96
87914-6416	-----	-----	-----	-----	-----	64	-----	6	81.28	78.74	10.92	5.84	2.79
87914-6426	-----	-----	-----	-----	-----	64	-----	6	81.28	78.74	12.25	7.00	2.96
87914-6427	-----	-----	-----	-----	-----	64	-----	6	81.28	78.74	12.25	7.00	2.96
-----	87914-6401	-----	-----	-----	-----	64	-----	4	81.28	78.74	13.21	8.13	2.79
-----	87914-6402	-----	-----	-----	-----	64	-----	5	81.28	78.74	13.21	8.13	2.79
-----	87914-6403	-----	-----	-----	-----	64	-----	6	81.28	78.74	13.21	8.13	2.79
-----	87914-6404	-----	-----	-----	-----	64	-----	4	81.28	78.74	11.11	6.10	2.72
-----	87914-6405	-----	-----	-----	-----	64	-----	5	81.28	78.74	11.11	6.10	2.72
-----	87914-6406	-----	-----	-----	-----	64	-----	6	81.28	78.74	11.11	6.10	2.72
-----	87914-6407	-----	-----	-----	-----	64	-----	6	81.28	78.74	11.11	6.10	2.72

D22

D22



THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											
DIMENSION UNITS		SCALE		CURRENT REV DESC: BRIGHT TIN PHASE OUT							
mm		NTS									
GENERAL TOLERANCES (UNLESS SPECIFIED)											
		MM		INCH		EC NO: 679909 DRWN: AKUMAR19 2021/06/29 CHK'D: MRAMAKRISHNA 2021/10/11 APPR: MRAMAKRISHNA 2021/10/11 INITIAL REVISION: DRWN: YLQIAO 2005/01/17 APPR: SCLOW 2005/01/25					
4 PLACES	±	±	±	PRODUCT CUSTOMER DRAWING							
3 PLACES	±	±	±	DOCUMENT NUMBER							
2 PLACES	±	0.2	±	SD-87914-013							
1 PLACE	±	±	±	DOC TYPE							
0 PLACES	±	±	±	PSD							
ANGULAR TOL		± 3.0°		THIRD ANGLE PROJECTION		DRAWING		SERIES			
						A3-SIZE		87914			
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				MATERIAL NUMBER		CUSTOMER		SHEET NUMBER			
				SEE TABLE		GENERAL MARKET		37 OF 45			

DOCUMENT STATUS	P1	RELEASE DATE	2021/10/11	11:53:31
-----------------	----	--------------	------------	----------

PART NO FOR BULK PACKAGING	PART NO FOR BULK PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION				
									A	B	F	M	P
87914-6611	-----	-----	-----	-----	-----	66	-----	1	83.82	81.28	10.92	5.84	2.79
87914-6621	-----	-----	-----	-----	-----	66	-----	1	83.82	81.28	12.25	7.00	2.96
87914-6612	-----	-----	-----	-----	-----	66	-----	2	83.82	81.28	10.92	5.84	2.79
87914-6622	-----	-----	-----	-----	-----	66	-----	2	83.82	81.28	12.25	7.00	2.96
87914-6613	-----	-----	-----	-----	-----	66	-----	3	83.82	81.28	10.92	5.84	2.79
87914-6623	-----	-----	-----	-----	-----	66	-----	3	83.82	81.28	12.25	7.00	2.96
87914-6614	-----	-----	-----	-----	-----	66	-----	4	83.82	81.28	10.92	5.84	2.79
87914-6624	-----	-----	-----	-----	-----	66	-----	4	83.82	81.28	12.25	7.00	2.96
87914-6615	-----	-----	-----	-----	-----	66	-----	5	83.82	81.28	10.92	5.84	2.79
87914-6625	-----	-----	-----	-----	-----	66	-----	5	83.82	81.28	12.25	7.00	2.96
87914-6616	-----	-----	-----	-----	-----	66	-----	6	83.82	81.28	10.92	5.84	2.79
87914-6626	-----	-----	-----	-----	-----	66	-----	6	83.82	81.28	12.25	7.00	2.96
87914-6627	-----	-----	-----	-----	-----	66	-----	6	83.82	81.28	12.25	7.00	2.96
-----	87914-6601	-----	-----	-----	-----	66	-----	4	83.82	81.28	13.21	8.13	2.79
-----	87914-6602	-----	-----	-----	-----	66	-----	5	83.82	81.28	13.21	8.13	2.79
-----	87914-6603	-----	-----	-----	-----	66	-----	6	83.82	81.28	13.21	8.13	2.79
-----	87914-6604	-----	-----	-----	-----	66	-----	4	83.82	81.28	11.11	6.10	2.72
-----	87914-6605	-----	-----	-----	-----	66	-----	5	83.82	81.28	11.11	6.10	2.72
-----	87914-6606	-----	-----	-----	-----	66	-----	6	83.82	81.28	11.11	6.10	2.72
-----	87914-6607	-----	-----	-----	-----	66	-----	6	83.82	81.28	11.11	6.10	2.72

D22

D22



THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									
DIMENSION UNITS		SCALE		CURRENT REV DESC: BRIGHT TIN PHASE OUT					
mm		NTS							
GENERAL TOLERANCES (UNLESS SPECIFIED)									
		MM		INCH		EC NO: 679909 DRWN: AKUMAR19 2021/06/29 CHK'D: MRAMAKRISHNA 2021/10/11 APPR: MRAMAKRISHNA 2021/10/11 INITIAL REVISION: DRWN: YLQIAO 2005/01/17 APPR: SLOW 2005/01/25			
4 PLACES	±	±	±						
3 PLACES	±	±	±						
2 PLACES	±	0.2	±						
1 PLACE	±	±	±						
0 PLACES	±	±	±						
ANGULAR TOL		± 3.0°							
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES	
						A3-SIZE		87914	
DOCUMENT NUMBER				DOC TYPE		DOC PART		REVISION	
SD-87914-013				PSD		000		D22	
MATERIAL NUMBER				CUSTOMER		SHEET NUMBER			
SEE TABLE				GENERAL MARKET		38 OF 45			

DOCUMENT STATUS	P1	RELEASE DATE	2021/10/11	11:53:31
-----------------	----	--------------	------------	----------

PART NO FOR BULK PACKAGING	PART NO FOR BULK PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION				
									A	B	F	M	P
87914-6811	-----	-----	-----	-----	-----	68	-----	1	86.36	83.82	10.92	5.84	2.79
87914-6821	-----	-----	-----	-----	-----	68	-----	1	86.36	83.82	12.25	7.00	2.96
87914-6812	-----	-----	-----	-----	-----	68	-----	2	86.36	83.82	10.92	5.84	2.79
87914-6822	-----	-----	-----	-----	-----	68	-----	2	86.36	83.82	12.25	7.00	2.96
87914-6813	-----	-----	-----	-----	-----	68	-----	3	86.36	83.82	10.92	5.84	2.79
87914-6823	-----	-----	-----	-----	-----	68	-----	3	86.36	83.82	12.25	7.00	2.96
87914-6814	-----	-----	-----	-----	-----	68	-----	4	86.36	83.82	10.92	5.84	2.79
87914-6824	-----	-----	-----	-----	-----	68	-----	4	86.36	83.82	12.25	7.00	2.96
87914-6815	-----	-----	-----	-----	-----	68	-----	5	86.36	83.82	10.92	5.84	2.79
87914-6825	-----	-----	-----	-----	-----	68	-----	5	86.36	83.82	12.25	7.00	2.96
87914-6816	-----	-----	-----	-----	-----	68	-----	6	86.36	83.82	10.92	5.84	2.79
87914-6826	-----	-----	-----	-----	-----	68	-----	6	86.36	83.82	12.25	7.00	2.96
87914-6827	-----	-----	-----	-----	-----	68	-----	6	86.36	83.82	12.25	7.00	2.96
-----	87914-6801	-----	-----	-----	-----	68	-----	4	86.36	83.82	13.21	8.13	2.79
-----	87914-6802	-----	-----	-----	-----	68	-----	5	86.36	83.82	13.21	8.13	2.79
-----	87914-6803	-----	-----	-----	-----	68	-----	6	86.36	83.82	13.21	8.13	2.79
-----	87914-6804	-----	-----	-----	-----	68	-----	4	86.36	83.82	11.11	6.10	2.72
-----	87914-6805	-----	-----	-----	-----	68	-----	5	86.36	83.82	11.11	6.10	2.72
-----	87914-6806	-----	-----	-----	-----	68	-----	6	86.36	83.82	11.11	6.10	2.72
-----	87914-6807	-----	-----	-----	-----	68	-----	6	86.36	83.82	11.11	6.10	2.72

D22

D22



THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											
DIMENSION UNITS		SCALE		CURRENT REV DESC: BRIGHT TIN PHASE OUT							
mm		NTS									
GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 679909		2021/06/29		2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H			
				DRWN: AKUMAR19		2021/10/11					
				CHK'D: MRAMAKRISHNA		2021/10/11		PRODUCT CUSTOMER DRAWING			
				APPR: MRAMAKRISHNA		2021/10/11					
				INITIAL REVISION:				DOCUMENT NUMBER		DOC TYPE	
				DRWN: YLQIAO		2005/01/17		SD-87914-013		PSD	
				APPR: SLOW		2005/01/25		000		D22	
ANGULAR TOL ± 3.0°				THIRD ANGLE PROJECTION		DRAWING		SERIES		SHEET NUMBER	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS						A3-SIZE		87914		39 OF 45	

DOCUMENT STATUS	P1	RELEASE DATE	2021/10/11	11:53:31
-----------------	----	--------------	------------	----------

PART NO FOR BULK PACKAGING	PART NO FOR BULK PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION				
									A	B	F	M	P
87914-7011	-----	-----	-----	-----	-----	70	-----	1	88.90	86.36	10.92	5.84	2.79
87914-7021	-----	-----	-----	-----	-----	70	-----	1	88.90	86.36	12.25	7.00	2.96
87914-7012	-----	-----	-----	-----	-----	70	-----	2	88.90	86.36	10.92	5.84	2.79
87914-7022	-----	-----	-----	-----	-----	70	-----	2	88.90	86.36	12.25	7.00	2.96
87914-7013	-----	-----	-----	-----	-----	70	-----	3	88.90	86.36	10.92	5.84	2.79
87914-7023	-----	-----	-----	-----	-----	70	-----	3	88.90	86.36	12.25	7.00	2.96
87914-7014	-----	-----	-----	-----	-----	70	-----	4	88.90	86.36	10.92	5.84	2.79
87914-7024	-----	-----	-----	-----	-----	70	-----	4	88.90	86.36	12.25	7.00	2.96
87914-7015	-----	-----	-----	-----	-----	70	-----	5	88.90	86.36	10.92	5.84	2.79
87914-7025	-----	-----	-----	-----	-----	70	-----	5	88.90	86.36	12.25	7.00	2.96
87914-7016	-----	-----	-----	-----	-----	70	-----	6	88.90	86.36	10.92	5.84	2.79
87914-7026	-----	-----	-----	-----	-----	70	-----	6	88.90	86.36	12.25	7.00	2.96
87914-7027	-----	-----	-----	-----	-----	70	-----	6	88.90	86.36	12.25	7.00	2.96
-----	87914-7001	-----	-----	-----	-----	70	-----	4	88.90	86.36	13.21	8.13	2.79
-----	87914-7002	-----	-----	-----	-----	70	-----	5	88.90	86.36	13.21	8.13	2.79
-----	87914-7003	-----	-----	-----	-----	70	-----	6	88.90	86.36	13.21	8.13	2.79
-----	87914-7004	-----	-----	-----	-----	70	-----	4	88.90	86.36	11.11	6.10	2.72
-----	87914-7005	-----	-----	-----	-----	70	-----	5	88.90	86.36	11.11	6.10	2.72
-----	87914-7006	-----	-----	-----	-----	70	-----	6	88.90	86.36	11.11	6.10	2.72
-----	87914-7007	-----	-----	-----	-----	70	-----	6	88.90	86.36	11.11	6.10	2.72

D22

D22



THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									
DIMENSION UNITS		SCALE		CURRENT REV DESC: BRIGHT TIN PHASE OUT					
mm		NTS							
GENERAL TOLERANCES (UNLESS SPECIFIED)									
		MM		INCH		EC NO: 679909 DRWN: AKUMAR19 2021/06/29 CHK'D: MRAMAKRISHNA 2021/10/11 APPR: MRAMAKRISHNA 2021/10/11 INITIAL REVISION: DRWN: YLQIAO 2005/01/17 APPR: SLOW 2005/01/25			
4 PLACES	±	±	±	±					
3 PLACES	±	±	±	±					
2 PLACES	±	0.2	±	±					
1 PLACE	±	±	±	±					
0 PLACES	±	±	±	±					
ANGULAR TOL		± 3.0°							
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES	
						A3-SIZE		87914	
DOCUMENT NUMBER				DOC TYPE		DOC PART		REVISION	
SD-87914-013				PSD		000		D22	
MATERIAL NUMBER				CUSTOMER		SHEET NUMBER			
SEE TABLE				GENERAL MARKET		40 OF 45			

DOCUMENT STATUS	P1	RELEASE DATE	2021/10/11	11:53:31
-----------------	----	--------------	------------	----------

PART NO FOR BULK PACKAGING	PART NO FOR BULK PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION				
									A	B	F	M	P
87914-7211	-----	-----	-----	-----	-----	72	-----	1	91.44	88.90	10.92	5.84	2.79
87914-7221	-----	-----	-----	-----	-----	72	-----	1	91.44	88.90	12.25	7.00	2.96
87914-7212	-----	-----	-----	-----	-----	72	-----	2	91.44	88.90	10.92	5.84	2.79
87914-7222	-----	-----	-----	-----	-----	72	-----	2	91.44	88.90	12.25	7.00	2.96
87914-7213	-----	-----	-----	-----	-----	72	-----	3	91.44	88.90	10.92	5.84	2.79
87914-7223	-----	-----	-----	-----	-----	72	-----	3	91.44	88.90	12.25	7.00	2.96
87914-7214	-----	-----	-----	-----	-----	72	-----	4	91.44	88.90	10.92	5.84	2.79
87914-7224	-----	-----	-----	-----	-----	72	-----	4	91.44	88.90	12.25	7.00	2.96
87914-7215	-----	-----	-----	-----	-----	72	-----	5	91.44	88.90	10.92	5.84	2.79
87914-7225	-----	-----	-----	-----	-----	72	-----	5	91.44	88.90	12.25	7.00	2.96
87914-7216	-----	-----	-----	-----	-----	72	-----	6	91.44	88.90	10.92	5.84	2.79
87914-7226	-----	-----	-----	-----	-----	72	-----	6	91.44	88.90	12.25	7.00	2.96
87914-7227	-----	-----	-----	-----	-----	72	-----	6	91.44	88.90	12.25	7.00	2.96
-----	87914-7201	-----	-----	-----	-----	72	-----	4	91.44	88.90	13.21	8.13	2.79
-----	87914-7202	-----	-----	-----	-----	72	-----	5	91.44	88.90	13.21	8.13	2.79
-----	87914-7203	-----	-----	-----	-----	72	-----	6	91.44	88.90	13.21	8.13	2.79
-----	87914-7204	-----	-----	-----	-----	72	-----	4	91.44	88.90	11.11	6.10	2.72
-----	87914-7205	-----	-----	-----	-----	72	-----	5	91.44	88.90	11.11	6.10	2.72
-----	87914-7206	-----	-----	-----	-----	72	-----	6	91.44	88.90	11.11	6.10	2.72
-----	87914-7207	-----	-----	-----	-----	72	-----	6	91.44	88.90	11.11	6.10	2.72

D22


D22

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									
DIMENSION UNITS		SCALE		CURRENT REV DESC: BRIGHT TIN PHASE OUT					
mm		NTS		 <p>2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H</p>					
GENERAL TOLERANCES (UNLESS SPECIFIED)									
		MM		INCH		EC NO: 679909			
4 PLACES		±		±		DRWN: AKUMAR19 2021/06/29			
3 PLACES		±		±		CHK'D: MRAMAKRISHNA 2021/10/11			
2 PLACES		± 0.2		±		APPR: MRAMAKRISHNA 2021/10/11			
1 PLACE		±		±		INITIAL REVISION:			
0 PLACES		±		±		DRWN: YLQIAO 2005/01/17			
ANGULAR TOL		± 3.0°		±		APPR: SCLOW 2005/01/25			
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES	
						A3-SIZE		87914	
DOCUMENT STATUS				P1		RELEASE DATE		2021/10/11 11:53:31	
DOCUMENT NUMBER		DOC TYPE		DOC PART		REVISION			
SD-87914-013		PSD		000		D22			
MATERIAL NUMBER				CUSTOMER		SHEET NUMBER			
SEE TABLE				GENERAL MARKET		41 OF 45			

PART NO FOR BULK PACKAGING	PART NO FOR BULK PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION				
									A	B	F	M	P
87914-7411	-----	-----	-----	-----	-----	74	-----	1	93.98	91.44	10.92	5.84	2.79
87914-7421	-----	-----	-----	-----	-----	74	-----	1	93.98	91.44	12.25	7.00	2.96
87914-7412	-----	-----	-----	-----	-----	74	-----	2	93.98	91.44	10.92	5.84	2.79
87914-7422	-----	-----	-----	-----	-----	74	-----	2	93.98	91.44	12.25	7.00	2.96
87914-7413	-----	-----	-----	-----	-----	74	-----	3	93.98	91.44	10.92	5.84	2.79
87914-7423	-----	-----	-----	-----	-----	74	-----	3	93.98	91.44	12.25	7.00	2.96
87914-7414	-----	-----	-----	-----	-----	74	-----	4	93.98	91.44	10.92	5.84	2.79
87914-7424	-----	-----	-----	-----	-----	74	-----	4	93.98	91.44	12.25	7.00	2.96
87914-7415	-----	-----	-----	-----	-----	74	-----	5	93.98	91.44	10.92	5.84	2.79
87914-7425	-----	-----	-----	-----	-----	74	-----	5	93.98	91.44	12.25	7.00	2.96
87914-7416	-----	-----	-----	-----	-----	74	-----	6	93.98	91.44	10.92	5.84	2.79
87914-7426	-----	-----	-----	-----	-----	74	-----	6	93.98	91.44	12.25	7.00	2.96
87914-7427	-----	-----	-----	-----	-----	74	-----	6	93.98	91.44	12.25	7.00	2.96
-----	87914-7401	-----	-----	-----	-----	74	-----	4	93.98	91.44	13.21	8.13	2.79
-----	87914-7402	-----	-----	-----	-----	74	-----	5	93.98	91.44	13.21	8.13	2.79
-----	87914-7403	-----	-----	-----	-----	74	-----	6	93.98	91.44	13.21	8.13	2.79
-----	87914-7404	-----	-----	-----	-----	74	-----	4	93.98	91.44	11.11	6.10	2.72
-----	87914-7405	-----	-----	-----	-----	74	-----	5	93.98	91.44	11.11	6.10	2.72
-----	87914-7406	-----	-----	-----	-----	74	-----	6	93.98	91.44	11.11	6.10	2.72
-----	87914-7407	-----	-----	-----	-----	74	-----	6	93.98	91.44	11.11	6.10	2.72

D22

D22



THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											
DIMENSION UNITS		SCALE		CURRENT REV DESC: BRIGHT TIN PHASE OUT							
mm		NTS									
GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 679909		DRWN: AKUMAR19		2021/06/29		2.54MM PITCH	
				CHK'D: MRAMAKRISHNA		2021/10/11				DUAL ROW HEADER SINGLE WAFER, T/H	
				APPR: MRAMAKRISHNA		2021/10/11				PRODUCT CUSTOMER DRAWING	
4 PLACES ±				INITIAL REVISION:		DRWN: YLQIAO		2005/01/17		DOCUMENT NUMBER	
3 PLACES ±				DRWN: YLQIAO		2005/01/25		2005/01/25		SD-87914-013	
2 PLACES ± 0.2				APPR: SCLW						DOC TYPE DOC PART REVISION	
1 PLACE ±				THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER	
0 PLACES ±				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		A3-SIZE		87914		CUSTOMER	
ANGULAR TOL ± 3.0°										SEE TABLE	
										GENERAL MARKET	
										SHEET NUMBER	
										42 OF 45	

DOCUMENT STATUS	P1	RELEASE DATE	2021/10/11	11:53:31
-----------------	----	--------------	------------	----------

PART NO FOR BULK PACKAGING	PART NO FOR BULK PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION				
									A	B	F	M	P
87914-7611	-----	-----	-----	-----	-----	76	-----	1	96.52	93.98	10.92	5.84	2.79
87914-7621	-----	-----	-----	-----	-----	76	-----	1	96.52	93.98	12.25	7.00	2.96
87914-7612	-----	-----	-----	-----	-----	76	-----	2	96.52	93.98	10.92	5.84	2.79
87914-7622	-----	-----	-----	-----	-----	76	-----	2	96.52	93.98	12.25	7.00	2.96
87914-7613	-----	-----	-----	-----	-----	76	-----	3	96.52	93.98	10.92	5.84	2.79
87914-7623	-----	-----	-----	-----	-----	76	-----	3	96.52	93.98	12.25	7.00	2.96
87914-7614	-----	-----	-----	-----	-----	76	-----	4	96.52	93.98	10.92	5.84	2.79
87914-7624	-----	-----	-----	-----	-----	76	-----	4	96.52	93.98	12.25	7.00	2.96
87914-7615	-----	-----	-----	-----	-----	76	-----	5	96.52	93.98	10.92	5.84	2.79
87914-7625	-----	-----	-----	-----	-----	76	-----	5	96.52	93.98	12.25	7.00	2.96
87914-7616	-----	-----	-----	-----	-----	76	-----	6	96.52	93.98	10.92	5.84	2.79
87914-7626	-----	-----	-----	-----	-----	76	-----	6	96.52	93.98	12.25	7.00	2.96
87914-7627	-----	-----	-----	-----	-----	76	-----	6	96.52	93.98	12.25	7.00	2.96
-----	87914-7601	-----	-----	-----	-----	76	-----	4	96.52	93.98	13.21	8.13	2.79
-----	87914-7602	-----	-----	-----	-----	76	-----	5	96.52	93.98	13.21	8.13	2.79
-----	87914-7603	-----	-----	-----	-----	76	-----	6	96.52	93.98	13.21	8.13	2.79
-----	87914-7604	-----	-----	-----	-----	76	-----	4	96.52	93.98	11.11	6.10	2.72
-----	87914-7605	-----	-----	-----	-----	76	-----	5	96.52	93.98	11.11	6.10	2.72
-----	87914-7606	-----	-----	-----	-----	76	-----	6	96.52	93.98	11.11	6.10	2.72
-----	87914-7607	-----	-----	-----	-----	76	-----	6	96.52	93.98	11.11	6.10	2.72

D22

D22

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									
DIMENSION UNITS		SCALE		CURRENT REV DESC: BRIGHT TIN PHASE OUT					
mm		NTS		 <p>2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H</p>					
GENERAL TOLERANCES (UNLESS SPECIFIED)									
		MM		INCH		EC NO: 679909			
4 PLACES		±		±		DRWN: AKUMAR19 2021/06/29			
3 PLACES		±		±		CHK'D: MRAMAKRISHNA 2021/10/11			
2 PLACES		± 0.2		±		APPR: MRAMAKRISHNA 2021/10/11			
1 PLACE		±		±		INITIAL REVISION:			
0 PLACES		±		±		DRWN: YLQIAO 2005/01/17			
ANGULAR TOL		± 3.0°		±		APPR: SLOW 2005/01/25			
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES	
						A3-SIZE		87914	
DOCUMENT STATUS				P1		RELEASE DATE		2021/10/11 11:53:31	
DOCUMENT NUMBER		DOC TYPE		DOC PART		REVISION			
SD-87914-013		PSD		000		D22			
MATERIAL NUMBER				CUSTOMER		SHEET NUMBER			
SEE TABLE				GENERAL MARKET		43 OF 45			

PART NO FOR BULK PACKAGING	PART NO FOR BULK PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION				
									A	B	F	M	P
87914-7811	-----	-----	-----	-----	-----	78	-----	1	99.06	96.52	10.92	5.84	2.79
87914-7821	-----	-----	-----	-----	-----	78	-----	1	99.06	96.52	12.25	7.00	2.96
87914-7812	-----	-----	-----	-----	-----	78	-----	2	99.06	96.52	10.92	5.84	2.79
87914-7822	-----	-----	-----	-----	-----	78	-----	2	99.06	96.52	12.25	7.00	2.96
87914-7813	-----	-----	-----	-----	-----	78	-----	3	99.06	96.52	10.92	5.84	2.79
87914-7823	-----	-----	-----	-----	-----	78	-----	3	99.06	96.52	12.25	7.00	2.96
87914-7814	-----	-----	-----	-----	-----	78	-----	4	99.06	96.52	10.92	5.84	2.79
87914-7824	-----	-----	-----	-----	-----	78	-----	4	99.06	96.52	12.25	7.00	2.96
87914-7815	-----	-----	-----	-----	-----	78	-----	5	99.06	96.52	10.92	5.84	2.79
87914-7825	-----	-----	-----	-----	-----	78	-----	5	99.06	96.52	12.25	7.00	2.96
87914-7816	-----	-----	-----	-----	-----	78	-----	6	99.06	96.52	10.92	5.84	2.79
87914-7826	-----	-----	-----	-----	-----	78	-----	6	99.06	96.52	12.25	7.00	2.96
87914-7827	-----	-----	-----	-----	-----	78	-----	6	99.06	96.52	12.25	7.00	2.96
-----	87914-7801	-----	-----	-----	-----	78	-----	4	99.06	96.52	13.21	8.13	2.79
-----	87914-7802	-----	-----	-----	-----	78	-----	5	99.06	96.52	13.21	8.13	2.79
-----	87914-7803	-----	-----	-----	-----	78	-----	6	99.06	96.52	13.21	8.13	2.79
-----	87914-7804	-----	-----	-----	-----	78	-----	4	99.06	96.52	11.11	6.10	2.72
-----	87914-7805	-----	-----	-----	-----	78	-----	5	99.06	96.52	11.11	6.10	2.72
-----	87914-7806	-----	-----	-----	-----	78	-----	6	99.06	96.52	11.11	6.10	2.72
-----	87914-7807	-----	-----	-----	-----	78	-----	6	99.06	96.52	11.11	6.10	2.72

D22

D22

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											
DIMENSION UNITS		SCALE		CURRENT REV DESC: BRIGHT TIN PHASE OUT						molex	
mm		NTS									
GENERAL TOLERANCES (UNLESS SPECIFIED)											
		MM		INCH							
4 PLACES		±		±							
3 PLACES		±		±							
2 PLACES		± 0.2		±							
1 PLACE		±		±							
0 PLACES		±		±							
ANGULAR TOL		± 3.0°									
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES		SHEET NUMBER	
						A3-SIZE		87914		44 OF 45	



DOCUMENT STATUS	P1	RELEASE DATE	2021/10/11	11:53:31
-----------------	----	--------------	------------	----------


PART NO FOR BULK PACKAGING	PART NO FOR BULK PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION				
									A	B	F	M	P
87914-8011	-----	-----	-----	-----	-----	80	-----	1	101.60	99.06	10.92	5.84	2.79
87914-8021	-----	-----	-----	-----	-----	80	-----	1	101.60	99.06	12.25	7.00	2.96
87914-8012	-----	-----	-----	-----	-----	80	-----	2	101.60	99.06	10.92	5.84	2.79
87914-8022	-----	-----	-----	-----	-----	80	-----	2	101.60	99.06	12.25	7.00	2.96
87914-8013	-----	-----	-----	-----	-----	80	-----	3	101.60	99.06	10.92	5.84	2.79
87914-8023	-----	-----	-----	-----	-----	80	-----	3	101.60	99.06	12.25	7.00	2.96
87914-8014	-----	-----	-----	-----	-----	80	-----	4	101.60	99.06	10.92	5.84	2.79
87914-8024	-----	-----	-----	-----	-----	80	-----	4	101.60	99.06	12.25	7.00	2.96
87914-8015	-----	-----	-----	-----	-----	80	-----	5	101.60	99.06	10.92	5.84	2.79
87914-8025	-----	-----	-----	-----	-----	80	-----	5	101.60	99.06	12.25	7.00	2.96
87914-8016	-----	-----	-----	-----	-----	80	-----	6	101.60	99.06	10.92	5.84	2.79
87914-8017	-----	-----	-----	-----	-----	80	-----	6	101.60	99.06	10.92	5.84	2.79
87914-8026	-----	-----	-----	-----	-----	80	-----	6	101.60	99.06	12.25	7.00	2.96
87914-8027	-----	-----	-----	-----	-----	80	-----	6	101.60	99.06	12.25	7.00	2.96
-----	87914-8001	-----	-----	-----	-----	80	-----	4	101.60	99.06	13.21	8.13	2.79
-----	87914-8002	-----	-----	-----	-----	80	-----	5	101.60	99.06	13.21	8.13	2.79
-----	87914-8003	-----	-----	-----	-----	80	-----	6	101.60	99.06	13.21	8.13	2.79
-----	87914-8004	-----	-----	-----	-----	80	-----	4	101.60	99.06	11.11	6.10	2.72
-----	87914-8005	-----	-----	-----	-----	80	-----	5	101.60	99.06	11.11	6.10	2.72
-----	87914-8006	-----	-----	-----	-----	80	-----	6	101.60	99.06	11.11	6.10	2.72
-----	87914-8007	-----	-----	-----	-----	80	-----	6	101.60	99.06	11.11	6.10	2.72

D22






D22

D22

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											
DIMENSION UNITS		SCALE		CURRENT REV DESC: BRIGHT TIN PHASE OUT							
mm		NTS									
GENERAL TOLERANCES (UNLESS SPECIFIED)											
		MM		INCH							
4 PLACES		±		±							
3 PLACES		±		±							
2 PLACES		± 0.2		±							
1 PLACE		±		±							
0 PLACES		±		±							
ANGULAR TOL ± 3.0°											
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES		SHEET NUMBER	
						A3-SIZE		87914		45 OF 45	

			
2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H			
PRODUCT CUSTOMER DRAWING			
DOCUMENT NUMBER	DOC TYPE	DOC PART	REVISION
SD-87914-013	PSD	000	D22

DOCUMENT STATUS	P1	RELEASE DATE	2021/10/11	11:53:31
-----------------	----	--------------	------------	----------



- NOTES:
- MATERIAL:
HOUSING: GLASS FILLED, PA6T, UL94V-0,
COLOR: BLACK
TERMINAL: 0.64 SQ PIN, COPPER ALLOY
 - PLATING TYPE:
(1) : GOLD FLASH OVER
50 MICRO INCHES MIN. NICKEL OVERALL.

(2) : 1 MICRO INCHES MIN. GOLD PLATE ON CONTACT AND
75 MICRO INCHES MIN. TIN ON SOLDERTAIL OVER
50 MICRO INCHES MIN. NICKEL OVERALL.

(3) : 10 MICRO INCHES MIN. GOLD PLATE ON CONTACT AND
75 MICRO INCHES MIN. TIN ON SOLDERTAIL OVER
50 MICRO INCHES MIN. NICKEL OVERALL.

(4) : 15 MICRO INCHES MIN. GOLD PLATE ON CONTACT AND
75 MICRO INCHES MIN. TIN ON SOLDERTAIL OVER
50 MICRO INCHES MIN. NICKEL OVERALL.


(5) : 30 MICRO INCHES MIN. GOLD PLATE ON CONTACT AND
75 MICRO INCHES MIN. TIN ON SOLDERTAIL OVER
50 MICRO INCHES MIN. NICKEL OVERALL.

(6) : 100 MICRO INCHES MIN. TIN IN SELECTED AREA OVER
50 MICRO INCHES MIN. NICKEL OVERALL.
 - PIN PUSHOUT FORCE: 1KG MIN IN EITHER DIRECTION
 - THE ABOVE 10 CKT IS FOR ILLUSTRATION PURPOSE ONLY.
 - FOR PACKAGING OPTION PLEASE REFER TO THE TABLE.
 - PACKAGING SPECIFICATION:
TRAY : PK-89990-489
TAPE AND REEL: PK-87898-400

RELEASE STATUS	RELEASE DATE
----------------	--------------


QUALITY SYMBOLS 	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION										
	ADD -0651 & -3686 EC NO: 115475 DRWN: FCSCC CHK'D: REV APPR: KHLIM	2017/07/28	2017/08/15	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS	SCALE				
				MM	INCH	MM	NTS				
		4 PLACES	±	±	DRWN BY	DATE	SALES DRAWING 2.54MM DUAL ROW HEADER WITH STANDOFF, T/H				
		3 PLACES	±	±	SKLIM01	2005/09/07					
		2 PLACES	±	0.2	±	CHK'D BY	DATE	PRODUCT CUSTOMER DRAWING			
	1 PLACES	±	±	BOKOK	2005/09/17						
	0 PLACES	±	±	APPR BY	DATE	SERIES: 87914 MATERIAL NUMBER: SEE TABLE CUSTOMER: GENERAL MARKET					
				MLONG	2010/09/06						
		ANGULAR TOL ± 3.0		DRAWING SIZE	THIRD ANGLE PROJECTION	DOCUMENT NUMBER: SD-87914-022 DOC TYPE: PSD DOC PART: 000 SHEET NUMBER: 1 OF 3					
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		A3								

FOR TAPE WIDTH WITH SINGLE ROW SPROCKET HOLES.




P/N	CKT SIZE	F	So	W	QTY/REEL
87914-0627	06	11.50	-	24.00	250
87914-0827	08	11.50	-	24.00	250

FOR TAPE WIDTH WITH 2 ROWS OF SPROCKET HOLES.




NOTES:

1. LEADER AND TRAILER TAPE



VIEW OF PART ORIENTATION IN TAPE & REEL

2. PEELING OFF FORCE OF THE TOP TAPE: 10 - 130gf. (A9)
(PEELING DIRECTION AS SHOWN IN FOLLOWING FIGURE)



3. TAPE AND REEL SPECIFICATION IS AS PER EIA-481.
4. THE TAPE IS TREATED FOR ANTI-STATIC.

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION										
QUALITY SYMBOLS	ADD -0651 & -3686	2017/07/28	2017/08/15	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS	SCALE			
				MM	INCH	MM	NTS			
$\nabla = 0$	EC NO: 115475 DRWN: FCSCC CHK'D: REV APPR: KHLIM	A9	REV	4 PLACES	\pm	SKLIM01	DATE	SALES DRAWING		
3 PLACES				\pm	BOKOK	DATE	2.54MM DUAL ROW HEADER WITH STANDOFF, T/H			
2 PLACES				± 0.2	MLONG	DATE				PRODUCT CUSTOMER DRAWING
1 PLACES				\pm	DRWING SIZE	THIRD ANGLE PROJECTION	SERIES	MATERIAL NUMBER	CUSTOMER	
0 PLACES				\pm	A3		87914	SEE TABLE	GENERAL MARKET	
$\nabla = 0$				ANGULAR TOL ± 3.0	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		DOCUMENT NUMBER	DOC TYPE	DOC PART	SHEET NUMBER
$\nabla = 0$				SD-87914-022	PSD	000	2 OF 3			

RELEASE STATUS	RELEASE DATE
----------------	--------------

PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSIONS					
								A	B	F	M	P	G
-----	-----	-----	-----	87914-0627	6	-----	6	7.62	5.08	13.55	8.08	2.98	14.70
-----	-----	-----	----- (A9)	87914-0651	6	-----	4	7.62	5.08	17.29	12.00	3.00	18.29
87914-0629	-----	-----	-----	-----	6	-----	6	10.16	7.62	16.26	10.82	2.95	-
-----	-----	-----	-----	87914-0827	8	-----	6	10.16	7.62	13.55	8.08	2.98	14.70
87914-3638	-----	----- (A9)	87914-3686	-----	36	-----	6	45.72	43.18	12.10	7.01	2.60	-

D

C

B

A

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																			
QUALITY SYMBOLS 	2017/07/28		2017/08/15		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS		SCALE										
	ADD -0651 & -3686		EC NO: 115475		MM INCH		MM NTS		NTS										
	DRWN: FCSCC		CHK'D: KHLIM		4 PLACES ± ±		DRWN BY		DATE		SALES DRAWING								
	REV APPR: KHLIM		EC NO: 115475		3 PLACES ± ±		SKLIM01		2005/09/07				2.54MM DUAL ROW HEADER WITH STANDOFF, T/H						
			DRWN: FCSCC		2 PLACES ± 0.2 ±		CHK'D BY		DATE		PRODUCT CUSTOMER DRAWING								
			CHK'D: KHLIM		1 PLACES ± ±		BOKOK		2005/09/17										
			APPR: KHLIM		0 PLACES ± ±		APPR BY		DATE		<table border="1"> <tr> <td>SERIES</td> <td>MATERIAL NUMBER</td> <td>CUSTOMER</td> </tr> <tr> <td>87914</td> <td>SEE TABLE</td> <td>GENERAL MARKET</td> </tr> </table>		SERIES	MATERIAL NUMBER	CUSTOMER	87914	SEE TABLE	GENERAL MARKET	
	SERIES	MATERIAL NUMBER	CUSTOMER																
	87914	SEE TABLE	GENERAL MARKET																
			REV APPR: KHLIM		ANGULAR TOL ± 3.0		MLONG		2010/09/06		<table border="1"> <tr> <td>DOCUMENT NUMBER</td> <td>DOC TYPE</td> <td>DOC PART</td> <td>SHEET NUMBER</td> </tr> <tr> <td>SD-87914-022</td> <td>PSD</td> <td>000</td> <td>3 OF 3</td> </tr> </table>		DOCUMENT NUMBER	DOC TYPE	DOC PART	SHEET NUMBER	SD-87914-022	PSD	000
DOCUMENT NUMBER	DOC TYPE	DOC PART	SHEET NUMBER																
SD-87914-022	PSD	000	3 OF 3																
		REV APPR: KHLIM		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		A3		THIRD ANGLE PROJECTION											
		REV APPR: KHLIM																	

RELEASE STATUS	RELEASE DATE
----------------	--------------