

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0934446612](#)  
**Status:** **Active**  
**Overview:** [ML-XT Sealed Connection System](#)  
**Description:** ML-XT Sealed 12 Circuit Receptacle Housing with Heatshrink, Pre-Assembled with Large Rear Seal and Cover, Keying Option A, Grey

**Documents:**

<a href="#">3D Model</a>	<a href="#">Application Specification 934430010-A (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Packaging Specification 934430002-K (PDF)</a>
<a href="#">3D Model (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Product Specification 934430010-P (PDF)</a>	<a href="#">Product Literature (PDF)</a>



**Agency Certification**

UL E29179

**General**

Product Family	Crimp Housings
Series	<a href="#">93444</a>
Application	Power, Signal, Wire-to-Wire
Overview	<a href="#">ML-XT Sealed Connection System</a>
Product Literature Order No	987651-0201
Product Name	ML-XT
UPC	889056512015

**Physical**

Circuits (maximum)	12
Color - Resin	Grey
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	18.900/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	N/A
Polarized to Mating Part	Yes
Temperature Range - Operating	-55° to +125°C

**Electrical**

Current - Maximum per Contact 13.0A

**Material Info**

**Reference - Drawing Numbers**

Application Specification	934430010-A
Packaging Specification	934430002-K
Product Specification	934430010-P
Sales Drawing	934430060-000

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per - ED/71/2019 (16 July 2019)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[93444 Series](#)

**Mates With**

[ML-XT Sealed 12 Circuit Plug Housing 934456612](#)

**Use With**

[ML-XT Male \(Pin\) Terminal 845240004 \(Nickel\)](#), [ML-XT Male \(Pin\) Terminal 845240014 \(Selective Gold\)](#), [ML-XT 12 Circuit Receptacle Wedgelock 93447](#), [ML-XT Blind Cavity Plug 934941000](#)