



Part Number : [987811003](#)
Product Description : NSCC Pin Connector 3.33mm Pitch, 1.50mm, Shorting Bar, Long, 5 Circuit, Green
Series Number : 98781
Status : Not Recommended For New Design
Product Category : Connector Housings



Documents and Resources

Drawings

[987811003_sd.pdf](#)

Specifications

[AS-98781-005-001.pdf](#)

[AS-98781-005-CH-001.pdf](#)

[PK-98781-001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 33
China RoHS	Not Relevant
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Not Recommended For New Design
Category	Connector Housings
Series	98781
Description	NSCC Pin Connector 3.33mm Pitch, 1.50mm, Shorting Bar, Long, 5 Circuit, Green
Application	Wire-to-Wire
Product Name	SICMA
UPC	822350623353

Physical

Circuits Detail	5
Circuits (maximum)	5
Color - Resin	Green
Gender	Plug
Glow-Wire Capable	No
Lock to Mating Part	Yes
Material - Resin	PBT
Net Weight	9.500/g
Number of Rows	1
Packaging Type	Carton
Panel Mount	No
Pitch - Mating Interface	3.33mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +85°C

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Mates With / Use With

Mates with Part(s)

Description	Part Number
NSCC Receptacle Connector 3.33mm Pitch, 1.50mm, Shorting Bar, Long, 5 Circuit, Green	<u>987841003</u>

Use with Part(s)

Description	Part Number
Use With	1.50mm Size FCI SICMA Male Terminal

Application Tooling

Global

Description	Part Number
Extractor Tool for 5-Way Male Housing	<u>638134100</u>
Extractor Tool for 5-Way Male Housing	<u>638134200</u>