

## Honeywell Sensing and Control

Search

**24CX12**

( Home : Products : Switches » MICRO SWITCH™ Hazardous Location Switches » CX )

## narrow your search

## Products

- Controls Monitoring and Lighting (352)
- Machine Safety (1701)
- Sensors (6224)
- Switches (9749)
- Wireless (39)

## Technology

- Control and Instrumentation (1052)
- Electromechanical (9301)
- Magnetic (541)
- Optical/Infrared (1042)
- Thick Film (1764)
- More...

## new products

## New Wireless Products

Go farther. Work smarter. Explore new possibilities. Just by cutting the cord and making the switch.



Wireless Web Site  
WGLA and WPMM  
XYR6000™

[find out more](#)

## white papers

- Wireless Switches Offer Unlimited Benefit
- Basic Switches Are Not Created Equal
- Applying Precision Switches
- Sensors for Medical Devices
- New Ways to Measure Torque
- Choosing Safety Switches
- Specifying Hour Meters

## Need help?

[Click here to contact us](#)**Lever NOT Included**

Actual product appearance may vary.  
[click here to download Hi-Res image](#)

**Explosion-Proof Limit Switches Series CX: Standard Housing: Side Rotary, Lever not included**

[Sales & Service](#)[Distributor Inventory](#)

[Overview](#) [Specs](#) [Documentation](#) [Application Notes](#)

## Product Specifications

Availability	Global
Operating Force (OF)	0.50 Nm [.369 lb ft] max.
Pretravel (PT)	30° max.
Overtravel (OT)	75° min.
Differential Travel (DT)	20° max.
Product Type	MICRO SWITCH™ Weather-Sealed, Explosion-Proof Limit Switches
Actuator	Side Rotary
Lever Type	Lever Not Included - Reference Lever Required Accessory
Circuitry	2NC 2NO DPDT Snap Action; Maintained; 2 Basic Switches
Ampere Rating	10 A Ind./0.3 A Res./0.15 A Res.
Supply Voltage	120 Vac or 240 Vac/125 Vdc/250 Vdc
Housing Material	Aluminum
Termination Type	0.75 in - 14NPT Conduit
Housing Type	CX: Standard: 145 mm [5.71 in]
Series Name	CX
Sealing	NEMA 1, 3, 4, 4x, 6, 6P, 7 (Class I, Division 1, Groups B, C, D), 9 (Class II, Division 1, Groups E, F, G), 13
CSA File #	LR57324
UL File #	E14274
Operating Temperature	-25 °C to 85 °C [-13 °F to 185 °F]
Comment	Maintained with continual CW and/or CCW rotation
Agency Approvals and Standards	UL, CSA
UNSPSC Code	302119
UNSPSC Commodity	302119 Switches and controls and relays
Sealed	Explosion-proof

## contacts

Customer Service  
Technical Support  
Global Sales & Service  
View Site Demo  
Site Comments?

## meet dr. larry

**VIDEO** - Dr. Larry Goldstein explains our newest and best technologies.



Meet Dr. Larry

## my links

[Login to iCOM](#)  
[Login to Rep/AD Portal](#)  
[Login to Digital University](#)

## News Center

HONEYWELL ANNOUNCES ADDITION TO RELIALIGN™ RESIDENTIAL DOOR INTERLOCK SWITCHES THAT FEATURE RUGGED, PLASTIC HOUSING

HONEYWELL RELEASES UNLIMITED POTENTIAL WITH NEW LIMITLESS™ WIRELESS SWITCHES

HONEYWELL'S XYR6000 WIRELESS POSITION SENSOR ENABLES MONITORING IN HAZARDOUS AREAS AND REMOTE LOCATIONS

**MICRO SWITCH Anniversary site**