

Honeywell Sensing and Control

Search

192-302LEW-A01

(Home : Products : Sensors » Temperature Sensors » Discrete Thermistors » 192)

narrow your search

Products

- Controls Monitoring and Lighting (286)
- Machine Safety (1727)
- Sensors (6004)
- Switches (9781)
- Wireless (45)

Technology

- Control and Instrumentation (988)
- Electromechanical (9307)
- Magnetic (541)
- Platinum thin film (56)
- Thick Film (1409)
- More...

new products

New Wireless Products

Go farther. Work smarter. Explore new possibilities. Just by cutting the cord and making the switch.



Wireless Web Site
WGLA and WPMW
XYR6000™

find out more

white papers

- ▶ Wireless Switches Offer Unlimited Benefit
- ▶ Basic Switches Are Not Created Equal
- ▶ Applying Precision Switches
- ▶ Sensors for Medical Devices
- ▶ New Ways to Measure Torque
- ▶ Choosing Safety Switches
- ▶ Specifying Hour Meters

Need help?

Click here to contact us



Actual product appearance may vary.

192 Series, Uni-Curve with bare leads and epoxy, 3,000 Ohm resistance, $\pm 1,0^\circ\text{C}$ [1.8°F] tolerance, 25/85 BETA = 3974

Sales & Service

Distributor Inventory

Overview Specs Documentation Application Notes

Product Specifications

Availability	Global
Resistance	3,000 Ohm
Tolerance	$\pm 1,0^\circ\text{C}$ [1.8°F]
Accuracy	0°C to 70°C [32°F to 158°F]
Beta	3974
Operating Temperature	-60°C to 150°C [-76°F to 302°F]
Diameter	2,413 mm [0,095 in]
Termination Material	32 Gauge tinned copper, alloy 180
Lead Length	38,1 mm [1,50 in]
Time Constant in Air	15,0 s
Dissipation Constant	0,75 m/W°C
Series Name	192

contacts

- ▶ Customer Service
- ▶ Technical Support
- ▶ Global Sales & Service
- ▶ View Site Demo
- ▶ Site Comments?

meet dr. larry

VIDEO - Dr. Larry Goldstein explains our newest and best technologies.



▶ Meet Dr. Larry

my links

- ▶ Login to iCOM
- ▶ Login to Rep/AD Portal
- ▶ Login to Digital University

News Center

- ▶ HONEYWELL EXPANDS ITS LIMITLESS™ PLATFORM WITH THE LAUNCH OF ITS GLOBALLY AVAILABLE INDUSTRIAL WIRELESS RECEIVER
- ▶ HONEYWELL EXTENDS ITS TRUSTABILITY® PRESSURE SENSOR PRODUCT LINE WITH A SINGLE SIDE LIQUID MEDIA OPTION
- ▶ HONEYWELL ADDS NEW 100° AND 180° ARC CONFIGURATIONS TO ITS SMART POSITION SENSOR PORTFOLIO
- ▶ HONEYWELL INTRODUCES ITS HAWK™ RESOLVERS 1-INCH SERIES, FULLY HOUSED CONFIGURATION
- ▶ HONEYWELL INTRODUCES MICROPOWER OMNIPOLAR DIGITAL HALL-EFFECT SENSOR ICS WITH LOW SUPPLY VOLTAGE AND ULTRA LOW TYPICAL CURRENT

