

MICRO SWITCH


A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR COMPANY
PINEBROOK, ILLINOIS

FED. MFR. CODE 91929

SWITCH - BASIC

CATALOG LISTING

1HS103



NOTE -

- 1 - THIS SWITCH IS FOR LEFT HAND MOUNTING ONLY
- 2 - THIS SWITCH IS RECOMMENDED FOR USE IN AMBIENT TEMPERATURES FROM 250° F TO MINUS 65° F
- 3 - .006 MAX ROLLER SLANT ACROSS LENGTH OF ROLLER MEASURED FROM CENTER LINE OF MOUNTING HOLES
- 4 - THE MASS OF THE MOVING CONTACT IS .22 GRAM

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS		ELECTRICAL DATA			SCALE FULL	
OPERATING FORCE-----10-22 OZ		CONTACT ARRANGEMENT S P D T		DO NOT SCALE PRINT		
RELEASE FORCE-----4 OZ MIN		LINE VOLTAGE	INDUCTIVE LOAD	RESISTIVE LOAD	UNLESS OTHERWISE SPECIFIED	
DIFFERENTIAL TRAVEL-----.013 MAX					DIMENSIONS ARE IN INCHES	
OVERTRAVEL-----.035-.047					TOLERANCES ARE:	
		28 V.D.C.	5 AMP.	15 AMP.	ONE PLACE (.0)	±.030
					TWO PLACE (.00)	±.015
					THREE PLACE (.000)	±.005
					ANGLES	±
		WEIGHT 1.9 OZ MAX				

1HS103

M

DRAWING NUMBER

210

ISSUE

CHECK

REVISIONS

MADE MFS 20 NOV 61

SR10463 23 AUG 62

CO19072 13 MAY 64

RER 9 NOV 84

CO56087 9 NOV 84

CO57626 31 AUG 62

CO65768 12 JUN 89

TSK 76375 2 SEPT 93

WES 2 SEPT 93

OMW 17 APR 61

FO-30378