

Honeywell Sensing and Control

Search 

narrow your search

- Products
- Controls Monitoring and Lighting (354)
 - Machine Safety (1726)
 - Sensors (7074)
 - Switches (9814)

- Technology
- Control and Instrumentation (1063)
 - Electromechanical (9357)
 - Microstructure (2328)
 - Optical/Infrared (1077)
 - Thick Film (1764)
 - More...

Need Help?
Click here to contact us 

364Y50K Trimmers
(Home : Products)



Actual product appearance may vary.

364 Series Trimmer, 50 kOhm, 0.5 W, 25 Turns, Square Body, Vertical Shaft

[Sales & Service !\[\]\(b4eeff342f60cc7bcd67d869b4fedca2_img.jpg\)](#)

[Distributor Inventory !\[\]\(4f6bf54ae7e4144a72d78316053e412d_img.jpg\)](#)

[Overview](#) [Specs](#) [Documentation](#) [Application Notes](#)

Product Specifications

Product Type	Trimmer
Watts	0.5 W
Turns	25
Element Type	Cermet
Resistance Value	50 kOhm
Resistance Tolerance	± 10 %
Temperature Coefficient	± 100 ppm/ °C
Body	9,53 mm [0.375 in] square
Shaft Location	Vertical
Rotational Life	200 cycles
Series Name	364
Availability	Global
UNSPSC Code	4111363300
UNSPSC Commodity	4111363300 Potentiometers