


HONEYWELL PART NUMBER
535-59AD14-104

REV	DOCUMENT	CHANGED BY	CHECK
F	0023731	CH 14AUG06	RK



HOUSING	300 SERIES ST.STEEL
WIRE	28 AWG STRANDED (7/36) TEFLON INSULATED, RED
THERMISTOR	Q, CURVE 1
MAX TEMPERATURE	150°C

RESISTANCE (OHMS)	MIN.	NOM.	MAX.	REF. TOL.
TEMP. (°C)				
125	2442	2640	2838	±7.5%

ALL DIMENSIONS NOMINAL UNLESS OTHERWISE SPECIFIED

RoHS COMPLIANT

DESIGN UNITS: INCH
TOLERANCES UNLESS NOTED:
NO PLACE X ±
ONE PLACE .X ±
TWO PLACE .XX ±
THREE PLACE .XXX ±
FOUR PLACE .XXXX ±
ANGLES X ±
THIRD ANGLE PROJECTION

DRAWN	CH	14AUG06
CHECK	RK	14AUG06
THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.		
INTERPRET PER ASME Y14.5M-1994 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY		

<b>Honeywell</b>			
TITLE		PROBE ASSEMBLY OUTLINE	
SIZE	TYPE	DRAWING NAME	REV
B	I	535-59AD14-104	F
AUTOCAD		SCALE	SHEET
		2D	1 OF 1