

Honeywell Sensing and Control

Search



narrow your search

Products

- Controls Monitoring and Lighting (286)
- Machine Safety (1727)
- Sensors (6165)
- Switches (9781)
- Wireless (45)

Technology

- Control and Instrumentation (890)
- Electromechanical (9307)
- Magnetic (541)
- Platinum thin film (56)
- Thick Film (1372)
- More...

new products

New Wireless Products

Go farther. Work smarter. Explore new possibilities. Just by cutting the cord and making the switch.



Wireless Web Site
WGLA and WPMM
XYR6000™

[find out more](#)

white papers

- Wireless Switches Offer Unlimited Benefit
- Basic Switches Are Not Created Equal
- Applying Precision Switches
- Sensors for Medical Devices
- New Ways to Measure Torque
- Choosing Safety Switches
- Specifying Hour Meters

Need help?

[Click here to contact us](#)

91MCE18-PBQ

(Home : Products : Switches » MICRO SWITCH™ Limit Switches » MICRO SWITCH™ Global Limit Switches » 91MCE)



Actual product appearance may vary.

Global Limit Switches Series 91MCE: Top Plunger with boot seal, 1NO 1NC Direct Opening Snap Action, 4 pin M12 connector - Bottom Exit

[Sales & Service](#) [Distributor Inventory](#)

Overview Specs Documentation Application Notes

Product Specifications

Availability	Global
Operating Force (OF)	11,0 N [2.4 lb]
Pretravel (PT)	144371
Overtravel (OT)	144371
Differential Travel (DT)	144371
Actuator	Top Plunger with Boot Seal
Lever Type	None
Circuitry	1NO 1NC Direct Opening Snap Action
Ampere Rating	10 A (Thermal)
Supply Voltage	300 Vac/250 Vdc max.
Housing Material	Zinc Die-Cast
Termination Type	4-pin M12 Connector
Series Name	91MCE
Sealing	IP67; NEMA 1, 4, 12, 13
UL File #	E37138
Expected Mechanical Life	5 Million
Operating Temperature	-25 °C to 85 °C [-13 °F to 185 °F]
Agency Approvals and Standards	cULus, CE, CCC
UNSPSC Code	302119
UNSPSC Commodity	302119 Switches and controls and relays

contacts

- Customer Service
- Technical Support
- Global Sales & Service
- View Site Demo
- Site Comments?

meet dr. larry

VIDEO - Dr. Larry Goldstein explains our newest and best technologies.



Meet Dr. Larry

my links

- Login to iCOM
- Login to Rep/AD Portal
- Login to Digital University

News Center

Honeywell Introduces TruStability® NSC Series, Uncompensated / Unamplified Board Mount Pressure Sensors

HONEYWELL EXPANDS ITS LIMITLESS™ PLATFORM WITH THE LAUNCH OF ITS GLOBALLY AVAILABLE INDUSTRIAL WIRELESS RECEIVER

HONEYWELL EXTENDS ITS TRUSTABILITY® PRESSURE SENSOR PRODUCT LINE WITH A SINGLE SIDE LIQUID MEDIA OPTION

HONEYWELL ADDS NEW 100° AND 180° ARC CONFIGURATIONS TO ITS SMART POSITION SENSOR PORTFOLIO

HONEYWELL INTRODUCES ITS HAWK™ RESOLVERS 1-INCH SERIES, FULLY HOUSED CONFIGURATION

HONEYWELL INTRODUCES MICROPOWER OMNIPOLAR DIGITAL HALL-EFFECT SENSOR ICS WITH LOW SUPPLY VOLTAGE AND ULTRA LOW TYPICAL CURRENT

MICRO SWITCH Anniversary site