

Honeywell Sensing and Control

Search



BZ-2RW8072224286-A2
 (Home : Products : Switches » MICRO SWITCH™ Basic Switches » Premium Large Basic Switches » BZ/BA/WA/YZ)

[contacts](#)

narrow your search

Products

- Controls Monitoring and Lighting (286)
- Machine Safety (1727)
- Sensors (6158)
- Switches (9781)
- Wireless (45)

Technology

- Control and Instrumentation (890)
- Electromechanical (9303)
- Magnetic (538)
- Platinum thin film (56)
- Thick Film (1372)
- More...



BZ Series Standard Basic Switch, Single Pole Double Throw Circuitry, 1 A at 125 Vac, Straight Lever Actuator, Screw Termination, Gold Contacts, UL, CSA, ENEC

Actual product appearance may vary.

[Sales & Service](#)

[Distributor Inventory](#)

- Customer Service
- Technical Support
- Global Sales & Service
- View Site Demo
- Site Comments?

[meet dr. larry](#)

VIDEO - Dr. Larry Goldstein explains our newest and best technologies.



Meet Dr. Larry

[my links](#)

- Login to iCOM
- Login to Rep/AD Portal
- Login to Digital University

new products

New Wireless Products

Go farther. Work smarter. Explore new possibilities. Just by cutting the cord and making the switch.



[Wireless Web Site WGLA and WPMM XYR6000™](#)

[find out more](#)

white papers

- Wireless Switches Offer Unlimited Benefit
- Basic Switches Are Not Created Equal
- Applying Precision Switches
- Sensors for Medical Devices
- New Ways to Measure Torque
- Choosing Safety Switches
- Specifying Hour Meters

Need help?

[Click here to contact us](#)

[Overview](#) [Specs](#) [Documentation](#) [Application Notes](#)

Product Specifications

Switch Type	MICRO SWITCH™ Standard 25,4 mm H x 17,8 mm W x 50,8 mm L [1.0 in H x 0.7 in W x 2.0 in L]
Sealed	No
Ampere Rating	1 A
Circuitry	SPDT
Actuator	Straight Lever
Termination	Screw
Operating Temperature	-55 °C to 85 °C [-67 °F to 185 °F]
Voltage	125 Vac
Actuator Length	63,5 mm [2.5 in]
Contact Type	Gold
Operating Force (OF)	0,7 N [2.5 oz] max.
Release Force	0,14 N [0.494 oz] min.
Overtravel (OT)	5,56 mm [0.219 in] min.
Differential Travel (DT)	0,18 mm [0.007 in] max.
Operating Position (OP)	19,1 mm [0.750 in]
Material	Plastic
Housing Material	General Purpose Phenolic
Agency Approvals and Standards	UL, CSA, ENEC
Mounting Screw Size	3,53 mm [0.139 in]
Mounting Centers	25,4 mm [1 in]
Tightening Torque	0,33 N m [3.0 in lb]
Weight	24,94 g to 34,01 g [0.055 lb to 0.075 lb]
Package Height	24,1 mm [0.95 in]
Package Width	17,5 mm [0.69 in]
Package Length	49,3 mm [1.94 in]
Comment	CE: 61058-1; UL: E12252; CSA: LR41370; Bottom facing #6 screws and cup washers
Availability	Global
UNSPSC Code	30211905
UNSPSC Commodity	30211905 Snap switches
Series Name	BZ/BA/WA/YZ

News Center

- HONEYWELL INTRODUCES TRUSTABILITY® NSC SERIES, UNCOMPENSATED / UNAMPLIFIED BOARD MOUNT PRESSURE SENSORS
- HONEYWELL EXPANDS ITS LIMITLESS™ PLATFORM WITH THE LAUNCH OF ITS GLOBALLY AVAILABLE INDUSTRIAL WIRELESS RECEIVER
- HONEYWELL EXTENDS ITS TRUSTABILITY® PRESSURE SENSOR PRODUCT LINE WITH A SINGLE SIDE LIQUID MEDIA OPTION

[MICRO SWITCH Anniversary site](#)