

Honeywell Sensing and Control

Search



narrow your search

Products

- Controls Monitoring and Lighting (286)
- Machine Safety (1727)
- Sensors (6158)
- Switches (9781)
- Wireless (45)

Technology

- Control and Instrumentation (890)
- Electromechanical (9303)
- Magnetic (538)
- Platinum thin film (56)
- Thick Film (1372)
- More...

new products

New Wireless Products

Go farther. Work smarter. Explore new possibilities. Just by cutting the cord and making the switch.



Wireless Web Site
WGLA and WPMM
XYR6000™

[find out more](#)

white papers

- Wireless Switches Offer Unlimited Benefit
- Basic Switches Are Not Created Equal
- Applying Precision Switches
- Sensors for Medical Devices
- New Ways to Measure Torque
- Choosing Safety Switches
- Specifying Hour Meters

Need help?

[Click here to contact us](#)

LSP1AB

(Home : Products : Switches » MICRO SWITCH™ Limit Switches » MICRO SWITCH™ Heavy-Duty Limit Switches » HDLS)



Actual product appearance may vary.
[click here to download Hi-Res image](#)

Series HDLS Plug-in: Side Rotary; 1NC 1NO SPDT Snap Action; 5-Pin Mini-Connector

[Sales & Service](#) [Distributor Inventory](#)

[Overview](#) [Specs](#) [Documentation](#) [Application Notes](#)

Product Specifications

Availability	Global
Operating Force (OF)	0,45 N m [4 in lb] max.
Pretravel (PT)	9° max.
Overtravel (OT)	66° min.
Differential Travel (DT)	3° max.
Product Type	MICRO SWITCH™ Heavy-Duty Limit Switches
Actuator	Side Rotary
Lever Type	Lever Not Included - Reference Lever Required Accessory
Circuitry	1NC 1NO SPDT Snap Action, Double Break
Ampere Rating	10 A (Thermal)
Supply Voltage	600 Vac and 250 Vdc max.
Housing Material	Zinc Die-Cast
Termination Type	5-Pin Mini-Connector
Housing Type	HDLS Plug-in
Series Name	HDLS
Sealing	NEMA 1, 3, 4, 6, 6P, 12, 13
UL File #	E37138
Operating Temperature	-12 °C to 121 °C [10 °F to 250 °F]
Comment	Low Differential Travel; Wired with 5 pin Mini style connector
Agency Approvals and Standards	UL, CE, CSA, CCC. EN60947-1, EN60947-5-1
UNSPSC Code	302119
UNSPSC Commodity	302119 Switches and controls and relays
Sealed	Industrial

contacts

- Customer Service
- Technical Support
- Global Sales & Service
- View Site Demo
- Site Comments?

meet dr. larry

VIDEO - Dr. Larry Goldstein explains our newest and best technologies.



Meet Dr. Larry

my links

- Login to iCOM
- Login to Rep/AD Portal
- Login to Digital University

News Center

HONEYWELL INTRODUCES TRUSTABILITY® NSC SERIES, UNCOMPENSATED / UNAMPLIFIED BOARD MOUNT PRESSURE SENSORS

HONEYWELL EXPANDS ITS LIMITLESS™ PLATFORM WITH THE LAUNCH OF ITS GLOBALLY AVAILABLE INDUSTRIAL WIRELESS RECEIVER

HONEYWELL EXTENDS ITS TRUSTABILITY® PRESSURE SENSOR PRODUCT LINE WITH A SINGLE SIDE LIQUID MEDIA OPTION

MICRO SWITCH Anniversary site