



Home> Products > Conductive Plastic> MKII> Product Page

200BF2D502



Actual product appearance may vary.

MKII Series Precision Potentiometer, Conductive Plastic Element, Turret Terminals, 1 W Power Rating, 5 kOhm Resistance Value

Features

- Linearity (Accuracy) 0.5 % or less
- 10 Million to 20 Million Lifecycles
- Servo and Bushing Mounting
- Custom Electrical Travels

Potential Applications

- Valve Position Feedback
- Panel Control
- Instrumentation
- Missile Fin Position Feedback

Description

Honeywell's MKV and MKII Potentiometers offer a cost effective way of obtaining high accuracy, long life position feedback. Honeywell has many years of experience in successfully providing high reliability/high performance products to the military and aerospace industries and continues to expand that technical capability to the low cost/high performance industrial and commercial segments.

Supporting Documentation

 [Dimensions](#)

Product Specifications	
Potentiometer Type	Precision
Element Type	Conductive Plastic
Terminal Type	Turret
Power Rating	1 W
Resistance Value	5 kOhm
Resistance Tolerance	± 10 %
Linearity	± 0.15 %
Bushing Thread	9,53 mm [0.375 in] x 32 NEF - 2A
Bushing length	9,53 mm [0.375 in]
Bushing Type	Standard
Shaft Diameter	6,35 mm [0.25 in]
Shaft length	19,05 mm [0.75 in]
Shaft Ending	Plain round
Body	50,80 mm [2.0 in] diameter, ± 23,11 mm [0.910]
Electrical Taper	Linear
Operating Temperature	- 65 °C to 125 °C [- 85 °F to 257 ° F]
Working Voltage (Max.)	750 V
Rotational Life	10 million cycles
Mechanical Rotation	360°
Availability	Global
Series Name	MKII
UNSPSC Code	4111363312
UNSPSC Commodity	4111363300 Potentiometers

My Links

- Login to iCOM
- Login as Rep/AD
- Login as Guest
- Login to Digital University

Keyword Search

Search for product and support information.

All Sensing and Control

Product Search

Part number search:

Use (*) to expand search

Specification Search