

- [PRODUCTS](#) ▾
- [DISTRIBUTOR INVENTORY](#)
- [INDUSTRIES](#) ▾
- [SUPPORT](#) ▾
- [NEWS & EVENTS](#) ▾
- [ABOUT US](#) ▾

# 102TL2-3G

[Products](#) > [Switches](#) > [Toggle Switches](#) > [TL Series](#) > [102TL2-3G](#)

## Overview

MICRO SWITCH TL Series Toggle Switch, 2 pole, 2 position, IWTS (16-20 Gage) terminal, Locking Lever, Military Part Number MS27788-23G. ... [View More](#)



- [view all 102TL2-3G literature](#)
- [view distributor inventory](#)
- [sample request](#)
- [email support](#)
- [get support](#)
- [email sales](#)
- [find a distributor](#)
- [email this page](#)

## Technical Specifications

Series Name	TL
Ampere/Voltage Range (Resistive Load)	0.5 A at 250 Vdc 0.5 A to 7.5 A at 0.5 Vdc to 28 Vdc 6 A at 0.5 Vac to 230 Vac 0.75 A at 115 Vdc
Action	2 position
Mounting	Bushing 15/32 in
MIL Spec. Number	MS27788-23G

Product Type	MICRO SWITCH Toggle Switch
Circuitry	DPDT
Circuitry/Operating action	
Termination	IWTS (16-20 Gage)
Lever Type	Locking

[View More](#)

View documents in: English ▾

## Documents

TITLE	DOCUMENT TYPE	LANGUAGE	SIZE
102TL2-3G highres photo	Photo	English	2MB
102TL2-3G lowres photo	Photo	English	223KB
MICRO SWITCH TL Series Military-Grade Toggle Switches	Datasheet	English	2MB
Sensors and Switches in Oil Rig Applications	Application Note	English	7MB

[View More](#)

## Product Features

- Qualified to MIL-DTL-3950
- Environment-proof sealing
- 1,2, and 4 pole circuitry
- Standard and pull-to-unlock levers
- 2 and 3 position, maintained and momentary toggle action
- Temperature range: -65 °C to 71 °C [-85 °F to 160 °F]

- Completely sealed switching chamber
- Step-design case provides added space between terminals to help prevent shorting
- UL recognized, CSA certified
- CE approved

## Applications

---

- Industrial machinery and equipment
- Military and commercial aviation
- Construction equipment
- Test instruments
- Agricultural machinery
- Process control
- Medical instrumentation

### NAVIGATION LINKS

[HOME PAGE](#)

[PRODUCTS](#)

[DISTRIBUTOR INVENTORY](#)

[INDUSTRIES](#)

[SUPPORT](#)

[NEWS & EVENTS](#)

[ABOUT US](#)

### DISTRIBUTOR LINKS

[ECOM LOGIN](#)

[LEARN CENTER](#)

[REQUEST ACCESS TO ECOM](#)


[SALES/AD PORTAL LOGIN](#)

[SALES/AD PORTAL ACCESS REQUEST](#)

[SAMPLE REQUEST](#)

[SUPPLIER MICROSITE](#)

### LANGUAGE

English 

### SOCIAL MEDIA



### SITE INFORMATION

[PRIVACY STATEMENT](#)

[SITEMAP](#)

[TERMS & CONDITIONS](#)

COPYRIGHT © 2018 HONEYWELL  
INTERNATIONAL INC.