



HONEYWELL

VP10FA-2500

See full Datasheet below...

onlinecomponents.com

THE ONLINE DISTRIBUTOR OF ELECTRONIC COMPONENTS

BUY NOW



MASTERTM
ELECTRONICS

BUY NOW

masterelectronics.com & onlinecomponents.com
are **authorized** e-commerce distributors
of electronic components.



narrow your search

Products

- ? Controls Monitoring and Lighting (301)
- ? Machine Safety (1412)
- ? Sensors (6855)
- ? Switches (9490)

Technology

- ? Control and Instrumentation(1010)
- ? Electromechanical (8984)
- ? Microstructure (2286)
- ? Optical/Infrared (806)
- ? Thick Film(1764)
- ? More...

Need Help?

Click here to contact us

VP10FA2500 Wirewound Resistors

(Home: Products)



VP Adjustable Series, 2.5 kOhms, 10.0 W, Adjustable, Wirewound Resistor

Actual product appearance may vary.

[Sales & Service](#)

[Distributor Inventory](#)

Overview

Specs

Documentation

Application Notes

Description

The VP Adjustable Series offer adjustable power resistors that are excellent for applications requiring settings at different resistance values. The resistors come equipped with an adjustable slider lug, making them ideal for adjusting circuits, obtaining odd resistance values and setting equipment to meet various line voltage requirements. The VF Adjustable series is made with tinned lug terminals solderable to MIL-R-26 standards. These resistors can be bracket mounted.

Note: Not suitable for high frequency applications.

Features

Features

- ? Adjustable slider
- ? Rugged vitreous enamel
- ? All-welded construction
- ? Meets or exceeds MIL-R-26 standards

Potential Applications

Potential Applications

- ? Applications requiring adjustable resistance values
- ? Power supplies
- ? Power dissipation circuits
- ? Load adjustors for power amplifiers
- ? Voltage divider in DC circuits