

**BU-60HT****(HIGH TEMPERATURE, ALLIGATOR CLIP)**

- The BU-60HT is a high temperature version of Mueller's world famous BU-60 alligator clip. It is manufactured with high temperature components which allow it to be used in applications that reach 1100°F (593°C). The maximum clip temperature is determined by the combination of the ambient temperature and the current (amps) being pulled through the clip.
- Length: 2" (51 mm), Width .3" (7.6mm), Height .4" (11mm)
- Jaw Opens 31" (7.9mm) Max.
- Rating: 10 Amps @ 900°F (482°C)
- Made from zinc plated CRS.
- Available High temperature Silicone Insulator (BU-62S-\*)
- RoHS2 Compliant