

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0936010565](#)
Status: **Active**
Overview: GWconnect Heavy Duty Connectors (HDC)
Description: GWconnect Crimp Contact Insert, Male, 25-Pole, 4A, for Turned Crimp Contacts, Size «34.2x14.6»

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E249674

General

Product Family Industrial Connectors / Enclosures
 Series [93601](#)
 Component Size «34.2x14.6»
 Component Type Inserts - Crimp Contact
 Exclude SD Check Yes
 Insert Series S-MD/25
 Overview [GWconnect Heavy Duty Connectors \(HDC\)](#)
 Product Category Heavy Duty Connectors
 Product Name GWconnect
 Standard CSA C22.2 NO. 182.3, EN 61984, UL 1977
 UPC 887191835228

Physical

Durability (mating cycles max) 500
 Flammability UL 94V-0
 Gender Male
 Insert Color Grey
 Material - Insert Polycarbonate
 Net Weight 11.200/g
 Number of Rows 3
 Packaging Type Bag
 Polarized to Mating Part Yes
 Poles 25
 Temperature Range - Operating -40° to +125°C

Electrical

Current - Maximum per Contact 4.0A
 Voltage - Maximum 50V

Material Info

Engineering Number 7725.3432.0



EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[93601](#) Series

Mates With

[936010564](#) Female Crimp Contact Insert

Use With

Turned Crimp Contacts - Male