

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0936014639](#)  
**Status:** **Active**  
**Overview:** GWconnect Heavy Duty Connectors (HDC)  
**Description:** Gwconnect HE - Harsh Environment S-CX/3A Shielded Circular BUS Connector with Housing, 1 Lever , Male, 4-Pole, with Size 3A «21x21», Black

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Industrial Connectors / Enclosures
Series	<a href="#">93601</a>
Comments	Contacts to be ordered Separately.
Component Size	3A «21x21»
Component Type	Circular BUS Connector
IP Rating	IP66, IP67
Insert Series	S-CX
Overview	<u>GWconnect Heavy Duty Connectors (HDC)</u>
Product Category	Heavy Duty Connectors
Product Name	GWconnect
Standard	EN 60664-1, EN 61984, UL 1977
Type	HE
UPC	887191839622

**Physical**

Durability (mating cycles max)	500
Flammability	UL 94V-0
Gender	Male
Housing Coating	Polyester Powder
Housing Color	Black RAL 9005
Lock to Mating Part	Yes
Material - Housing	Die-cast Aluminum
Material - Insert	Polycarbonate
Material - Lever	Stainless Steel
Net Weight	51.000/g
Packaging Type	Bag
Polarized to Mating Part	Yes
Poles	4
Temperature Range - Operating	-40° to +125°C

**Electrical**

Current - Maximum per Contact	10.0A
Voltage	EN 61984: 50V 0.8kV 3

**Material Info**

Engineering Number	7903.4496.1
--------------------	-------------



*Series image - Reference only*

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[93601 Series](#)

**Mates With**

[93601-4603](#) Female Circular BUS Connector Hood Assembly -M20,  
[93601-4691](#) Female Circular BUS Connector Hood Assembly -Pg11/Pg13.5

**Use With**

S-D Series Male Turned Crimp Contact