



Part Number : [936000386](#)

Product Description : Heavy-Duty Plastic Gable Gland with Gasket, Pg7 Thread, Black RAL 9005

Series Number : 93600

Status : Active

Product Category : Heavy-Duty Cable Glands

Engineering Part Number : 7000.7829.1



Documents & Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Contained per D(2022)9120-DC (17 Jan 2023)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Cable Glands
Series	93600
Description	Heavy-Duty Plastic Gable Gland with Gasket, Pg7 Thread, Black RAL 9005
Cable Gland Type	IP68 with Gasket
IP Rating	IP68
Product Name	Heavy-Duty Connectors
Standard	DIN 40430, EN 60529
UPC	887191854380

Physical

Cable Diameter	3.00-6.50mm
Gland Color	Black RAL 9005
Material - Cable Gland	Polyamide
Material - Gasket	NBR
Material - Nut	Polyamide
Net Weight	3.667/g
Packaging Type	Bag
Panel Cutout Diameter	12.70mm
Panel Mount	Yes
Temperature Range - Operating	-40° to +100°C
Thread Size	Pg7
Thread Type	(Pg)
Waterproof / Dustproof	Yes
Waterproof / Dustproof Type	IP68

Mates With / Use With

Use with Part(s)

Description	Part Number
Use With	Sealed Enclosures and Boxes