



Audio

## Circular Adapters

[back](#)

[Home](#)  
[About Us](#)

### Products

**Audio**

[Video](#)

[Lighting](#)

[Data Connectors](#)

[Industrial](#)

[Support](#)

[News](#)

[Sitemap](#)

Search

PRODUCTS ONLY

© Neutrik® AG  
All rights reserved  
[Legal Notices](#)

### NA3MJ

#### Product

Connector Type     Adapter

#### Electrical

Contact resistance     ≤ 3 mΩ (XLR)

Dielectric strength     1.5 kV dc / > 1 kVdc (XLR/Jack)

Insulation resistance     > 2 GΩ

#### Mechanical

Locking device     Latch lock

#### Material

Contact plating     2 μm Ag

Contacts     Brass (CuZn39Pb3) (XLR male)

Contacts     Bronze (CuBe2) (jack)

Insert     Polyamide (PA 6.6 30 % GR)

Shell     Zinc diecast (ZnAl4Cu1)

Shell plating     gal Cu/Ni

#### Environmental

Temperature range     -20 °C to +65 °C