



NA3FJ

3 pole XLR female - Stereo 1/4" locking jack (tip, ring, sleeve contact)

Features & Benefits

- Versatile, pre-wired and ready to use adapters to reliably interlock various connector systems
- Professional look and compact space saving design, based on the XX Series
- Rugged diecast shell for best reliability

Technical Information

Product	
Title	NA3FJ
Connection Type	Adapter

Electrical	
Contact resistance	$\leq 3 \text{ m}\Omega$ (XLR)
Contact resistance	$\leq 6 \text{ m}\Omega$
Dielectric strength	1.5 kV dc / > 1 kVdc (XLR/Jack)
Insulation resistance	> 2 G Ω

Mechanical	
Wiresize	
Locking device	Latch lock

Material	
Contact plating	2 μm Ag
Contacts	Bronze (CuBe2) (jack)
Insert	Polyamide (PA 6.6 30 % GR)
Shell	Zinc diecast (ZnAl4Cu1)
Shell plating	gal Cu/Ni

Environmental	
Temperature range	-20 °C to +65 °C