


NEUTRIK
[Home](#)
[Products](#)
[About us](#)
[Contact](#)
[Support](#)

[Products](#) > [Audio](#) > [XLR](#) > [XLR Chassis Connectors](#) > [DL Series](#) > NC6MD-L-BAG-1

[print](#)

NC6MD-L-BAG-1

6 pole male receptacle, solder cups, black metal housing, silver contacts

Universal D-size metal body XLR panel mount series. UL recognized component.

Features & Benefits

- Robust "D" metal shell
- Standardized D sized 24 mm panel cutout
- Solder cups on 3 - 7 pole version



Downloads

- [Product Guide 2012, 02 XLR](#)
- [UL Certificate of Compliance](#)
- [Drawing NC6MD-L-1](#)
- [Drawing NC6MD-L-1](#)
- [3D File NC6MD-L-1](#)

Links

- [UL Certificate \(ECBT2.E135070\)](#)
- [cUL Certificate \(ECBT8.E135070\)](#)

Technical Information hide

Product	
Title	NC6MD-L-BAG-1
Connection Type	XLR
Gender	male
Electrical	
Capacitance between contacts	≤ 7 pF
Contact resistance	≤ 5 m Ω (inner)
Dielectric strength	1,5 kVdc
Insulation resistance	> 2 G Ω (initial)
Rated current per contact	7,5 A
Rated voltage	50 V
Mechanical	
Insertion force	≤ 20 N
Withdrawal force	≤ 20 N
Lifetime	> 1000 mating cycles
Wiresize	max. 1.0 mm ²

Wiresize	max. 18 AWG
Wiring	Solder contacts
Locking device	Latch lock
Chassis shape	D

Material

Contact plating	2 µm Ag over 2 µm Ni
Contacts	Brass (CuZn39Pb3)
Insert	Polyamide (PA 6.6 30 % GR)
Locking element	Stahl Ck67
Shell	Zinc diecast (ZnAl4Cu1)
Shell plating	Black chromium

Environmental

Approvals	UL
Flammability	UL 94 HB
Standard compliance	IEC 61076-2-103
Protection class	IP 40
Solderability	Complies with IEC 68-2-20
Temperature range	-30 °C to +80 °C

Accessories



