



## NA3MP

3-pole XLR male - stereo 1/4" plug (Tip, Ring, Sleeve contact)

### Features & Benefits

- ✓ Versatile, pre-wired and ready to use adapters to reliably interlock various connector systems
- ✓ Professional look and compact space saving design, based on the X Series (XLR worldwide accepted standard)
- ✓ Rugged diecast shell for best reliability

### Technical Information

Product	
Title	NA3MP
Connection Type	Adapter

Electrical	
Contact resistance	$\leq 3 \text{ m}\Omega$ (XLR)
Contact resistance	$\leq 6 \text{ m}\Omega$
Dielectric strength	1.5 kV dc / > 1 kVdc (XLR/Plug)
Insulation resistance	> 2 G $\Omega$

## Mechanical

Wire size	
Locking device	Latch lock

## Material

Contact plating	2 µm Ag over 2 µm Ni
Contacts	Brass (CuZn39Pb3) (plug)
Insert	Polyamide (PA 6.6 30 % GR)
Shell	Zinc diecast (ZnAl4Cu1)
Shell plating	gal Cu/Ni

## Environmental

Temperature range	-20 °C to +65 °C
-------------------	------------------