


**NEUTRIK**
[Home](#)
[Products](#)
[About us](#)
[Contact](#)
[Support](#)

[Products](#) > [Video](#) > [Phono \(RCA\)](#) > [Phono \(RCA\) Chassis Connectors](#) > NF2D-B-6

[print](#)

# NF2D-B-6





Phono socket in black chrome D-shape housing, blue isolation washers, solder version.

## Features & Benefits

- Precisely machined to our demanding quality standards
- Gold plated contacts



## Downloads

-  [Product Guide 2012, 03 Plugs+Jacks](#)
-  [Drawing NF2D](#)
-  [Drawing NF2D](#)
-  [3D File NF2D](#)

## Technical Information [hide](#)

### Product

Title	NF2D-B-6
Connection Type	RCA
Gender	female

### Electrical

Capacitance between contacts	≤ 9 pF
Contact resistance	<5G mΩ (inner)
Dielectric strength	0,5 kVdc
Insulation resistance	< 5 GΩ
Rated current per contact	16 A
Rated voltage	50 V

### Mechanical

Lifetime	> 2000 mating cycles
Wiring	Solder contacts
Mounting direction	front

Chassis shape	D
<b>Material</b>	
Contact plating	5 µm Au over 5 µm Ni
Contacts	Brass (CuZn39Pb3)
Shell	Zinc diecast (ZnAl4Cu1)
<b>Environmental</b>	
Flammability	UL 94 HB
Standard compliance	IEC 601-14
Protection class	IP 40
Solderability	Complies with IEC 68-2-20
Temperature range	-30 °C to +80 °C

#### Accessories



CAS-DUMMY



DSS-\*



MFD



NDP



SCDP-\*



SCDX

