



NP2XL

2 pole 1/4" professional phone plug, up to 10 mm cable O.D.

The professional 1/4" jumboPLUG for thick instrument and loudspeaker cables offers an ergonomic barrel and incorporates the proven features and benefits of the standard PX range.

Features & Benefits

- Robust diecast shell in stylish design
- Ergonomic design for best handling convenience
- Proven chuck type strain relief for reliable cable retention
- Precision machined one-piece contacts - avoid hook up of tip contact

Technical Information

Product

Title	NP2XL
--------------	-------

Electrical

Contact resistance	? mΩ depends on mating connector
Dielectric strength	1 kVdc
Insulation resistance	> 2 GΩ (initial), ≥ 1 GΩ (after damp heat test)
Rated current per contact	? A depends on mating connector
Rated voltage	< 50 V

Mechanical

Cable O.D.	≤ 10 mm
Lifetime	> 1000 mating cycles
Wiresize	1 mm ²
Wiresize	18 AWG

Environmental

Standard compliance	IEC 60603-11 / EIA RS-453
Temperature range	-20 °C to +65 °C