



## Detailed Specifications

<b>Expected Life:</b>	25 degree C 100,000 Hours (L10)
<b>DC Fan:</b>	IP69K Ball Bearing Fan
<b>Nominal Voltage:</b>	24[V]
<b>Operating Voltage Lower:</b>	10[V]
<b>Operating Voltage Upper:</b>	26.4[V]
<b>Industry:</b>	Industrial Machines
<b>Current:</b>	0.5[A]
<b>Input Power:</b>	12[W]
<b>Speed:</b>	7000[ $\text{min}^{-1}$ ]
<b>Max. Air Flow:</b>	3[m <sup>3</sup> /min]
<b>Max. Air Flow:</b>	105.9[CFM]
<b>Max. Static Pressure:</b>	275[Pa]
<b>Max. Static Pressure:</b>	1.1[In H <sub>2</sub> O]
<b>Noise:</b>	59[dB]
<b>Mass:</b>	220[g]
<b>Fan Size:</b>	92[mm]
<b>Fan Width:</b>	32[mm]

DC Fans