

D-SUB SOLDER CUP CONNECTORS - D SERIES

UL Listing No. E196862

CSA File No. 213627

SPECIFICATIONS:

Not RoHS or ELV Compliant

MECHANICAL:

Shell: Steel

Finish: Yellow zinc chromate or tin plated

Insulator: Glass filled PBT UL94V0

CONTACTS:

Machined Pin: Brass


Stamped Pin: Brass

Contact Engagement Force: Max. 12 oz. [3.40N]

Contact Separation Force: Max 0.75 oz. [0.20N]

Finish: Reference Catalog Page or Drawing

[DRAWING](#)



ELECTRICAL:

Current Rating: 3 amps

Voltage Rating : 300 vdc

Dielectric Withstanding Voltage: 1000 vac @ 1 min.

Insulation Resistance: >3000 meg ohm @ 500v

Contact Resistance: <15 milli ohms (mated)

Temperature Range: -55° TO +105° C

Available Sizes:

Male: 9, 15, 25, 37 & 50 position

Female: 9, 15, 25, 37 & 50 position

Part Numbers

D9PTE	D9PTEC	D9PTES	D9PTESC
D9ST	D9STC	D9STS	D9STSC
D15PTE	D15PTEC	D15PTES	D15PTESC
D15ST	D15STC	D15STS	D15STSC
D25PTE	D25PTEC	D25PTES	D25PTESC
D25ST	D25STC	D25STS	D25STSC
D37PTE	D37PTEC	D37PTES	D37PTESC
D37ST	D37STC	D37STS	D37STSC
D50PTE	D50PTEC	D50PTES	D50PTESC

D50ST

D50STC

D50STS

D50STSC
